




Microscopes•Digital Scopes•Video Inspection Systems•Cameras•Illumination•Magnifying Lamps•Hand Tools Soldering Test and Measurement Instruments•Bench Accessories



2017 Digital Catalog

Table of Contents



Product Category	Page(s)
New At Aven	3-8
Digital Microscopes	9-10
Stereo Zoom Microscopes	11-16
Video Inspection Systems	17 - 20
Microscope & Video Accessories	21-29
Magnifiers	30 - 32
Magnifying Lamps & Accessories	33- 35
Work Lights	36
Hand Tools	37 - 43
Precision Cutters & Pliers	44 - 51
Tweezers	52 - 59
Soldering & Desoldering	60 - 64



Mighty Scope HD High Definition Digital Microscope





Small, But Mighty

Inspect and analyze with ease directly from your HD monitor. Compact and handy, the Mighty Scope HD can be mounted to the included stand or be used hand held, and produces detailed, trueto-life images. Built-in features include digital zoom, LED brightness control, focus control, and on-screen menu controls. The Mighty Scope HD is ideal for applications where PC use is not feasible, such as workbenches with space limitations and assembly lines.

Features

- 1080p Resolution
- 3x 270x Optical Magnification
- Digital Zoom up to 2x on-screen magnification
- Freeze Frame Mode
- Adjustable screen settings
- 6 adjustable LEDs
- Easy HDMI plug-and-play

Mighty Scope HD Digital Microscope	
Effective Pixels	1280x1024
Image Sensor	1/4" CMOS Color
Video Format	1080p @ 60 Frames Per Second
Magnification	3x-270x
LED Lighting	6 LEDs with brightness control
Signal Output	HDMI
Gain Control	Automatic
Digital Magnification	Up to 2x on-screen digital zoom
Power Consumption	5V 470 mA
Stand	6" pole stand with fine focus adjustment
LED Type	6 white LEDs
Package Contents	Mighty Scope HD HDMI cable Adjustable Stand Manual Power Adapter

Part #	Description	Price
26700-230	Mighty Scope HD Digital Microscope	\$395.00





SharpVue HD Video Inspection System Futuristic, Innovative and Easy to Use Item#

The SharpVue features an auto focus HD camera with optical magnification of up to 20x or 30x, and digital magnification up to 300x depending on the lens used. The SharpVue produces high quality 1080p HD images without any distortion or delay and with excellent depth of field. The built in LED lights ensures shadow-free illumination even when viewing shiny objects. The SharpVue features a large working distance of 9 inches, ensuring that objects of any size can be inspected. This system is operated with the included wireless remote. Zoom in and out, turn auto focus on or off, insert a cross hair, fine tune your focus, and much more all with a touch of a button.

Includes HDMI and USB outputs. Connect the SharpVue to your computer via USB cable to utilize the included imaging and measurement software.

ltem#	Description
26700-135	SharpVue Video Inspection System
Magnification	20x and 30x
Resolution	1080p (monitor) / 720p (Computer)
Zoom	20x Optical, 12x Digital
Output	USB / HDMI
Lighting	Built-in angled LED
Focus	Auto/Manual
Image/Video	With imaging software
Dimensions	16.14″ x 6.7″ x 13.78″
Weight	9.9 lbs
Package Contents	Aven Sharpvue system, Imaging Software, wireless remote control



SharpVue Video Inspection System

Modern Design, Ease Of Use

Aven's SharpVue system is designed to inspect, capture images and video, and much more with ease. Adjust your settings with the included easy-to-use remote control.





The SharpVue offers crystal-clear 1080p imaging, with a magnification of up to 30x optical zoom, 300x Digital zoom. View your images on an HD monitor, eliminating the eye strain and fatigue from frequent microscope use.



Built-In Features



Built-in LED lights for shadow-free illumination



USB and HDMI outputs. Connect to your monitor for lagfree 1080p inspection with the HDMI port. Or use the USB port to connect to your PC.

For more information on SharpVue accessories visit **aveninc.com**



SharpVue X-Y Sliding Table Item # 26700-135-XYTB



Image Capture Box Item # 26700-401-CB



SharpVue Tiltable Table Item # 26700-135-TTB



LCD 1080p Monitor Item # 26700-406





This innovative inspection scope connects directly to an HD monitor through a convenient 1080p HDMI output allowing operators to view high quality magnified images while looking straight ahead at a large screen, rather than hunching over narrow eyepieces. A large working distance and 30 LEDs that can be adjusted for intensity allow examination of objects of various sizes. Magnification ranges up to 132x on a 21.5" HD monitor.

This breakthrough instrument increases accuracy and productivity while easing eye strain and user fatigue from frequent microscope use, valuable benefits in high-volume applications.

Features

- 2-megapixel sensor
- HDMI output connects directly to an HD monitor future firmware updates
- 30 energy-efficient LED illumination with intensity control
- Up to 132x Magnification
- Infrared remote control for all major features

Cyclops HDMI Digital Microscope	
Effective Pixels	2M Pixels
Image Sensor	CMOS Color
Frames Per Second	30FPS
Magnification / Zoom	Up to 132x
LED Lighting	30 White LEDs with brightness & sector control
Video Output	1920x1080p HD
Gain Control	Automatic
Power Source	DC 5A/2A input; Cable length: 180cm
Power Consump- tion	0.225A (MAX)
Dimensions	106 x 152 mm
Weight	0.70 lbs. 310g

Part #	Description	Price
26700-401	Cyclops HDMI Digital Microscope	\$750.00



Cyclops Digital Microscope Accessories



Provides a constant laser point to highlight exact areas for display or inspection. Attaches to the Cyclops stand. Includes light intensity control.



AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com

AVEN Mighty Cam 3.0 USB Camera

Expererience USB 3.0 Speed

Aven's Mighty Cam 3.0 is the new generation USB3.0 camera. Capable of frame rates more than double of USB 2.0 devices, the Mighty Cam 3.0 is ideal for applications that require reduced image lag times. Simply attach the Mighty Cam 3.0 to your microscope, plug in the USB 3.0 cable and connect to your computer. Includes ezMeasure software to capture stunning images, record video, make accurate measurements and more.

Part #	Description	Sensor
26100-244	Mighty Cam 3.0	смоѕ



- USB 3.0 interface provides high speed image transfer rates.
- Automatic/Maunual White Balance
- Progressive Scan
- USB cable plugs into any computer to save, process and share images
- Windows 7 & 8-compatible ezMeasure Software
- Ideal for applications that require reduced lag times

Mighty Cam CCD USB Camera

See the CCD Difference

The Mighty Cam CCD is designed for challenging lighting and color conditions. The CCD sensor provides precise color reproduction and highly detailed images for your demanding applications. The Mighty Cam CCD is capable of high resolution images with low noise and can precisely capture moving objects.

Part #	Description	Sensor
26100-245	Mighty Cam CCD	CCD



- 1/2" 1.4MP Color CCD Sensor provides crisp images with accurate color
- Automatic/Maunual White Balance
- Progressive Scan
- USB cable plugs into any computer to save, process and share images
 - Windows 7 & 8-compatible ezMeasure Software
- Ideal for challenging lighting and color conditions

Digital Microscopes

Inspect, analyze & measure with ease on your PC

Mighty Scope USB Digital Microscopes

- New Models available with 1.3 and 5MP CMOS sensor
- Active Pixel Technology produces sharp and accurate color images
- Microtouch shutter allows for quick and convenient image capture
- Compatible with Windows and Mac
 10 200% 500% LW and Near Infrared
- 10-200x, 500x, UV and Near Infrared models
- Ergonomic design allows comfortable use in either hand
- Includes measurement software and adjustable metal stand
- 10-200x available with polarizer



"Inspect, analyze, measure easily on your laptop"

Product ID	Description
26700-200	Mighty Scope 1.3M USB Digital Microscope (10x-200x)
26700-200-PLR	Mighty Scope 1.3M USB Digital Microscope w/Polarizer (10x-200x)
26700-204	Mighty Scope 1.3M USB Digital Microscope (500x)
26700-205	Mighty Scope 1.3M USB Digital Microscope w/ UV Illumination (10x-200x)
26700-207	Mighty Scope 5M USB Digital Microscope w/NIR Illumination (10x-200x)
26700-209	Mighty Scope 5M USB Digital Microscope (10x-200x)
26700-209-PLR	Mighty Scope 5M USB Digital Microscope with Polarizer (10x-200x)
26700-216	Mighty Scope 1.3M Polarizer
26700-217	Mighty Scope 5M Polarizer

Register online to receive updates on the newest products and for the latest specials from Aven.







Digital Microscopes

Inspect, analyze & measure with ease on your PC

Cyclops Digital Microscope

This innovative inspection scope connects directly to an HD monitor as well as to a computer. Operators observe magnified videos or single frames while looking directly at the monitor, rather than straining over narrow eyepieces. A large working distance and 30 LEDs allow examination of sizable objects. Magnification ranges up to 270x on a 21.5" extended monitor or 534x for PC viewing.

- Dual output HDMI and USB
- Auto Focus enabled
- Designed to maximize efficiency and operator comfort
- 5-megapixel sensor
- High magnification range and extended working distance
- Up to 273x magnification in HDMI mode and 534x in PC mode
- ▶ LED illumination with intensity control
- Infrared remote control for all major features
- Includes standard 4x objective lens and measurement software
- Optional articulating arm stands and 10x lens available

Product ID	Description
26700-400	Cyclops Digital Microscope
26700-400-L10X	Cyclops Objective Lens 10X
26700-400-L4X	Cyclops Objective Lens 4X
26700-400-RC	Cyclops Remote Control
26700-400-STN	Cyclops Stand
26700-400-GN	Cyclops Gooseneck LED Lights

Digital Microscope Stands



Product ID	Description	
26700-210	Mighty Scope Boom Stand	
26700-211	Mighty Scope Standard Stand	
26700-212	Mighty Scope Flex Stand	
26700-213	Mighty Scope Cradle Stand	
26700-214	Mighty Scope Stand with Fine Adjustment	
26700-215	Mighty Scope Dual View Stand	
26700-311	Universal Digital Microscope Stand w/Backlight	
26700-312	3D Stand for Digital Microscopes and Cameras	
26700-312-LED	3D Stand with LED for Digital Microscopes and Cameras	
26700-410-C18	Cyclops Articulating Arm Stand, Post Height 17-in	
26700-411-C15	Cyclops Articulating Arm Stand, Post Height 12-in	-



"Dual-mode scope features HDMI and USB outputs"



High-grade optics and unibody design

SPZ-50 Series Stereo Zoom

Microscopes

Pro SPZ SPZ

- Magnification Range: 6.7x to 50x (3.35x to 200x with optional lenses)
- Large 7.46:1 Zoom Ratio (best Zoom Ratio in this class)
- Field of View: 34.3mm to 3.6mm (1.35" to 0.14")
- Working Distance: 108mm (4.25")
- Includes high eye point DHW10x (F.N.23) eyepieces for comfortable viewing even for operators with eyeglasses
- Optional eyepieces available include DHW15x (F.N.15) & DHW20x (F.N.11.4)
- Trinocular body type features click stop zoom adjustment SPZV-50 for extremely accurate measuring
- Trinocular port includes easy adjust C-mount camera adapter for fine focusing
- Includes rubber eyeguards and dust cover

oduct ID	Description
Z-50	SPZ-50 Stereo Zoom Binocular Microscope
ZV-50	SPZV-50 Stereo Zoom Trinocular Microscope

Optical Data for SPZ-50 & SPZV-50

Eyepiece DHW10x (F.N.23)					
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x	w/2x
Magnifications	6.7x-50x	3.35x-25x	5x-37.5x	10.72x-80x	13.4x-100x
Working Dist.	108mm	240mm	132mm	50mm	41mm
Field of View	34.3-4.6mm	68.9-9.2mm	45.7-6.1mm	21.4-2.8mm	17.1-2.3mm

Eyepiece DHW15x (F.N.15)					
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x	w/2x
Magnifications	10.05x-75x	5.02x-37.5x	7.53x-56.25x	16.08x-120x	20.1x-150x
Working Dist.	108mm	240mm	132mm	50mm	41mm
Field of View	22.3-3mm	44.7-6mm	29.8-4mm	16-1.8mm	11.1-1.5mm

Eyepiece DHW20x (F.N.11.4)					
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x	w/2x
Magnifications	13.4x-100x	6.7x-50x	10.05x-75x	21.44x-160x	26.8x-200x
Working Dist.	108mm	240mm	132mm	50mm	41mm
Field of View	17-2.2mm	34-4.5mm	22.6-3mm	10.6-1.4mm	8.5-1.1mm

NOTE: When creating your own microscope system, the 0.5x Auxiliary Lens cannot be used on the SPZ series body with stands P, PF, T and TL.

> Register online to receive updates on the newest products and for the latest specials from Aven.

SPZH-135 Series Stereo Zoom Microscopes

- Magnification Range: 21x to 135x (14x to 180x with optional lenses)
- 6.4:1 Zoom Ratio
- Field of View: 34.3mm to 3.6mm (1.35" to 0.14")
- Working Distance: 84mm (3.3")
- Includes high eye point DHW15x (F.N.15) eyepieces for comfortable viewing even for operators with eyeglasses
- DHW20x (F.N.11.4) optional eyepieces available
- Trinocular body type features click stop zoom adjustment for extremely accurate measuring
- Trinocular port includes easy adjust C-mount camera adapter for fine focusina
- Includes rubber eyeguards and dust cover

Product ID	Description
SPZH-135	SPZH-135 Stereo Zoom Binocular Microscope
SPZHT-135	SPZHT-135 Stereo Zoom Trinocular Microscope

Optical Data for SPZH-135 & SPZHT-135

Eyepiece	DHW15x (F.N.15)		DHW20x (F.N.11.4)	
Auxiliary Lens	Nil	w/0.5x	Nil	w/0.5x
Magnifications	21x-135x	10.5x-67.5x	28x-180x	14x-90x
Working Dist.	84mm	135mm	84mm	135mm
Field of View	10.7-1.6mm	21.4-3.3mm	8.1-1.2mm	16.2-2.5mm

NSW Series Binocular Stereo Microscopes

- Dual magnification (10x/20x; 10x/30x; 6x/20x)
- Field of view 38.3mm at 6x
- Field of view 23mm at 10x
- Field of view 11.5mm at 20x
- Field of view 7.6mm at 30x
- Includes DSW10x (F.N.23) eyepieces
- Includes rubber eyeguards and dust cover

Product ID	Description
NSW-20	Dual Magnification 10x & 20x Stereo Body
NSW-30	Dual Magnification 10x & 30x Stereo Body

Optical Data for NSW Series Binocular Stereo Microscopes

Models	NSW-20 NSW-30 NSW-620				
Magnification (Field of View)			6x (38.3mm) 20x (11.5mm)		
Objective Lenses	1x & 2x	1x & 3x	0.6x & 2x		
Eyepieces	Wide Field DSW10x (F.N.23)				
Optical Body	360° rotatable binocular type 45° inclined eyepiece tube				
Working Distance	82.5mm	82.5mm	82.5mm		

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com





SPZH-135

NSW-20



High-grade optics and unibody design

DSZ-44 Series Stereo Zoom Microscopes

- Magnification Range: 10x to 44x (2.5x to 140.8x with optional lenses)
- Zoom ratio: 4.4:1
- Field of view 23mm to 5.2mm (0.90" to 0.20")
- Working distance: 90mm (3.54")
- Includes Wide Field DSW10x (F.N.23) eyepieces
- Optional eyepieces available include DSW5x (F.N.22.5), DSW15x (F.N.15) & DSW20x (F.N.11.4)
- Trinocular port includes easy adjust C-mount camera adapter for fine focusing
- Includes rubber eyeguards and dust cover

Product ID	Description	
DSZ-44	DSZ-44 - Stereo Zoom Binocular Microscope	
DSZV-44	DSZV-44 - Stereo Zoom Trinocular Microscope	

DSZV-44

Optical Data for DSZ-44 & DSZV-44

Eyepiece DSW5x (F.N. 22.5)			
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x
Magnifications	5x-22x	2.5x-11x	3.75x-16.5x	8x-35.2x
Working Dist.	90mm	150mm	105mm	45mm
Field of View	22.5-5.1mm	45-10.2mm	30-6.8mm	14-3.1mm
Eyepiece DSW10x	Eyepiece DSW10x (F.N. 23)			
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x
Magnifications	10x-44x	5x-22x	7.5x-33x	16x-70.4x
Working Dist.	90mm	150mm	105mm	45mm
Field of View	23-5.2mm	46-10.4mm	30.6-6.9mm	14.3-3.2mm

Eyepiece DSW15X (F.N. 15)				
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x
Magnifications	15x-66x	7.5x-33x	11.25x-49.5x	24x-105.6x
Working Dist.	90mm	150mm	105mm	45mm
Field of View	15-3.4mm	30-6.8mm	20-49.5mm	9.3-2.1mm

Eyepiece DSW20X (F.	N. 11.4)			
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x
Magnifications	20x-88x	10x-44x	15х-ббх	32x-140.8x
Working Dist.	90mm	150mm	105mm	45mm
Field of View	11.4-2.5mm	22.8-5.1mm	15.2-3.45mm	7.1-1.6mm

DSZ-70 Series Binocular Zoom Microscopes

- Magnification Range: 20x to 70x (5x to 224x with optional lenses)
- 3.5:1 Zoom Ratio
- Field of View: 10mm to 2.8mm (0.39' to 0.11")
- Working Distance: 80mm (4.25")
- Includes DSW10xZ (F.N.20) eyepieces
- Optional eyepieces available include DSW5xZ (F.N.20), DSW15x (F.N.15) & DSW20x (F.N.11.4)
 Versatile binocular microscope best suited for
- high magnification applications
- Includes rubber eyeguards and dust cover

Product ID	Description
DSZ-70	DSZ-70 - Binocular Stereo Zoom Microscope

Optical Data for DSZ-70

Eyepiece DSW5xZ (F.N.20)					
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x	
Magnifications	10x-35x	5x-17.5x	7.5x-26.25x	16x-56x	
Working Dist.	80mm	120mm	85mm	41mm	
Field of View	10-2.9mm	20-5.7mm	13.3-3.8mm	6.2-1.7mm	
Eyepiece DSW10xZ (F.N. 20)					
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x	
Magnifications	20x-70x	10x-35x	15x-52.5x	32x-112x	
Working Dist.	80mm	120mm	85mm	41mm	
Field of View	10-2.8mm	20-5.7mm	13.3-3.8mm	6.2-1.7mm	
Eyepiece DSW15x (F.N. 15)					

Eyepiece DSW15x (F.N. 15)				
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x
Magnifications	30x-105x	15x-52.5x	22.5x-78.75x	48x-168x
Working Dist.	80mm	120mm	85mm	41mm
Field of View	7.5-2.1mm	15-4.2mm	10-2.8mm	4.6-1.3mm

Eyepiece DSW20x (F.N. 11.4)					
Auxiliary Lens	Nil	w/0.5x	w/0.75x	w/1.6x	
Magnifications	40x-140x	20x-70x	30x-105x	64x-224x	
Working Dist.	80mm	120mm	85mm	41mm	
Field of View	5.7-1.6mm	11.4-3.2mm	7.6-2.1mm	3.5-1mm	



Design Your Own Microscope System

With a large variety of cameras, lighting options, and stands and focus mounts, you can create and order your own customized microscope system on our website. If you need help creating a custom system, please call our experienced sales team and let them assist you in creating a tailor made solution that will meet your specific requirements.



www.aveninc.com



Preconfigured Microscope Systems



SPZH-135 Stereo Zoom **Binocular Microscope** on Stand PLED

- Magnification Range: 21x to 135x
- Zoom Ratio: 6.4:1
- Field of View: 10.7-1.6mm (0.42" to 0.6")
- Working Distance: 84mm (3.3")
- Includes high eye point DHW15x (F.N.15) eyepieces for comfortable viewing even for operators with eyeqlasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 50mm to 74mm (1.96" to 2.91") accommodates any operator
- Pole stand with built in LED illumination with dimmer control
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

26800B-351 SPZH-135 Stereo Zoom Binocular Microscope on Stand PLED

SPZH-135 Stereo Zoom

Microscope with DBL Arm Boom, EARM, LED FOI

illumination

- Magnification Range: 21x to 135x ►
- Zoom Ratio: 6.4:1
- Field of View: 10.7-1.6mm (0.42" to 0.6")
- Working Distance: 84mm (3.3")
- Includes high eye point DHW15x (F.N.15) evepieces for comfortable viewing even for operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 50mm to 74mm (1.96" to 2.91") accommodates any operator
- Mounted in an E-ARM focus mount attached to a Double Arm Boom Stand that delivers the smooth movement of a ball bearing slide, letting the microscope glide easily over and across objects being viewed
- High Output LED fiber optic illuminator and ring light provide clear illumination for imaging
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

26800B-352 SPZH-135 Stereo Zoom Microscope w/ DBL Arm Boom, EARM, LED FOI

> Register online to receive updates on the newest products and for the latest specials from Aven.

SPZHT-135 Stereo Zoom Trinocular Microscope

on Stand PLED with HD Monitor

- Magnification Range: 21x to 135x
- On screen Magnification Range: 27x to 179x
- Zoom Ratio: 6.4:1
- Field of View: 10.7-1.6mm (0.42" to 0.6")
- Working Distance: 84mm (3.3")
- Includes high eye point DHW15x (F.N.15) eyepieces for comfortable viewing even for operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 50mm to 74mm (1.96" to 2.91") accommodates any operator
- Click stop zoom adjustments for accurate, repeatable measurement
- 1080P HD camera for unsurpassed imagery
- One touch fine focus trinocular camera port adjustment for quick 889 camera focus and parfocaling the scope
- Pole stand with built in LED illumination with dimmer control
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work
- Monitor helps increase productivity by reducing eye & neck strain

Product ID Description

SPZHT-135 Stereo Zoom Trinocular Microscope on Stand PLED with HD 26800B-353

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108





26800B-351



Preconfigured Microscope Systems

26800B-371

SPZ-50 Stereo Zoom Binocular Microscope on Stand DABS w/ Integrated LED Ring Light

- Magnification Range: 6.7x to 50x
- Large Zoom Ratio: 7.46:1

AVEN

- Field of View: 34.3mm to 4.6mm (1.35" to 0.18")
- Working Distance: 108mm (4.25")
- Includes high eye point DHW10x (F.N.23) eyepieces for ► comfortable viewing even for operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Double Arm Boom Stand delivers smooth movement of a ball bearing slide, letting the microscope glide easily over and across objects being viewed
- Tiltable arbor enables you to angle the microscope for maximum comfort and viewing
- Integrated 60 LED Ring Light with dimmer
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

SPZ-50 Stereo Zoom Binocular Microscope on Stand DABS & Integrated 26800B-369 LED Ring Light

SPZ-50 Stereo Zoom Binocular Microscope on Stand DABS with LED FOI

- Magnification Range: 6.7x to 50x
- Large Zoom Ratio: 7.46:1
- Field of View: 34.3mm to 4.6mm (1.35" to 0.18")
- Working Distance: 108mm (4.25")
- Includes high eye point DHW10x (F.N.23) eyepieces for comfortable viewing even for operators with 26800B-370
- Diopter adjustment on both eyepiece tubes

eyeglasses

- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Double Arm Boom Stand delivers smooth movement of a ball bearing slide, letting the microscope glide easily over and across objects being viewed
- Tilt able arbor enables you to angle the microscope for maximum comfort and viewing
- High Output LED fiber optic illuminator and ring light provide clear illumination for imaging
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

26800B-370 SPZ-50 Stereo Zoom Binocular Microscope on Stand DABS w/ LED FOI



AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

SPZ-50 Stereo Zoom

Binocular Microscope on Stand PLED

- Magnification Range: 6.7x to 50x
- Large Zoom Ratio: 7.46:1
- Field of View: 34.3mm to 4.6mm (1.35" to 0.18")
- Working Distance: 108mm (4.25")
- Includes high eye point DHW10x (F.N.23) eyepieces for comfortable viewing even for operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Pole stand with built in LED illumination with dimmer control
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

SPZ-50 Stereo Zoom Binocular Microscope on Stand DABS & Integrated 26800B-371 LED Ring Light

SPZ-50 Stereo Zoom Binocular Microscope

on Stand LW & LED Ring Light

- Magnification Range: 6.7x to 50x
- Large Zoom Ratio: 7.46:1
- Field of View: 34.3mm to 4.6mm (1.35" to 0.18")
- Working Distance: 108mm (4.25")
- Includes high eye point DHW10x (F.N.23) eyepieces for comfortable viewing even for operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Mounted in an E-ARM focus mount attached to a LW articulating arm stand that extends area of view and working distance
- 60 LED Ring Light with brightness and 4 sector control
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

26800B-372 SPZ-50 Stereo Zoom Binocular Microscope on Stand LW & LED Ring Light

SPZ-50 Stereo Zoom Microscope on Stand P with Diffuse Axial LED Illuminator

- Magnification Range: 6.7x to 50x
- Large Zoom Ratio: 7.46:1
- Field of View: 34.3mm to 4.6mm (1.35" to 0.18")
- Working Distance: 108mm (4.25")
- Includes high eye point DHW10x (F.N.23) eyepieces for comfortable viewing even operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Compact lightweight pole stand with focus mount
- Diffuse Axial LED Illuminator, ideal for viewing highly relective parts, eliminates hot spots & reduces glare
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

SPZ-50 Stereo Zoom Binocular Microscope on Stand P w/ Diffuse Axial 26800B-384 Illuminator



- 26800B-384





Preconfigured Microscope Systems

DSZ-44 Stereo Zoom Binocular Microscope on Stand DABS with LED FOI

- Magnification Range: 10x to 44x
- Zoom Ratio: 4.4:1
- Field of View: 23-5.2mm (0.91" to 0.2")
- Working Distance: 90mm (3.54") Includes wide field DSW10x (F.N.23)
- eyepieces Diopter adjustment on both
- eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Double Arm Boom Stand delivers smooth movement of a ball bearing slide, letting the microscope glide easily over and across objects being viewed
- Tiltable arbor enables you to angle the microscope for maximum comfort and viewing
- High Output LED fiber optic illuminator and ring light provide clear illumination for imaging
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Optic Illuminator

Product ID Description DSZ-44 Stereo Zoom Binocular Microscope on Stand DABS with LED Fiber 26800B-303

DSZ-44 Gemscope

- Magnification Range: 10x to 44x
- Zoom Ratio: 4.4:1
- Field of View: 23-5.2mm (0.91"-0.2")
- Working Distance: 90mm (3.54")
- Includes wide field DSW10x (F.N.23) eyepieces
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Gemology stand (inclines from 0-10°) with independently controllable fluorescent front light and dimmable halogen pipe light with separate controls
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

26800B-386 DSZ-44 Gemscope

DSZV-44 Gemscope w/1080P

HD Camera

- Magnification Range: 10x to 44x
- Zoom Ratio: 4.4:1
- Field of View: 23-5.2mm (0.91"-0.2")
- Includes wide field DSW10x (F.N.23) eyepieces
 - Diopter adjustment on both eyepiece tubes
 - Adjustable Interpupillary Distance of 52mm to 2.95") accommodates any operator
- 1080P HD camera for unsurpassed imagery
- Gemology stand (inclines from 0-10°) with independently controllable fluorescent front light and dimmable halogen pipe light with separate controls
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work
- Monitor helps increase productivity by reducing eye & neck strain

Product ID Description

26800B-387 DSZV-44 Gemscope w/1080P HD Camera

DSZV-44 Stereo Zoom Trinocular Microscope on Stand PLED with Mighty Cam USB 5M CMOS Camera

- Magnification Range: 10x to 44x
- Zoom Ratio: 4.4:1
- Field of View: 23-5.2mm (0.91"-0.2")
- Working Distance: 90mm (3.54")
- Includes wide field DSW10x (F.N.23) eyepieces
- Diopter adjustment on both evepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Mighty Cam USB 5M CMOS Camera with ezMeasure software
- Pole stand with built in LED illumination with dimmer control
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

DSZV-44 Stereo Zoom Trinocular Microscope on Stand PLED with Mighty 26800B-323 Cam USB 5M CMOS Camera

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com

See Aven's exclusive article "How to Select the Right Microscope or Video Inspection System"





26800B-386





26800B-303

- Working Distance: 90mm (3.54")



to 75mm (2.04"

Preconfigured Microscope Systems

DSZV-44 Stereo Zoom Trinocular Microscope on Stand PLED

HD Camera and 8" HD Monitor

- Magnification Range: 10x to 44x
- Zoom Ratio: 4.4:1
- Field of View: 23-5.2mm (0.91"-0.2")
- Working Distance: 90mm (3.54") ►
- Includes wide field DSW10x (F.N.23) eyepieces
- ► Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm ► (2.04" to 2.95") accommodates any operator
- 1080P HD camera for unsurpassed imagery
- Pole stand with built in LED illumination with dimmer control
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

26800B-327	DSZV-44 Stereo Zoom Trinocular Microscope on Stand PLED HD Camera and 8" HD Monitor

DSZ-70 Stereo Zoom Binocular Microscope on Stand P with LED FOI

- Magnification Range: 20x to 70x
- Zoom Ratio: 3.5:1 ►
- Field of View: 10-2.8mm (0.39"-0.11")
- Working Distance: 80mm (3.15") Includes wide field DSW10xZ (F.N.20) ►
- eyepieces
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates operator
- Compact lightweight pole stand with focus mount
- High Output LED fiber optic illuminator and ring light provide clear illumination for imaging
- Multi coated optical components, free from chromatic and spherical aberration
- Coarse and fine focusing, ideal for fine detail work

Product ID Description

DSZ-70 Stereo Zoom Binocular Microscope on Stand P with LED Fiber 26800B-344 Optic Illuminator

NSW-20 Stereo Binocular Microscope with Stand PLED

- Magnification: 10x & 20x
- Field of View 10x; 23mm (0.91")
- Field of View 20x: 11.5mm (0.45") ►
- Working Distance: 113mm (4.45")
- Includes wide field DSW10x (F.N.23) eyepieces
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 52mm to 75mm (2.04" to 2.95") accommodates any operator
- Pole stand with built in LED illumination with dimmer control
- Multi coated optical components, free from chromatic and spherical aberration

26800B-360

Coarse and fine focusing, ideal for fine detail work

Product ID Description 26800B-360 NSW-20 Stereo Binocular Microscope with Stand PLED

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108





any







Video Inspection System Lenses



Micro Lens System Zoom 640

- Infinity Optical Design for large depth of field and zoom ratio
- Parfocal throughout zoom range
- Compact design
- High contrast images and vivid colors

produces crisp Aven Micro Lens System and clear images that are distortion free and void of chromatic aberration. This lens system comes with detents which allows you to calibrate the lens for measurement repeatability. Comes standard with 1x C mount coupler and 1x objective lens. Total magnification is 0.6x to 4.0x, Field of View is 6 x 8mm at low magnification and 0.8 x 1.2mm at high magnification. Working Distance is 82mm. Additional couplers and objective lenses are available to help you configure a lens system to meet your application.

Micro Lens System Zoom 640



26700-151

Micro Lens System FM123

- Four Lenses
- Switchable Magnification
- Object stays in focus when switching magnification
- Can be used as a monocular microscope with included 10x eyepiece
- C-Mount Adapter Included

The Micro FM123 lens has four switchable lenses, 0.78x, 1.56x, 2.34x and 3.12x, located in the unit. Simply rotate the head to switch between magnifications. It includes a 10x eyepiece which allows you to use the lens as a monocular microscope with magnification of 7.8x, 15.6x, 23.4x and 31.2x. Using a 1/3" CCD camera and a 19" monitor, the on screen magnification is about 62x, 125x, 188x and 250x subject to 4:3 aspect ratio of both screen and camera chip. For other aspect ratio such as 16:9, these magnifications may change depending on the screen and the camera used. Ideal for high magnification field of view measurement.



26700-

	duct ID	Description
2670	00-151	Micro Lens System FM123

Macro Lens System Zoom 7000

- 6:1 zoom ratio
- 6x magnification over focal range of 18mm to 108mm (0.71" to 4.25")
- Working distance 127mm (5") to Infinity
- Compatible with cameras 16.9mm (0.67") or smaller

The Zoom 7000 is a close focusing macro video lens ideal for applications where objects over 25mm (1") in diameter must be imaged. It offers unsurpassed clarity and parfocal zoom capabilities. Compatible with cameras 2/3" (16.9mm) or smaller. Ideal for quality assurance or assembly applications



where easy to view, sharp and true to life magnified image of your product is required.

Product ID	Description
26700-180	Macro Lens System Zoom 7000

Create Your Own Custom Video Inspection System

With a large variety of adapters, auxiliary lenses, cameras, lighting options, video capture cards and stands you can create and order your own customized video inspection system on our website. If you need help creating a custom video inspection system, please call our experienced sales team and let them assist you in creating a tailor made solution that will meet your specific requirements. Whether you are inspecting objects like integrated circuits, solder joints and small parts, or you require magnification for precision assembly we can provide a customized solution to fit your needs.



www.aveninc.com

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108



Micro Lens System Zoom 640 with In Line LED Coaxial Illumination

Description

- Inline Coaxial Illumination for highly reflective surfaces
- Infinity Optical Design for large depth of field and zoom ratio
- Parfocal throughout zoom range
- Compact design

17

Product ID

26700-151

High contrast images and vivid colors

Aven Micro Lens System with inline Coaxial Illumination is ideal for applications involving highly reflective surfaces, such as wafers, polished parts and fluids. This lens system will provide even illumination in high magnification applications. This lens system comes with detents which allows you to calibrate the lens for measurement repeatability. Comes standard with 1x C-mount coupler and 1x objective lens and LED illuminator with intensity control. Total magnification is 0.6x to 4.0x, Field of view is 6 x 8mm at low magnification and 0.8 x 1.2mm at high magnification. Working distance is 82mm. Additional couplers and objective lenses are available to help you configure a lens system to meet your application.

Product IDDescription26700-151-CXMicro Lens System Zoom 640 with In Line LED Coaxial Illumination



Adapters, Couplers and Objective Lenses

26700-164

26700-165

26700-166

Adapter Plate for Macro Lens Zoom 7000

- Adaptor for Macro Lens Zoom 7000
- For focus mounts (26800B-517 & 26800B-518)
- Outside diameter: 73mm
- Inside diameter: 46.75mm
- 22.5mm height ►



26800B-430

	Product ID	Description	- [2670
26800B-430 Adapter Plate for Macro Lens Zoom 7000	26800B-430	Adapter Plate for Macro Lens Zoom 7000	1	Oh

Adapter Plate for Micro Lens 640

- Adaptor for Micro Lens 640
- For focus mounts (26800B-517 & 26800B-518)
- Outside diameter: 73mm
- Inside diameter: 35.25mm
- 24mm height

26700-151AP

Product ID	Description	O	biec
26700-151AP	Adapter Plate for Micro Lens 640		Obje
			Zoo

C-Mount Coupler 0.5x

- Mounts to Micro Video Lens System Zoom 640
- Reduces magnification by 0.5x ►
- Ideal for cameras with sensors 12.7mm (1/2") or larger
- Can be used with any C-Mount camera
- See optical specification chart for more details


Product ID	Description		
26700-156	C-Mount Coupler 0.5x		

C-Mount Coupler 1.0x

- Mounts to Micro Video Lens System Zoom 640
- Increases magnification by 1x
- Ideal for with sensors less than 16.9mm (2/3") ►
- Can be used with any C-Mount camera
- See optical specification chart for more details

Description

C-Mount Coupler 1.0x



26700-162

Objective Lens 0.5x

Product ID

26700-158

- Objective Lens for Micro Video Lens System Zoom 640
- Reduces magnification by 0.5x
- Color corrected lens system ►
- Working distance 175mm (6.9")
- See optical specification chart for more details

Product ID	Description
26700-162	Objective Lens 0.5x

Objective Lens 0.75x

- Objective Lens for Micro Video Lens System Zoom 640
- Reduces magnification by 0.75x
- Color corrected lens system
- Working distance 117mm (4.6")
- See optical specification chart for more details

Product ID Description Objective Lens 0.75x 700-163

Objective Lens 1x

- Objective Lens for Micro Video Lens System Zoom 640
- Color corrected lens system
- Working distance 82mm (3.2")
- See optical specification chart for more details

Product ID	Description
26700-164	Objective Lens 1x

ctive Lens 1.5x

- jective Lens for Micro Video Lens System om 640
- Increases magnification by 1.5x
- Color corrected lens system
- Working distance 54mm (2.1")
- See optical specification chart for more details

Product ID Description

26700-165 Objective Lens 1.5x

Objective Lens 2x

- Objective Lens for Micro Video Lens System Zoom 640
- Increases magnification by 2x
- Color corrected lens system
- Working distance 35mm (1.4")
- See optical specification chart for more details

Product ID Description 26700-166 Objective Lens 2x

Optical Data Chart

Objective	Objective		CCD Couple	er
Magnification	Working Distance		0.5X	1X
0.3X	WD:293mm	Total Mag.	0.09X0.6X	0.18X1.2X
0.3X		FOV(mm)	40X53.336X8	20X26.673X4
0.5%	WD:175mm WD:177mm WD:82mm WD:54mm	Total Mag.	0.15X1X	0.3X2X
0.5X		FOV(mm)	24X323.6X4.8	12X161.8X2.4
0.75%		Total Mag.	0.225X1.5X	0.45X3X
0.75X		FOV(mm)	16X21.33-2.4X3.2	8X10.67-1.2x1.6
		Total Mag.	0.3X-2X	0.6X-4X
1X		FOV(mm)	12X16-1.8X2.4	6X8-0.9X1.2
		Total Mag.	0.45X-3X	.9X-6X
1.5X		FOV(mm)	8X10.67-1.2X1.6	4X5.33-0.6X0.8
2X	WD:35mm	Total Mag.	0.6X-4X	1.2X-8X
27	WD:35mm	FOV(mm)	6X8-0.9X1.2	3X4-0.45X0.6





X WD:82











Preconfigured Micro Zoom Video Inspection Systems

Micro Zoom Series 640 PK1

- PC not required for image processing
- Produces crisp clear images
- White LED illumination with intensity control
- Color camera with movable and ► switchable crosshairs
- On screen menu for controlling color, contrast, white balance etc.
- 100

26700-102-00

- Heavy Duty Post Stand includes
- 10 tapped holes for mounting x-y stages
- Compact system, helps save bench space
- On screen magnification: 14.25x to 190x
- Working distance: 82mm with 1x Objective Lens Field of view: 6 x 8 to 0.9 x 1.2mm with 1x Objective
- Parfocal lens system

Product ID Description 26700-102-00 Micro Zoom Series 640 PK1

Micro Zoom Series 640 PK2

- PC not required for image processing
- Produces stunning clear and crisp HD images
- White LED Fiber Optic free illumination
- Illumination provides shadow
- 1080P Color Camera with HDMI ►
- output; On screen menu for controlling color, contrast, white balance etc Dual Arm Boom Stand provides stability and eliminates vibrations while allowing you to move over large areas of the object being viewed
- Lens can be angled in any direction for enhanced viewing
- On screen magnification: 19.5x to 263x
- Working distance: 82mm with 1x Objective Lens
- Field of view: 6 x 8 to 0.9 x 1.2mm with 1x Objective
- Parfocal lens system

Product ID Description

26700-102-10 Micro Zoom Series 640 PK2

Micro Zoom Series 640 PK3

Benchtop Measurement System

- Produces crisp clear images; PC not required for image processing
- White LED Fiber Optic Illumination
- HD 1080p Color camera with USB mouse control and Built In Measurement Software
- Measure lines/distance, circles, arcs, squares, polygon, perimeters, angles, center to center distance
- Compact system, helps save bench space
- On screen magnification: 19.5x to 263x
- Working distance: 82mm with 1x Objective Lens

Description

- Field of view: 6 x 8 to 0.9 x 1.2mm with 1x Objective
- Parfocal lens system

Micro Zoom Series 640 PK3 Benchtop Measurement System

Micro Series FM123 PK4 Benchtop Measurement

System

- Measure lines/distance, circles, arcs, and polygons
- Produces crisp and clear images
- White LED Fiber Optic Illumination
- Color camera with USB mouse control and Built in Measurement Software
- On screen menu for controlling color, contrast, white balance etc
- On screen magnification from 44.2x to 176.9x
- Working distance: 64.3mm
- Four switchable lens system: 0.78x, 1.56x, 2.34x, and 3.12x
- Field of view: 6 x 4.5mm @ 0.78x; 3 x 2.2mm @ 1.56x; 2 x 1.5mm @ 2.34x; 1.5 x 1.1mm @ 3.12x

Product ID	Description
26700-102-20	Micro Series FM123 PK4 Benchtop Measurement System

Micro Zoom Series 745 PK1

- Produces crisp clear images
- View object on a large 22" HD Color LED Monitor
- Working distance: 46mm
- Field of view: 8.8 to 1.3mm
- On screen magnification from 50x to 340x
- Compact system helps save bench space
- White top and bottom LED illumination with intensity control
- 720p VGA color camera with cross hair and on screen menu for controlling color, contrast, white balance etc.

Product ID Description 26700-102-30 Micro Zoom Series 745 PK1

Micro Zoom Series 640 with Coaxial Illumination PK 5

- In line coaxial illumination helps reduce
- when inspecting shiny parts Color HD camera with movable and
- switchable crosshairs
- On screen menu for controlling color, contrast and white balance
- Parfocal lens system Working distance: 46mm
- Field of view: 8.8 to 1.3mm
- On screen magnification from 50x to 340x
- Product ID Description 26700-102-35 Micro Zoom Series 640 with Coaxial Illumination PK 5

Product ID

26700-102-15



AVEN

26700-102-20



102-15





26700-102-30









Preconfigured Macro Zoom Video Inspection Systems

Macro Series Zoom 7000 PK M1

- Stunning Life Like Picture on 22" HD LCD Monitor
- Large Magnification Range 3.7x to 61.9x
- Large working distance; 117.8 to 304.8mm
- 6:1 zoom allows for quick magnification of area of interest
- Parfocal over entire zoom range
- PC not required for image processing
- Heavy Duty Post Stand includes 10 tapped holes for mounting x-y stages

Product ID	Description
26700-103-00	Macro Series Zoom 7000 PK M1

22" HD

Macro Series Zoom 7000 PK M2

- Stunning Life Like Picture on ► LCD Monitor
- Large Magnification Range 3.7x to 61.9x
- Large working distance; 117.8 to 304.8mm
- Double Arm "Easy Glide" Boom Stand with heavy base for stability
- Parfocal over entire zoom range
- PC not required for image processing
- 6:1 zoom allows for guick magnification of area of interest

h	Stand
	 Wide field of view and long working distance 60 LED ring light with intensity control 2x Digital Zoom and Mirror function built into Compact and Easy to Use Focus mount includes course and fine adjustm On screen Magnification: 7x - 40x at a 6" workit

26700-103-00

26700-103-10

Product ID Description 26700-117 Macro Vue Eidos Video Inspection System with Standard Stand

Macro Vue Eidos Video Inspection System with Gliding Boom Stand

26700-117

Macro View Eidos With Gliding **Boom Stand**

Macro View Eidos With Standard

2x Digital Zoom and Mirror function built into camera

Focus mount includes course and fine adjustment knobs

On screen Magnification: 7x - 40x at a 6" working distance

- Wide field of view and long working distance
- 60 LED ring light with intensity control
- 2x Digital Zoom and Mirror function built into camera
- Compact and Easy to Use

Product ID

26700-118

- Focus mount includes course and fine adjustment knobs
- On screen Magnification: 7x 40x at a 6" working distance

Description

Product ID	Description
26700-103-10	Macro Series Zoom 7000 PK M2

Macro Series Zoom 7000 PK M3

- Stunning Life Like Picture on 22" ► HD LCD Monitor
- Large Magnification Range 3.7x to 61.9x
- Large working distance: 117.8 to 304.8mm 6:1 zoom allows quick magnification of



- area of interest
- Light weight articulating arm with E-Arm allows users to cover a large working area and move microscope out of the way when not in use
- Parfocal over entire zoom range
- ► PC not required for image processing

Product ID	Description
26700-103-20	Macro Series Zoom 7000 PK M3



CCD & CMOS Cameras

Mighty Cam USB 5M CMOS Camera

The Mighty Cam USB 5M CMOS camera includes ezMeasure software which produces stunning images with exceptional clarity for measuring, analyzing and annotating your magnified images. The large 5M CMOS sensor provides excellent color fidelity offering true color out of the box with no need for adjustment. The versatile C/CS lense mount adapter ring attaches between camera and lens, and converts a CS-Mount lens to C-Mount camera to achieve a focused image.



26100-243

- Provides wide, dynamic range and crisp, natural color reproduction in any lighting
- USB 5M CMOS Camera with ezMeasure Software
- 5M CMOS Sensor (2592 x 1944)
- Easy Plug and Play USB 2.0 Interface
- Compact and Light Weight
- Versatile C/CS lenses mount
- Ideal for inspection, scientific image analysis, biomedical research

Product ID	Description
26100-243	Mighty Cam USB 5M CMOS Camera

Aven's Mighty Cam 3.0 is the new generation USB3.0 camera. Capable of frame rates more than double of USB 2.0 devices, the Mighty Cam 3.0 is ideal for applications that require reduced image lag times. Simply attach the Mighty Cam 3.0 to your microscope, plug in the USB 3.0 cable and connect to your computer. Includes ezMeasure software to capture stunning images, record



26100-244

- USB 3.0 interface provides high speed image transfer rates.
- Automatic/Maunual White Balance
- **Progressive Scan**
- USB cable plugs into any computer to save, process and share images
- Windows 7 & 8-compatible ezMeasure Software

Product ID	Description
26100-244	Mighty Cam 3.0

Mighty Cam VGA Color Camera 720p

Aven's color VGA camera allows connectivity directly to a PC monitor. A PC is not required for image processing thus saving you the cost of a PC and bench space. All features of the digital camera can be controlled via on screen menus such as RGB values, white balance, cross hair, auto exposure, etc.



26100-252

- Compact 720p Color Camera with VGA output
- Live/Freeze Image Function; Cross Hair for quick gaging
- Produces crisp and clear color images in wide screen format
- Auto gain exposure setting to reduce glare
- On screen menu for quick access to camera settings

GA Color Camera 720p
G

Mighty Cam VGA Color Camera 1.3M w/SD Card

Aven's color VGA camera allows you to connect directly to a PC monitor. A PC not required for image processing, thus saving you bench space. In addition, a built in SD card allows you to save images. All features of this digital camera can be controlled via on screen menus, such as RGB values, white balance, cross hair grid, and auto exposure. 4 Vertical and 4 horizontal cross hair grids available with 6 color selections.



26100-253

- Compact 1.3M Color Camera with VGA Output
- Built in SD card for saving images
- Live/Freeze Image Function
- Multiple cross hair for quick gaging
- Produces crisp and clear color images in wide screen format
- Auto gain exposure setting to reduce glare

Product ID	Description
26100-253	Aven VGA Color Camera 1.3M w/ SD Card

Mighty Cam 1080P HDMI Color Camera 2M w/ USB Flash Drive

Aven's 1080P HD color camera allows you to

connect the camera directly to a HD monitor with an HDMI input. A PC is not required for image processing, thus saving you bench space. In addition, a built in USB Flash Drive allows you to save images. All features of this digital camera can be controlled via on screen menus, such as RGB



26100-253HD

values, white balance, cross hair grid, and auto exposure.

- Connects directly to an HD monitor with HDMI input
- Built in USB Flash Drive for saving images
- Live/Freeze image function
- Multiple cross hair for quick gaging
- Produces stunning life like images with exceptional clarity

Product ID	Description
26100-253HD	Aven 1080P HDMI Color Camera 2M w/ USB Flash Drive

Mighty Cam HDMI Color Camera 2.0M w/USB Flash Drive & Built in

Measurement Software

Aven's color HDMI camera with built in USB Flash Drive and measurement software, is a simple solution to those that need to inspect and measure with accuracy. A PC is not required for image processing and no software to install. Images with measurement data can be saved to the built in USB Flash Drive using the remote trigger (included). Built in software includes the following



features: Edge Detection, Live/Freeze Image, Measure line, circle, radius, angle and parallel lines.


- Compact 720p Color Camera with VGA output
- Live/Freeze Image Function; Cross Hair for quick gaging
- Produces crisp and clear color images in wide screen format
- Auto gain exposure setting to reduce glare
- On screen menu for quick access to camera settings

Product ID	Description
26100-254	Aven HDMI Color Camera 2.0M w/SD Card



Imaging & Measurement Software

Measurement Camera Software for 26100-254



Measure and Analyze with Ease

The advanced measurement software is able to detect gray scale gradations and can measure a line, circle, radius, angle and parallel lines in millimeters or inches. Users can save five sets of measurement data on the USB Flash Drive, which simplifies comparisons and record-keeping. White balance and exposure can be automatic or one-click mouse functions.



Capture High Quality Images

Create enhanced still photos with or without measurement lines and save for further analysis.

11	17 -	. 10		
177(11) [31]	. See	Cine	11	1
5.15	0.04			
issue forther	Later Line		1	lin

Optional Capture Settings

Software allows you to choose which image format to save files in (JPG or BMP) and also measurements you added to the image.

a [Electory 0					
		-				Real Property lies
		(interior	-	-	10.00	10.00
	and a second	(Applant)	-		E.R.	1.1
100			-		- N	
				_	10.2	C
		1.0	-		 I 	
-		Circle 1		_	1.1	1000
		100	_		1.2	

Camera Settings

The software also allows you to edit all camera settings. Options include luminance, contrast, RGB values, auto exposure and auto white balance.




Edge Detection Tool

Software has an Intelligent Edge detection tool built in for finding boundaries of objects within images. It works by detecting the discontinuities in brightness.



Easy Measurement Calibration

Calibrating the software for measurement is as simple as placing a ruler or other scale under the lens, selecting the size, e.g. 16mm and pressing the Calibrate button.



Magnifying Window

Software digitally magnifies the area around the mouse pointer by 4x, 9x and 16x (selectable). This is particularly helpful when you need to see minute features.

Additional Features


- ▶ Photo Browser displays images saved on USB Flash Drive and can be expanded to full screen for review
- ▶ Measurement results are displayed in the side panel and can be exported and saved on the USB Flash Drive
- > Multiple measurement tools such as lines, parallel lines, circles and polygons (plotted with up to 10 points) are available in the Manual tab

* Note: Aven recommends that you use a detented lens system or a microscope with click stops for accurate repeatable measurements.

Imaging & Measurement Software




ezMeasure[®] Software




Measure, Annotate and Analyze with Ease

ezMeasure[®] software allows you to measure, annotate, and analyze your images with just a few mouse clicks. Create written reports that include the raw data, plus the images involved. With ezMeasure[®] you can view realtime live images or screenshots from your saved folder which can be reviewed, replayed, and anaylzed. Recent projects are easily accessible with thumbprint menu.




Capture High Quality Images

Create enhanced still photos or record a live video stream for play back.



Simultaneous Live Views

Use two cameras on same work station for side by side live views.




Grid Feature

Locate and compare with ease using multiple grid views.




Customize the Layout

Set the layout to your personal preferences and save your unique settings for future use.



Measurement Tools

- Set the image pixels to real units eg. mm or inches.
- Record and save multiple calibration settings.
- Measure the distances between different points, or edges.



Text Button

Allows annotations directly onto the screen. The user has the ability to adjust the size and the appearance of the text.

Additional Features

- Fill Mode Tool determines the image size: Fit-to-Fill the entire viewing area, Zoomed in, or Preserve the Original aspect ratio.
- ► Location Button provides a cursor for the X,Y,Z-axis coordinates. Moving the Cursor with the mouse updates the coordinates.
- And many many more ...

Product ID	Description
26100-406	ezMeasure [®] Software



Fiber Optic Illumination

ProLux LED Fiber

- Optic Illuminator
- Accepts Virtually any Light Guide with **Quick Change Adapters**
- Advanced Heat Pipe Technology Using Metal Core PCB's
- Higher Brightness, Better Color, Longer Life, Half the Energy Consumption and **Reduced Ownership Costs**
- Linear Light Intensity Control with **Continuous Dimming**
- 26200A-300 Maintenance Free LEDs Have a Minimum Lifetime of 25,000 Hours

Product ID Description 26200A-300 ProLux LED Fiber Optic Illuminator

Dual Pipe Light Guide

- High quality fiber
- Large fiber bundle assures maximum light transmission
- Obedient "stay-up" Sheathing for accurate positioning
- Focusable lens on each pipe for individual light control

Product ID	Description
26200A-523	Dual Pipe Light Guide

Fiber Optic Are Backlight - 4 x 4

- Ideal for high co images
- Highly diffuse ev Sleek, slim desig
- mounting in tigh

Dual Pipe Light Guide	
ea	
4 in	
ontrast silhoutted	
ven light distribution	
gn provides versitility for	Statistic Concession of the second state
ht space	26200A-532

Product ID	Description
26200A-532	Fiber Optic Area Backlight - 4 x 4 in



Fiber Optic Ring Light

- High quality glass fiber Provides 360° shadow free
- illumination Large fiber bundle ensures maximum
- light transmission
- Accepts polarizers
- Comes with standard 15.875mm (5/8") adapter
- Inner diameter 58.674mm (2.31")

Product ID	Description
26200A-402	Fiber Optic Ring Light

Ring Light - Video Lenses

- High quality fiber
- Provides 360° shadow free illumination
- Large fiber bundle ensures maximum light transmission
- Comes with standard 15.875mm (5/8") adapter
- Inner diameter 28.58mm (1.125")
- Designed for use with Video Lenses



26200A-403

Product ID	Description
26200A-403	Ring Light - Video Lenses

Polarizer for Fiber Optic **Ring Lights**

- Helps reduce glare
- Analyzer sits in Counterbore
- Low profile does
- inhibit placement of lens or object viewed



Product ID Description 26200A-402F Polarizer for Fiber Optic Ring Light

Illumination for Microscopy & Video Inspection

Aven offers a variety of lighting options. Ecofriendly white LED ring lights are designed to be used with standard microscopes and video lenses providing a stable bright light at a very low temperature. Fiber optic illuminators are often referred to as "cold light" illuminators because they provide high intensity focused light without the heat typically associated with high intensity lamps. Additional options include a ring light with polarizer for shiny surfaces as well as diffuse axial LED illuminator for specular & shiny surfaces.



26200A-402

	\frown	
\mathcal{M}	()	
、 ""		

26200A-523

LED Illumination

Product ID

26200B-220

Product ID

26200B-207

parts

►

►

Focus Mount

Diffuse Axial LED Illuminator

- Evenly illuminates flat and shiny surfaces
- Enhances scribed, indented or embossed features
- Creates contrast between specular, diffuse and/ or absorptive surfaces
- Diminish visibility of clear overcoats or coverings
- Ideal for electronic component inspection

Description

Integrated LED ring light with focus mount

Eliminates chance of LED ring becoming

Description

Ring Light LED with Polarizer

Polarizer with Analyzer is ideal for

illuminating shiny or highly reflective

Ring Light LED with Integrated

with coarse and fine focus

loose from the microscope

Increases working distance

double arm boom stands*

Diffuse Axial LED Illuminator



Pro Series 40 LED Rina Light

- 40 powerful high precision aligned LEDs (white daylight)
- 4 quadrant controller and auto voltage sensing power supply
- Machined aluminum alloy housing for durability
- Fully adjustable dimming control
- 360° shadow free illumination



26200B-217

Product ID Description 26200B-217 Pro Series 40 LED Ring Light

LED Ring Light w/Brightness and Sector Control

- 60 High Intensity LED Lights
- 7 Step Brightness Control
- 4 sectors and each can be controlled independently
- Flicker Free
- No color change with temperature



Product ID Description

26200B-211 LED Ring Light w/Brightness and Sector Control

LED Ring Light w/Brightness and Sector Control

- 72 High Performance LED Lights
- **Continuous Brightness Control**
- 4 sectors and each can be controlled
- independently Flicker Free
- No color change with temperature

26200B-212

- LED lights are flicker free, energy efficient and ecofriendly
- 26200B-214
- Operates at a low temperature and does not change color over time
- Inner diameter is 70mm (2.75") with three thumb screws for easy mounting

Product ID	Description
26200B-214	Ring Light LED with Polarizer

Ring Light LED with Integrated Focus Mount

Ring Light LED Triple Color

- 120 LEDs, 40 White, 40 Blue and 40 Red
- 7 Step Brightness Control
- Flicker Free
- No color change with temperature
- Energy efficient and eco friendly



26200B-213

Product ID	Description
26200B-213	Ring Light LED Triple Color

* Note: When used with articulating stand, single arm boom stand, or double arm boom stand, an arbor (26800B-521) is required for mounting.

Product ID	Description
26200B-212	LED Ring Light w/Brightness and Sector Control

Ring Light Adapater

- Allows for secure mounting of ring lights to DSZ, NSW and SPZ Series Microscopes
- Screws onto bottom of microscope body

, 1		I	
26800B-460			

Product ID	Description
26800B-460	Ring Light Adapater

Protective Lens Cover

- Glass fitted inside metal ring with threaded screw
- Mounts to bottom of microscope body
- Useful when soldering under the microscope
- Protects fumes from damaging the microscope lenses

26800B-465

Product ID	Description
26800B-465	Protective Lens Cover

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com





Stands & Focus Mounts

Single Arm Boom Stand w/Heavy Metal Base

- ► Base dimensions: 285 x 260 x 18mm (11.22" x 10.23" x 0.71")
- Vertical post length: 384mm (15.12")
- Heavy base provides excellent stability
- Allows positioning of microscopes over large area
- Posts are highly polished for smooth operation



Base dimensions: 210 x 278 x 25mm (8.26" x 10.94" x 0.98")

Vertical post length: 255mm (10")

Pole Stand with Focus Mount

- Includes rack & pinion focus mount with fine focus adjustment
- Frosted, Black & White Stage Plates
- Safety clamp included



26800B-510

26800B-508

Product ID Description 26800B-509

Pole Stand with Focus Mount

Pole Stand with Focus Mount with LED Illumination Top and Bottom

- Base dimensions: 210 x 278 x 40mm (8.26" x 10.94" x 1.57")
- Vertical post length: 255mm (10")
- Includes rack & pinion focus mount with fine focus adjustment
- Top & Bottom LED illumination with dimmer control
- Frosted, Black & White Stage Plates
- Safety clamp included

Product ID Description

26800B-510 Pole Stand with Focus Mount with LED Illumination Top and Bottom

Track Stand with Focus Mount with LED Illumination Top and Bottom

- Base dimensions: 210 x 278 x 40mm (8.26" x 10.94" x 1.57")
- Tracking range: 245mm (9.65")
- Light weight compact track stand
- Comes with rack & pinion focus mount with fine focus adjustment
- Top & Bottom LED illumination with dimmer control
- Frosted, Black & White Stage Plates


Jeschption	Product ID	Description
Double Arm Boom Stand w/Heavy Metal Base	26800B-508	Track Stand with Focus Mount with LED Illumination Top and Bottom
oom Stand v Clamp	Pole Stand w	/ith Focus Mount and
ngth: 384mm (15.12") nent of a ball bearing slide allows easy nicroscope over object being viewed lamp provides stability and saves bench	 Base dimension Vertical post I Light weight of Comes with rate 	ons: 220 x 284 x 15mm (8.6" x 11" x 0.6") ength: 255mm (10") compact stand ack & pinion focus mount 26800B-512 nd fine adjustment knobs
ing of microscopes over large area		D ring light with dimmer control

26800B-534

26800B-525

Product ID	Description
26800B-512	Pole Stand with Focus Mount and LED Illumination

Note: Pole stands are not suitable for SPZ Series microscopes with 0.5x lens as vertical post is not long enough to accommodate the working distance.



Single Arm Boom Stand w/Heavy Metal Base

Single Arm Boom Stand w/Heavy Duty Clamp

- Vertical post length: 384mm (15.12")
- Smooth movement of a ball bearing slide allows easy positioning of microscope over object being viewed
- Heavy duty C Clamp provides stability and saves bench space
- Allows positioning of microscopes over large area

Product ID Description

26800B-525 Single Arm Boom Stand w/Heavy Duty Clamp

Double Arm Boom Stand

w/Heavy Metal Base

- Base dimensions: 285 x 260 x 18mm (11.22" x 10.23" x 0.71")
- Vertical post length: 384mm (15.12")
- Heavy Base couples with ball bearing slide allows for easy positioning of the microscope
- 605mm height available with extension post

Product ID De 26800B-534 Do

Double Arm Bo w/Heavy Duty

- Vertical post leng
- Smooth moveme positioning of mi
- Heavy duty C Cla space
- Allows positionir

		26800B-536
Product ID	Description	
26800B-536	Double Arm Boom Stand w/Heavy Duty Clamp	

Note: Single & Double Arm Boom Stands require either a Focus Mount (26800B-517) with tiltable arbor (26800B-521) or E-Arm Focus Mount (26800B-518).

Stands & Focus Mounts

Diffuser for Glare Reduction

- ► Helps reduce glare from shiny objects
- Made from durable plastic material ►
- Ideal for observing solder joints, metallic parts or shiny surfaces
- Designed for use with 26800B-512 (Stand PLED) and 26200B-207 (Ring Light with Focus Mount)

26200B-209DF2

Gemology Stand with Fluorescent and Halogen Illumination

- ► Independently controllable fluorescent front light provides even shadow free illumination
- Dimmable halogen transmitted and pipe light with separate controls
- 2 post positioning, right and left for adjustable gem tweezers
- Adjustable iris in dark field attachment
- Stand can be inclined from 0 to 10 degree

26800B-507

Product ID	Description		
26200B-209DF2	Diffuser for Glare Reduction	Product ID	Description
Pole Stand	with Focus Mount	26800B-507	Gemology Stand with Fluorescent and Halogen Illumination
 (8.66" x 11.1 Vertical pos Light weigh Ideal for exa Saves bench Includes with 	it length: 250mm (10") at compact stand amining small parts 26800B-511	 Base dimer Vertical post Aluminum 10 tapped I UNC bolt at Vertical post to which both at 	ty Post Stand nsion: 279 x 330 x 12.7mm (10.98" x 13" x 0.5") st length: 406mm (15.98") powder coated base holes for mounting x-y stages nd safety clamp included st will accept focus mount (26800B-517) odies SPZH, SPZ series, DSZ series and NSW be mounted
Product ID	Description		
26800B-511	Pole Stand with Focus Mount	Product ID	Description
		26800B-570	Heavy Duty Post Stand
 18" Flexible Flex to any p Includes 360 1/4" screw r 		 Precision Rate Tension Co 74mm dian 	ine Focus Adjustments ack & Pinion Mechanism with ntrol 26800B-517
Product ID	Description	 Will accept 	our SPZH, SPZ, DSZ and NSW series microscopes
26800B-557	18" FlexArm with 2" Table Clamp		
26800B-558	18" FlexArm with 3" Magnetic Base	Product ID	Description
Standard A	rticulating	26800B-517	Focus Mount
microscope	ved out of way when not 26800B-560	 Focus Adju 50mm focudirection 74mm dian 	on Mechanism with Coarse Istment Ising distance in vertical 26800B-518
26800B-560	Standard Articulating Arm Stand		
LCD Monito	or Mount roductivity with expanded workspace	Product ID 26800B-518	Description E-Arm Focus Mount
 Arms have 3 +15 degree Made of hig Holds Wides Heavy duty 	gonomic comfort 360 degree swivel and rotation and -15 to tilt adjustment gh grade steel and aluminum screen Display up to 27" "C" clamp mounts to desktop providing excellent	of boom sta stands Allows tiltir	o extend the working range ands and articulating arm ng of microscope bodies to 26800B-521
stability	26700-410	increase op	perator comfort
stability Product ID	26700-410 Description		
		Product ID 26800B-521	Description Tiltable Arbor

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com





Gliding Stages & Eyepieces

Microscope Eyepiece 10x with 10:100mm Scale

- 10x magnification power
- ► 10:100mm scale reticle
- Excellent for measurement
- High Eye-point Design
- 20mm Super Wide Field of View



Product ID	Description
26800B-455	Microscope Eyepiece 10x with 10:100mm scale

Microscope Eyepiece 10x with 5:100mm scale

Microscope Eyepiece 10x with 5:100mm Scale

- 10x magnification power
- ► 5:100mm scale reticle
- Excellent for measurement

Product ID

26800B-456

Product ID

- High Eye-point Design
- 20mm Super Wide Field of View

Description



Gliding Stage w/95mm Ring Mount

- Smooth motion for precise specimen placement
- Anodized black metal and glass components
- Glass top with interior Y and exterior X unit measurements
- Coaxial dial system for easy and accurate operation
- Useful for dissection and circuit board inspection

Product ID	Description
26800B-477	Gliding Stage w/95mm Ring Mount

Gliding Stage-Large

- Precision-machined bevel-cut gearing
- Fine, controlled movement along the entire 300x200mm travel in the X-Y axis
- Black anodized finish
- Ideal for smooth and controlled movement of parts underneath a microscope

Product ID	Description		
26800B-478	Gliding Stage-Large		



26800B-478

26800B-477

with 20x20 0.5mm Squares 10x magnification power

Microscope Eyepiece 10x

- Tox magnification power
 20x20_0 Emm squares ret
- 20x20, 0.5mm squares reticle
 Excellent for measurement
- High Eye-point Design
- 20mm Super Wide Field of View



26800B-457 Microscope Eyepiece 10x with 20x20 0.5mm Squares

Description

Microscope Eyepiece 10x with 10x10 1mm Squares

- 10x magnification power
- 10x10, 1mm squares reticle
- Excellent for measurement
- High Eye-point Design
- 20mm Super Wide Field of View



 Product ID
 Description

 26800B-458
 Microscope Eyepiece 10x with 10x10 1mm Squares

Microscope Eyepiece 10x with 10:100mm Scale Cross Hair

- 10x magnification power
- 10:100mm scale cross hair reticle
- Excellent for measurement
- High Eye-point Design
- 20mm Super Wide Field of View

		26800B-459
Product ID	Description	
26800B-459	Microscope Eyepiece 10x with 10:100mm Scale Cross Hair	

Eyepieces & Auxiliary Lenses



Magnifiers

AVEN

Inspection Loupes, Magnifiers & Magniloupes

Swing Out Inspection Loupe 10x Hex

- Triplet lens system corrected for spherical and chromatic aberrations
- Produces a sharp and distortion free image
- 10x magnification

Product ID

Product ID

Product ID

Magnifier 10x

close-up

photography

illuminate the object

Powerful 10x magnification

26012

26011



26010

26011

26012

26010 Swing Out Inspection Loupe 10x Hex

Description

Swing Quit Inspection Loupe 19x

- Made from optical glass
- 10x eye loupe with 1" working distance
 Chrome finish loupe easily folds up to protect lens



Description Swing Out Inspection Loupe 10x

Swing Out Inspection Loupe 20x

- Distortion free, three piece, bonded lens
- Made from optical glass
- 20x eye loupe with 1/2" working distance

Description

Swing Out Inspection Loupe 20x

Pre-focused dual lenses allow examination of objects

Ideal for model makers, stamp and coin collectors, and

Transparent acrylic base permits ambient light to

- Chrome finish loupe easily folds up to protect lens
- Includes leather carrying case

Magniloupe w/Cushion

- Lightweight glass lens magnifier
- Soft rubber cushion provides comfor during use
- Powerful magnification
- Excellent for close inspection of small parts
 Ideal for use by jewelers, photographers, watchmakers, printers, and quality control inspectors

26041

Product ID	Description
26041	8x Magniloupe w/Cushion
26042	7x Magniloupe w/Cushion
26043	4.5x MagniLoupe w/Cushion

Eye Loupe 10x

- Lightweight & sturdy glass lens magnifier
- Powerful 10x magnification
- Excellent for close inspection of small parts
- Rests comfortably in the eye socket
- Ideal for use by jewelers, photographers, watchmakers, printers, and quality control inspectors



Product ID	Description
26034	Eye Loupe 10x

Eye Loupe 10x with LED Light

- Lightweight glass lens magnifier
- Powerful 10x magnification
- Excellent for close inspection of small parts
- Adjustable, bright LED light
- Ideal for use by jewelers, photographers, watchmakers, printers, and quality control inspectors

26034-LED

photography		26051		
Product ID	Description		Product ID	Description
26051	Magnifier 10x		26034-LED	Eye Loupe 10x with LED Light

User Pairs Mighty Scope with a Low-Tech Companion

Performance matters more than size, as our popular Mighty Scope Digital Microscope shows.

We and our sales representatives hear manufacturing engineers praise the handheld scope's convenience for inline inspection, image and video capture, and monitor viewing via USB or the Wi-Fi model. The latest field report comes from a user who called to describe how he previously used an eye loupe with a scale-measuring reticle for parts check to assure that any defects are within tolerances.

Cleverly, he now pairs a newly purchased Mighty Scope 5M with his original tool to combine the loupe's scale with our instrument for a close-up, measurable view illuminated with six LEDs. The Mighty Scope can capture that combined image for reference and sharing.







Magnifiers

Eye Loupes & Pocket Microscopes



Pen Type Microscope 25x w/LED Light

- Perfect "pen-type" microscope with 25x magnification
- Includes pocket clip and a bright LED light
- Beveled opening to gather and focus light
- Provides distortion free inverted image ►
- Ideal for inspection in electronics, medical, printing, and jewelry industries

Description

Product ID

26800C-550

Product ID

26800C-551



Eyepiece has scale with 0.1mm graduation and a

- measurement range of 4mm Operates on two AA batteries (not included)
- Useful for engineers, tool makers and quality control inspectors

Pocket Microscope 40x w/ illumination

Perfect carry-with microscope with magnification of 40x

26800C-534

Product ID Description 26800C-534 Pocket Microscope 40x w/illumination

Pocket Microscope 40x w/ illumination

- Perfect carry-with microscope with magnification of 40x
- Eyepiece has scale with 0.05mm graduation and a measurement range of 2mm
- Operates on three AA batteries (not included)
- Useful for engineers, tool makers and quality control inspectors

26800C-541

Product ID

26800C-541 Pocket Microscope 40x with LED illumination

Pocket Microscope 60-100x

Description


w/ LED illumination

- Perfect carry-with microscope with magnification of 60-100x
- Focus wheel allows you to quickly focus onto the object being viewed
- Operates on three LR1130 Button Cell batteries (not included)
- Useful for engineers, tool makers and quality control inspectors

26800C-542

Product ID Description

26800C-542 Pocket Microscope 60-100x with LED illumination



Etched into the eyepiece with graduations of 0.05mm 26800C-552 & 26800C-553

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Pen Type Microscope 25x w/LED Light

Perfect "pen-type" microscope with 50x magnification

Pen Type Microscope 50x w/LED Light

Includes pocket clip and a bright LED light

Beveled opening to gather and focus light

Provides distortion free inverted image Ideal for inspection in electronics, medical,

printing, and jewelry industries

Pen Type Microscope 50x w/LED Light Pen Type Microscope 25x w/LED Light & Scale

- Perfect "pen-type" microscope with 25x magnification and ► includes reticle scale
- Includes pocket clip and a bright LED light

Description

- Beveled opening to gather and focus light
- Provides distortion free inverted image
- Ideal for inspection in electronics, medical, printing, and jewelry industries

26800C-552

26800C-551

Product ID	Description
26800C-552	Pen Type Microscope 25x w/LED Light & Scale

Pen Type Microscope 50x w/LED Light & Scale

- Perfect "pen-type" microscope with 50x magnification and ► includes reticle scale
- Includes pocket clip and a bright LED light
- Beveled opening to gather and focus light
- Provides distortion free inverted image
- Ideal for inspection in electronics, medical, printing, and jewelry industries

26800C-553

Product ID	Description
26800C-553	Pen Type Microscope 50x w/LED Light & Scale

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com





Magnifiers

Headband Magnifiers

OptiVisor Headband Magnifiers

- Optical glass prismatic lenses ► ground and polished to precision optical standards
- Adjustable pivots allow the visor to be tilted out of the way when not needed and at your fingertips when you need magnification
- Adjusts to fit all head sizes
- High impact visor provides a tough, durable, always-new appearance
- Padded orthopedic felt adds to comfort

26101

Product ID Description 26101 OptiVisor Headband Magnifier - 1.5x 26102 OptiVisor Headband Magnifier - 1.75x 26103 OptiVisor Headband Magnifier - 2x 26104 OptiVisor Headband Magnifier - 2.5x 26105 OptiVisor Headband Magnifier - 2.75x 26106 OptiVisor Headband Magnifier - 3.5x

Replacement Lenses

- 1.5x 3.5x Replacement Lenses
- Optical glass prismatic lenses ground and polished to precision optical standards
- **Replacement Lens for Optivisor** Headband Magnifier



26107

Product ID	Description
26107	Replacement Lens #2 - 1.5x
26108	Replacement Lens #3 - 1.75x
26109	Replacement Lens #4 - 2x
26110	Replacement Lens #5 - 2.5x
26111	Replacement Lens #7 - 2.75x
26112	Replacement Lens #10 - 3.5x

Auxiliary Lens - 2.5x

- Attaches to the front of Optivisor headband magnifier
- Mounts on one side of the lens plate to provides an additional 2-1/2X magnification
- Pivots out of the way when not needed

Product ID Description 26113 Auxiliary Lens - 2.5x



Headband Magnifier with LED Light

- Excellent for quality control inspection
- Removable LED lamp can be used as a free standing light source
- Includes four clip-on lenses (1.5x, 2x, 2.5x, and 3x)
- Headband is adjustable to fit all sizes
- Ideal for close up inspection of small parts

Product ID	Description
26221	Headband Magnifier with LED Light

OptiSight Headband Magnifier

- Visor can be worn over
- Prescription or safety glasses
- Durable high-strength plastic
- Interchangeable lenses 1.75x, 2x, 2.5x
- Visor design shields out unwanted glare
- Precision optical grade acrylic prismatic lens.



26221

 Precision optical grade acrylic prismatic lens. 2622 		26224
Product ID	Description	
26224	OptiSight Headband Magnifier	

OptiVue Headband Magnifier - 2.5x

- Provides hands-free magnification
- Visor tilts up for normal viewing
- Includes 2.5x crystal clear acrylic lens
- Adjustable headband fits any size



Product ID	Description
26225	OptiVue Headband Magnifier - 2.5x

Register online to receive updates on the newest products and for the latest specials from Aven.

Magnifying Lamps

ProVue Lamps & Accessories



ProVue SuperSlim Magnifying Lamp

- Available in two configurations: 5-Diopter (2.25x) and 8-Diopter (3x ► Magnifcation)
- 5" crystal clear glass lens for 360° distortion-free viewing
- 36" spring balanced arm stays set in any position
- Heavy-duty mounting clamp with 63.5mm (2.5") opening
- Fluorescent model features 22 Watt bulb operating at 6400k

26501-LED

- LED models feature 60 high powered energy efficient SMD LEDs lights that provide shadow free illumination LED lights are rated for over 20,000 hours of use
- Unit operates at 115 VAC

Product ID	Description	Lighting	Magnification
26501-SIV	ProVue Magnifying Lamp	22W fluorescent	2.25x (5 diopter)
26501-LED	ProVue LED Magnifying Lamp	60 SMD LED	2.25x (5 diopter)
26501-LED-8D	ProVue LED Magnifying Lamp	60 SMD LED	3x (3 diopter)

ProVue Magnifying Lamp LED with **Rolling Stand**

Same features as our 26501-LED except mounted on our heavy duty floor stand with casters

26501-LED-STN



22-watt Replacement Bulb

- Replacement bulb for 26501-SIV and 26501-DSG
- Universal standard fluorescent light
- Energy efficient
- Rated lifetime of 12,000 hours

26501-B22

Product ID	Description	
26501-B22	22-watt Replacement Bulb	
		12.2

ProVue Deluxe LED Magnifying Lamp

- Energy efficient 72 SMD LED board
- 5 Diopter Glass Lens
- 36" Frinction Arms. No springs, no pinch hazards Beautifully constructed aluminium design
- Built-in brightness control
- 3 locking joints. Stays in place in any position
- Minimum lifetime of 20,000 hours

26501-DSG-LED

Product ID	Description
26501-DSG-LED	ProVue Deluxe LED Magnifying Lamp

Auxiliary Lens - 3-Diopter (1.75x)

- Provides additional magnification
- 3.875" 1.75x (3 diopter) auxiliary lens
- Designed to attach to bottom of Aven 26501-DSG magnifying lamp

Deside at 1D	Development			
Product ID	Description	De l'Allo	Development	
	Deal/via Manaifria a Lanza LED with Dalling Stand	Product ID	Description	
26501-LED-STN	ProVue Magnifying Lamp LED with Rolling Stand	26501 412		
		26501-AL3	Auxiliary Lens - 3-Diopter (1.75x)	

Swing-Away Lens - 5-Diopter (2.25x)

- Provides additional magnification
- 5 diopter (2.25x)
- Works with all magnifying lamps

26501-SLA

Product ID	Description
26501-SLA	Swing-Away Lens - 5-Diopter (2.25x)

ProVue Replacement Clamp

- Heavy-duty metal mounting clamp with 63.5mm (2.5") opening
- Mounts easily to desk or table top
- Fits ProVue magnifying lamps

26501-RC

Product ID	Description
26501-RC	ProVue Replacement Clamp

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

26501-AL3



ProVue Slim & Touch LED Magnifying Lamps

ProVue Touch Magnifying Lamp w/ LED Illumination

- 54 powerful energy saving white SMD LEDs provide shadow free illumination
- SMD technology ensures reliability and long life
- Large 7" crystal clear 1.75x (3 diopter) glass lens with protective cover
- Touch sensitive 3-stage on-off switch for controlling light intensity
- Rugged ABS plastic housing attached to a 35" industrial grade spring balance arm for precise positioning
- Lens can be easily removed and replaced when necessary
- Built-in metal grips for quick and easy positioning
- Heavy duty metal mounting clamp with 89mm (3.5") opening
- LED lights are rated for over 20,000 hours of use
- Unit operates at 115 to 240wv VAC

ProVue Touch White & UV LED Magnifying Lamp

- Dual lighting provides 54 powerful energy saving white SMD LED lights and 48 SMD UV LED lights (400nm)
- UV lighting ideal for forensic analysis, counterfit inspection and detection of fluoresces in adhesives, laminates and conformal coating
- SMD technology ensures reliability and long life
- Large 7" crystal clear 1.75x (3 diopter) glass lens with protective cover
- Touch sensitive 3-stage on-off switch for controlling light intensity
- Rugged ABS plastic housing attached to a 35" industrial grade spring balance arm for precise positioning
- Lens can be easily removed and replaced when necessary
- Built-in metal grips for quick and easy positioning
- Heavy duty metal mounting clamp with 89mm (3.5") opening
- LED lights are rated for over 20,000 hours of use
- Unit operates at 115 to 240 VAC

Product ID	Description	Product ID	Description
26508-LED	ProVue Slim LED Magnifying Lamp	26508-LDV	ProVue Touch White & UV LED Magnifying Lamp

ProVue SuperSlim

Magnifying Lamp

- Super-Slim Modern Design
- Spring arm stays set in any position
- High intensity energy saving LEDs
- Cool operating temperature
- Exceptionally long LED element life (minimum 20,000 hours)
- Ideal for assembly, workshop or inspection applications
- Mounting Clamp allows for easy attachment to desk and bench tops



26508-I FD

26501-LED

Product ID	Description
26501-LED	ProVue SuperSlim LED 5 Diopter (2.25x)
26501-LED-8D	ProVue SuperSlim LED 8 Diopter (3x)
26501-SIV	ProVue SuperSlim Fluorescent 5 Diopter (2.25x)

Register online to receive updates on the newest products and for the latest specials from Aven.

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com

ProVue Deluxe Magnifying Lamp

- Durable aluminum construction
- Friction arm stays set in any position
- 5" 5 diopter round glass lens (2.25x Magnification)
- High intensity energy saving LEDs
- Cool operating temperature
 Exceptionally long LED element life
- Exceptionally long LED element life (minimum 20,000 hours)
- Ideal for assembly, workshop or inspection applications
- Mounting Clamp allows for easy attachment to desk and bench tops, or mount directly to your work surface.



26508-LDV

Product ID Description 26501-DSG-LED ProVue Deluxe LED 5 Diopter (2.25x)

OptiVue 5-Diopter LED Magnification Desk Lamp

- ▶ 11" flexible gooseneck arm
- ▶ 4" 5-Diopter glass lens

Product ID

26507-XL5

36 High intensity energy saving SMD LEDs

Description

11" flexible gooseneck arm

(

OptiVue 5-Diopter LED Magnification Desk Lamp

Magnifying Lamps

Mighty Vue Lamps & Accessories



Mighty Vue Magnifying Lamp-LED

- Large 7" x 6" lens, 3-diopter
- Durable ESD safe mar-resistant plastic housing
- 36" spring balanced arm stays put in any position
- Heavy-duty ESD safe metal mounting clamp with 63.5mm (2.5") opening
- plastic
- Color temperature ranges from 3500K-6500K
- Feature 60 high powered energy efficient SMD LEDs lights (30 per color
- temperature) that provide shadow free illumination
- LED lights are rated for over 20,000 hours of use

Product ID	Description
26505-LED-XL3	Mighty Vue Magnifying Lamp-LED

Mighty Vue Pro Magnifying Lamp

- Large 7" x 6" lens
- Durable ESD safe mar-resistant plastic housing
- 36" spring balanced arm stays put in any position
- Heavy-duty ESD safe metal mounting clamp with 63.5mm (2.5") opening
- Color temperature ranges from 3500K-6500K
- Feature 60 high powered energy efficient SMD LEDs lights (30 per color temperature) that provide shadow free illumination
- LED lights are rated for over 20,000 hours of use
- Features Brightness Adjustment (max: 1100lm)
- Unit operates at 115 VAC

 Product ID
 Description
 Lighting
 Magnification

 26505-ESL-XL5
 Mighty Vue Magnifying Lamp ESD Safe (black)
 60 SMD LED
 2.25x (5 diopter)

Mighty Vue Pro Magnifying Lamp

- Durable aluminium construction
- Touch-sensitve brightness control with 5 color-coded settings
- ▶ 36 friction arm stays set in any position
- 7 5 diopter round glass lens (2.25x Magnification)
- High intensity energy saving LEDs
- Cool operating temperature
- Exceptionally long LED element life (minimum 20,000 hours)
- Ideal for assembly, workshop or inspection applications
- Mounting Clamp allows for easy attachment to desk and bench tops, or mount directly to your work surface.

Product ID	Description	Lighting	Magnification
26505-DSG-LED	Mighty Vue Deluxe LED Magnifying Lamp	72 SMD LED	2.25x (5 diopter)

9 Watt Replacement Bulb

- ▶ 9 Watt Replacement bulb designed for Mighty Vue Magnifiers
- Color temperature 6400K
- Energy efficient universal standard fluorescent light

26505-B09

26505-RC

26505-RC-ESD

Product ID	Description	
26505-B09	9 Watt Replacement Bulb	

Replacement Clamp - 26505-SIV

- Replacement Heavy-duty metal mounting clamp with 63.5mm (2.5") opening
- Mounts easily to desk or table top

Product ID

26505-RC

Ρ

26

 Fits Mighty Vue 26505-SIV and 26505-LED magnifying lamps

Description

Replacement Clamp - 26505-ESD

- Replacement Heavy-duty metal mounting clamp with 63.5mm (2.5") opening
- Mounts easily to desk or table top
- Fits Mighty Vue 26505-ESD and 25505-ESD-5D magnifying lamps

Replacement Clamp - 26505-SIV

Product ID	Description	
26505-RC-ESD	Replacement Clamp - 26505-ESD	

Floor Stand Heavy Duty with Castors

- ► 5 full swivel castors for easy mobility
- Designed for durability
- Easy to clean, no maintenance required
- Provides full mobility for magnifying lamp applications in beauty salons, the medical field, electronics repair, dental clinics, industrial inspection, scientific research laboratories and even at home
- Works with ProVue SuperSlim magnifying lamps









26505-ESL-XL5

Work Lights

Machine Tool LED Task Lamps & Accessories



Sirrus Magnetic Base

26520-MB

Alignment Tools & Screwdrivers

Ceramic Alignment Screwdrivers

- Anti Static, non magnetic, non inductive heat resistant ceramic tips
- Heat resistant up to 1292°F (700°C)
- Blades made from Zirconia ceramic
- Outlasts metal or plastic tip tools
- No eddy current loss in high frequency

Product ID	Description	Blade	Tip Size
13220	Ceramic Alignment Screwdriver	Phillips	PH1.7
13221	Ceramic Alignment Screwdriver	Slotted	1.3 mm
13222	Ceramic Alignment Screwdriver	Slotted	2.6mm
13224	Ceramic Alignment Screwdriver	Slotted	0.9mm
13225	Ceramic Alignment Screwdriver	Slotted	1.8mm
13230	Ceramic Alignment Screwdriver 4-in-1	Phillips & Slotted	Phillips 0 & 1.7 Slotted 1.8 & 0.9mm

Ceramic Alignment Screwdriver - 6-Piece Set

- Anti Static, non magnetic, non inductive heat ► resistant ceramic tips
- Heat resistant up to 1292°F (700°C)
- Blades made from Zirconia ceramic
- Outlasts metal or plastic tip tools
- No eddy current loss in high frequency

Description



13016

13225

13231 Ceramic Alignment Screwdriver - 6-Piece Set

9-Piece Anti-Static Alignment Tool Kit

Anti-Static

Product ID

- Designed for adjusting and aligning conventional components
- Includes 9 popular alignment tools

Product ID Description

13016 9-Piece Anti-Static Alignment Tool Kit

Precision Screwdriver - 8-Piece Set

- Ergonomically designed handle with swivel head cap for ► precise control and comfort
- Two component handle provides soft touch and non slip surface and is oil and solvent resistant
- Blade made from high grade alloy steel
- Supplied in a handy plastic case for secure storage

13715

Description Product ID 13715 Precision Screwdriver - 8-Piece Set

Precision Screwdriver - 7-Piece Set

- Chrome Vanadium steel with satin finish and black tips
- Duplex Component handle is designed for rapid rotation and control
- Fast turning swivel caps
- Imprinted sizes on handle for easy selection
- 50mm Blade Length



13940

Product ID	Description
13940	Precision Screwdriver - 7-Piece Set

Aven Precision Screwdrivers

- Precisely machined hardened black tips for durability and exact fit
- Screwdriver blades manufactured from chrome-molybdenum steel for extra strength
- Ergonomically designed bi-component handle with swivel cap for extra comfort and grip

Product ID	Description	Blade	Size	Length	Overall Length
13901	Precision Screwdriver	Slotted	1.6mm	50mm	150mm
13902	Precision Screwdriver	Slotted	2.0mm	50mm	150mm
13903	Precision Screwdriver	Slotted	2.4mm	50mm	150mm
13904	Precision Screwdriver	Slotted	3.0mm	50mm	150mm
13906	Precision Screwdriver	Slotted	3.0mm	100mm	200mm
13910	Precision Screwdriver	Phillips	No. 000	50mm	150mm
13911	Precision Screwdriver	Phillips	No. 00	50mm	150mm
13913	Precision Screwdriver	Phillips	No. 1	50mm	150mm
13915	Precision Screwdriver	Phillips	No. 1	100mm	200mm
13921	Precision Screwdriver	Torx	Т6	50mm	150mm
13923	Precision Screwdriver	Torx	Т8	50mm	150mm
13930	Precision Nutdriver	-	M3.0	72mm	172mm
13932	Precision Nutdriver	-	M4.0	72mm	172mm
13933	Precision Nutdriver	-	M4.5	72mm	172mm
13935	Precision Nutdriver	-	M5.5	72mm	172mm

Precision Screwdriver - 6-Piece Set

- Screwdriver features Rotative Caps Two-component construction for soft touch and non-slip surface
- Environmentally friendly and recyclable materials
- Heat treated high grade allow steel blades with blackened tips

Product ID Description

13722 Precision Screwdriver - 6-Piece Set

8 Piece Reversible Screwdriver Set

- Neo Microtip screwdriver handle features rotating cap Two-component construction for soft touch and non-
- slip surface
 - Made from environmentally friendly and recyclable materials
 - Heat treated high grade alloy steel blades with blackened tips

Product ID Description


13722 Precision Screwdriver - 6-Piece Set

> Register online to receive updates on the newest products and for the latest specials from Aven.

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108



13722



10355

10355-FR

10766

10365



Stainless Steel Wrenches, Cutters & Pliers

Adjustable Wrench - Stainless Steel

- Manufactured from 304 series stainless steel
- Mirror polished to provide excellent rust resistance
- Handle hole for tethering, hanging or storage
- Can be autoclaved to temperatures up to 250 degrees Fahrenheit

Product ID	Description
21190-6	Adjustable Wrench 6" Stainless Steel
21190-8	Adjustable Wrench 8" Stainless Steel
21190-10	Adjustable Wrench 10" Stainless Steel
21190-12	Adjustable Wrench 12" Stainless Steel

Adjustable Wrench - Stainless Steel w/ PVC Grip

- Manufactured from 304 series stainless steel
- Mirror polished to provide excellent
- rust resistance
- Cushion-grip handle
- Handle hole for tethering, hanging or storage

21	190- 1	10G

21187-0516

21187-105

21190-6

Product ID	Description
21190-6G	Adjustable Wrench 6" w/PVC Grip
21190-8G	Adjustable Wrench 8" w/PVC Grip
21190-10G	Adjustable Wrench 10" w/PVC Grip
21190-12G	Adjustable Wrench 12" w/PVC Grip

Combination Wrench - Stainless Steel

- Manufactured from 304 series stainless steel
- Can be autoclaved to temperatures up to 250 degrees Fahrenheit
- Rust resistant, can help eliminate risk of ferrous contamination

Product ID	Description
21187-0516	Combination Wrench Stainless Steel 5/16"
21187-0308	Combination Wrench Stainless Steel 3/8"
21187-0716	Combination Wrench Stainless Steel 7/16"
21187-0102	Combination Wrench Stainless Steel 1/2"
21187-0916	Combination Wrench Stainless Steel 9/16"
21187-0508	Combination Wrench Stainless Steel 5/8"

Combination Wrench - Stainless Steel -

6-Piece Set

- Made from 304 series stainless steel
- Can be autoclaved to temperatures up to 250 degrees Fahrenheit
- Rust resistant, can help eliminate risk of ferrous contamination
- Includes handy roll up plastic pouch

Product ID	Description
21187-105	Combination Wrench Set Stainless Steel 6pc

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Diagonal Cutter - Stainless Steel 6"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- Oval head designed for greater access in confined spaces
 - Beveled cutting edge is hardened for long lasting performance
- Can be autoclaved to temperatures up to 250 degrees Fahrenheit

TIOGUCCID	Description	
10355	Diagonal Cutter - Stainless Steel 6"	
Diagonal Cutter w/Comfort Grip Handles 6"		

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- Oval head designed for greater access in confined spaces
 - Beveled cutting edge is hardened for long lasting performance
- Ergonomically designed grips for extra comfort

Diagonal Cutter w/Comfort Grip Handles 6" Diagonal Cutter "High Leverage" Stainless Steel 7"

Manufactured from 400 series stainless steel

Description

Product ID

10355-ER

Product ID

- Mirror polished to provide excellent rust
- resistance Provides more cutting power than
- general purpose pliers Beveled cutting edge is hardened for long lasting 10356 performance
- Can be autoclaved to temperatures up to 250 degrees Fahrenheit

Diagonal Cutter "High Leverage" Stainless Steel 7" 10356

Flat Nose Parallel Action Pliers 6.75"

Description

- Serrated Jaws with V-Slot for holding wire
- Grip remains consistently parallel along length of jaw when open or closed
- Compound lever action with no spring
- Built-in wire cutter cuts soft wire up to 4mm (0.16")

Product ID Description Flat Nose Parallel Action Pliers 6.75" 10766



- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust
- resistance Slip-resistant tongue and groove design used for grasping and turnina
- Serrated jaws with four adjustable positions
- Can be autoclaved to temperatures up to 250 degrees Fahrenheit

Product ID	Description
10365	Groove Joint Pliers Stainless Steel 9.5"

Stainless Steel Pliers



Combination Pliers Stainless Steel 8"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- Tapered head design allows for greater access in confined spaces
- Designed for gripping and turning round objects such as pipes, rods and pins
- Serrated jaws with machined gripping teeth and wire cutter

Product ID Description

Combination Pliers Stainless Steel 8" 10351

Combination Pliers w/Plastic Grips 8"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- Tapered head design allows for greater access in confined spaces
- Designed for gripping and turning round objects such as pipes, rods and pins
- Serrated jaws with machined gripping teeth and wire cutter

Product ID Description 10351-P

Combination Pliers w/Plastic Handles 8"

Long Nose Pliers Stainless Steel 6"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- Length and slim design are ideal for tight spaces
- Serrated jaws with machined gripping teeth and wire cutter

10360

Description Product ID

10360 Long Nose Pliers Stainless Steel 6"

Long Nose Pliers w/Comfort Grip Handles 6"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- Length and slim design are ideal for tight spaces
- Ergonomically designed grips for extra comfort

10360-ER

Product ID Description 10360-ER Long Nose Pliers w/Comfort Grip Handles 6"

Pliers Set Stainless Steel

- Mirror polished stainless steel provides excellent corrosion resistance
- Packaged in a leatherette roll-up pouch
- Set includes: 6" long-nose pliers, 6" slip-joint pliers, 6" wire-cutting pliers, 9-1/2" groove-joint pliers with flat jaws, and an 8" combination pliers

Description

Pliers Set Stainless Steel



10381

Slip Joint Pliers Stainless Steel 6.5"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- All purpose pliers with serrated jaws, built-in wire cutter and pipe grip



10370

10370-P

10375

10376

10377

Product ID	Description
10370	Slip Joint Pliers Stainless Steel 6.5"

Slip Joint Pliers w/Plastic Grips 6.5"

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent rust resistance
- All purpose pliers with serrated jaws, built-in
- wire cutter and pipe grip
- Plastic grips provide extra comfort

Product ID Description 10370-P Slip Joint Pliers Stainless Steel 6.5"

Locking Pliers Stainless Steel 7"

- Body and springs made from 304 non-magnetic stainless steel
- Jaws are made from 420-series stainless steel
- Fully polished to provide excellent rust resistance
- Smooth gliding locking mechanism enables easy one-handed operation
- Trigger release handles and easy turning pressure adjusting screw

Product ID Description 10375 Locking Pliers Stainless Steel 7"

Locking Pliers Stainless Steel 9"

- Body and springs made from 304 non-magnetic stainless steel
- Jaws are made from 420-series stainless steel

Fully polished to provide excellent rust resistance

Smooth gliding locking mechanism enables easy one-handed operation

Product ID	Description
10376	Locking Pliers Stainless Steel 9"

Locking Pliers, Long Nose, Stainless Steel 6"

- Fully polished stainless steel provides excellent corrosion resistance
- Smooth gliding locking mechanism enables easy one-handed operation
- Long thin nose is ideal for accessing tight spaces
- Trigger release handles and easy turning pressure adjusting screw

Product ID	Description
10377	Locking Pliers, Long Nose, Stainless Steel 6"

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Product ID

10381





Crimping Tools & Scissors

11014

11016

11022

Crimping Tool for Wire Ferrules

- For use with 22 to 6 AWG wire
- Replaceable dies
- Built in ratchet applies correct pressure to ensure a complete crimp
- Durable steel construction and hardened dies to ensure reliability and longevity
- ABS grips make this tool comfortable and easy to use

10178

trimmed 11080

11081

Product ID	Description
10178	Crimping Tool for Wire Ferrules 12 to 22 AWG
10179	Crimping Tool for Wire Ferrules 6 to 10 AWG

2-in-1 Combination Scissor

- Easily trim materials such as nylon fiber, cabtire cord, Kevlar etc.
- Gives you a fine flush cut
- Notched blades prevent the material to be from slipping
- U-types notches on the blade allows you to hold items such as copper wire, cabtire or insulated cords etc. firmly in place
- Stainless Steel with blade hardness of HRC 54

Product ID	Description
11080	2-in-1 Combination Scissor

2-in-1 Heavy-Duty Combination Scissor

- Easily trim materials such as nylon fiber, cabtire cord, Kevlar
- 3mm thick blade gives you a fine flush cut
- Notched blades prevent the material to be trimmed from slipping
- U-types notches on the blade allows you to hold items such as copper wire, cabtire or insulated cords etc. firmly in place
- Stainless Steel with blade hardness of HRC 56-60

		Product ID	Description
oduct ID	Description	11023	8" All Purpose Standard Scissor
081	2-in-1 Heavy-Duty Combination Scissor	L	

5" Electrician Scissor

Pro

- Fully polished stainless steel provides excellent corrosion resistance
- Scraper and file on back edge of the blade
 Notched to strip 23 to 19 AWG wire

11012

Product ID	Description
11012	5" Electrician Scissor

4-1/2" Slim Blade Straight Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- Precision scissor for cutting fine wire and general use
- 1-1/4" durable stainless steel blade

Product ID	Description
11014	4-1/2" Slim Blade Straight Scissor

4-1/2" Precision Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- Fine beaks for precise and delicate work
- 1-3/8" durable stainless steel blade

Product ID	Description
11016	4-1/2" Precision Scissor

7" All Purpose Standard Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- 3-1/4" durable stainless steel blade


Product ID	Description
11022	7" All Purpose Standard Scissor
 Fully polished resistance 	e Standard Scissor I stainless steel provides excellent corrosion e stainless steel blade 11023
Product ID	Description
11023	8" All Purpose Standard Scissor

Register online to receive updates on the newest products and for the latest specials from Aven.

Hemostats & Probes

12201

12001



Stainless Steel Probe 4-piece Set

- Made from 400 series stainless steel
- Sharp tip for precision work around delicate circuits and components
- Set of four contains: Straight, Bent, Curved and Angled Models

Product ID	Description
20210	Stainless Steel Probe 4-piece Set

Alligator Clamp

- Serrated jaws for secure grip
- Angled to provide maximum view
- Stainless steel construction
- Designed to securely retrieve and hold small

Product ID	Description	Jaw Length	Opening
12201	Alligator Clamp 3.5"	0.5"	0.25"
12202	Alligator Clamp 5.5"	0.5"	0.25"

Hemostat - Straight

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent corrosion
- Serrated jaws hold objects firmly without cutting them
- Designed for intricate work in tight
- Ratchet lock in handle allows varying gripping pressure

Product ID	Description	Jaw Length
12001	Hemostat - Straight 3.5in	20mm
12015	Hemostat - Straight 5in	25.4mm
12011	Hemostat - Straight 5in w/Plastic Coated Handle	25.4mm
12017	Hemostat - Straight 6in	31.75mm
12013	Hemostat - Straight 6in w/Plastic Coated Handle	31.75mm
12019	Hemostat - Straight 8in	60mm
12021	Hemostat - Straight 16in	127mm
12030	Hemostat - Straight 18in	139mm
12032	Hemostat - Straight 24in	155mm

Hemostat - Curved

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent corrosion resistance
- Serrated jaws hold objects firmly without cutting

20210

Designed for intricate work in tight Ratchet lock in handle allows

spaces 12002

Product ID	Description	Jaw Length
12002	Hemostat - Curved 3.5in	20mm
12016	Hemostat - Curved 5in	25.4mm
12012	Hemostat - Curved Sin w/Plastic Coated Handle	25.4mm
12018	Hemostat - Curved 6in	31.75mm
12014	Hemostat - Curved 6in w/Plastic Coated Handle	31.75mm
12020	Hemostat - Curved 8in	60mm
12022	Hemostat - Curved 16in	127mm
12031	Hemostat - Curved 18in	139mm
12033	Hemostat - Curved 24in	155mm

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108



Precision Knives & Blades

44016

44017

44018

Technik K-18 Grip-On Non-Roll Soft Handle Knife

- ► 5-inch comfortable soft grip handle
- Four jaw machined aluminum chuck for secure blade positioning
- Includes a super sharp #11 blade and clear plastic safety cap
- Ideal for cutting or trimming plastic, wood, paper, cloth and film

Product ID	Description	Blade Size
44011	Technik K-18 Grip-On Non-Roll Soft Handle Knife	#11

Technik K-1 Precision Light Duty Knife

- ▶ 4-3/4-inch aluminum handle
- 4-slot point chuck for easy blade release
- Includes a super sharp #11 blade and a high impact safety cap
- Ideal for precision cutting, forming and stripping of paper, plastic, wood, cloth and film
- Fits replacement blades #10, 11, 16, 17

Product ID	Description	Blade Size
44012	Technik K-1 Precision Light Duty Knife	#11

Technik K-2 Medium Duty Knife

- ▶ 4-3/4-inch aluminum handle
- 4-slot point chuck for easy blade release
 Includes a super sharp #22 blade and a high
- impact safety cap
- Ideal for precision cutting, trimming and stripping paper, plastic, wood, cloth and film
- Fits replacement blades #2, 18, 19, 22, 23, 24, 25, 26, 27, 28

Product ID	Description	Blade Size
44013	Technik K-2 Medium Duty Knife	#22

Technik K-5 Heavy Duty Knife

- ▶ 7/16-inch aluminum adapter
- ▶ 4-slot point chuck for easy blade release
- Includes a #19 sharp edge angled blade and a snug fitting plastic safety cap
- Ideal for precision cutting, trimming and stripping paper, plastic, and wood
- Fits replacement blades #2, 18, 19, 22, 23, 24, 25, 26, 27, 28

Product ID	Description	Blade Size
44014	Technik K-5 Heavy Duty Knife	#19

Technik K-8 Flat Handle Light Duty Knife

- Sleek long handle design with a sharp utility blade
- Both ends of the blade can be used for cutting
- Blade can be adjusted easily
- Ideal for cutting boxes, wood, leather and foam
- Fits replacement blades 44257, K-8 Replacement Blade (5/pk)

Product ID Description 44015 Technik K-8 Flat Handle Light Duty Knife

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Technik K-10 Plastic Snap Blade Knife

- 13-Point snap off blade in a strong plastic track
- Plastic auto-lock handle

44011

44012

44013

44014

44015

- Ideal for home, office, or industrial use cutting paper, plastic, wood and other items
- Fits replacement blades 44256, K-10 Replacement Blade (100/pk)

Product ID Description 44016 Technik K-10 Plastic Snap Blade Knife

Technik K-13 Heavy Duty Snap Blade Knife

- > 7-Point deluxe snap off blade in a strong plastic track
- Plastic auto-lock handle
- Ideal for home, office, or industrial use cutting paper, plastic, wood and other items
- Fits replacement blades 44254, K-13 Replacement Blade (100/pk)

Product ID Description 44017 Technik K-13 Heavy Duty Snap Blade Knife

Technik K-40 Pocket Clip Light Duty Utility Knife

- Multi-purpose precision knife is ideal for cutting and trimming
- Unique twist lock pocket clip safety cap
- Machined aluminum 4 jaw chuck for tight secure blade housing
- Comfortable ridged tapered plastic handle
- Fits replacement blades #10, 11, 16, 17
- Super sharp #11 blade

	Product ID	Description	Blade Size
]	44018	Technik K-40 Pocket Clip Light Duty Utility Knife	#11
-			

Technik Knife Set

- Contains K1, K2, K5 knife handles
- ► 13 assorted blades
- Includes a Teflon covered magnetic strip to help in holding the blades securely
- Organized in convenient plastic tray

Product ID Description 44101 Technik Knife Set

Technik Deluxe Knife Set

- Contains K1, K2, K5 knife handles
- 13 assorted blades
- Includes a Teflon covered magnetic strip to help in holding the blades securely
- Securely organized in a deluxe wood box

Product ID	Description
44102	Technik Deluxe Knife Set





Precision Knives & Blades





- Replacement blade for Technik K-8, Technik K-10, and Technik K-13 knives
- Ideal for home, office, or industrial use cutting paper, plastic, wood and other items

Product ID	Description
44254	K-13 Replacement Blade (100/pk)
44256	K-10 Replacement Blade (100/pk)
44257	K-8 Replacement Blade (5/pk)

44254

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Product ID

44041

44042

44043

44044

44045

micro circuitry, photography, art, etc.

Description

Scalpel Blade #10

Scalpel Blade #11

Scalpel Blade #12

Scalpel Blade #15

Scalpel Blade #23

Contains two pieces per tube

Can be used with a plastic or stainless steel handle

Blade Type

Curved cutting edge

Small curved cutting edge

Elongated triangular cutting edge

Rounded "leaf shaped" cutting edge

Small, pointed, crescent shaped cutting edge




Accu-Cut Oval Head Cutter

- This popular shape can be used for many applications
- ESD Safe Ergonomic Grips for superior comfort
- Robust oval head designed for durability

108215

Product ID	Description	Cutting Edge	Capacity
108215	Accu-Cut Oval Head Cutter	Semi-Flush	0.2-1.25mm
10821F	Accu-Cut Oval Head Cutter	Flush	0.15-1.25mm

Accu-Cut Oval Relief Head Cutter



- Relieved head allows easier access in tight confined areas
- ESD Safe Ergonomic Grips for superior comfort
- Designed to be durable

10822F

SD

Product ID	Description	Cutting Edge	Capacity
108225	Accu-Cut Oval Relief Head Cutter	Semi-Flush	0.2-1.2mm
10822F	Accu-Cut Oval Relief Head Cutter	Flush	0.15-1.1mm

Accu-Cut Large Oval Head Cutter

- > 25% larger than our standard oval head cutters
- Larger cutting capacity
- ESD Safe Ergonomic Grips for superior comfort
 Designed to be durable



10823S

Product ID	Description	Cutting Edge	Capacity
108235	Accu-Cut Large Oval Head Cutter	Semi-Flush	0.2-1.5mm
10823F	Accu-Cut Large Oval Head Cutter	Flush	0.15-1.5mm
10823R	Accu-Cut Large Oval Head Cutter	Razor Flush [®]	0.15-1.3mm

Register online to receive updates on the newest products and for the latest specials from Aven.

Accu-Cut XL Oval Head Cutter

- Extra large oval head for cutting heavy duty wire
- ESD Safe Ergonomic Grips for superior comfort
- Designed to be durable

Prod 1082 1082



		108295	
duct ID	Description	Cutting Edge	Capacity
295	Accu-Cut XL Oval Head Cutter	Semi-Flush	0.4-2mm
29F	Accu-Cut XL Oval Head Cutter	Flush	0.3-2mm

Accu-Cut Mini Oval Head Cutter

- Miniature oval head for fine cutting work
- ESD Safe Ergonomic Grips for superior comfort
- Designed to be durable

			1002/1
Product ID	Description	Cutting Edge	Capacity
108275	Accu-Cut Mini Oval Head Cutter	Semi-Flush	0.2-1.25mm
10827F	Accu-Cut Mini Oval Head Cutter	Flush	0.1-0.9mm

Accu-Cut Tapered Head Cutter

- Pointed head allows for increased access in tight areas
- ESD Safe Ergonomic Grips for superior comfort
 Designed to be durable



10827F

10825S

ESD

10826F

10828S

Product ID	Description	Cutting Edge	Capacity
108255	Accu-Cut Tapered Head Cutter	Semi-Flush	0.2-1.25mm
10825F	Accu-Cut Tapered Head Cutter	Flush	0.15-1.25mm

Accu-Cut Tapered Relief Head Cutter

- Pointed head with relief allows for increased access in tight areas
 - ESD Safe Ergonomic Grips for superior comfort
 - Designed to be durable

Product ID	Description	Cutting Edge	Capacity
10826S	Accu-Cut Tapered Relief Head Cutter	Semi-Flush	0.2-1.15mm
10826F	Accu-Cut Tapered Relief Head Cutter	Flush	0.1-1.05mm

Accu-Cut Mini Tapered Relief Cutter

- Miniature tapered head with relief for exceptionally fine cutting work
- ESD Safe Ergonomic Grips for superior comfort
- Designed to be durable

Product ID	Description	Cutting Edge	Capacity
108285	Accu-Cut Mini Tapered Relief Cutter	Semi-Flush	0.2-1.1mm
10828F	Accu-Cut Mini Tapered Relief Cutter	Flush	0.1-1mm

Technik Stainless Steel Pliers and Cutters



10331

10330

10327

Oval Head Cutter 114mm (4.5")

- Manufactured from 400 series stainless steel ►
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw ► alignment and durability

1 alter		
	10321	

Product ID	Description	Cutting Edge	Capacity
10321*	Oval Head Cutter 114mm (4.5")	Semi-Flush	0.2-1.25mm
10323	Oval Head Cutter 114mm (4.5")	Flush	0.15-1.25mm

Oval Head Cutter Large 127mm (5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs ►
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

10322

10332

10325

10329

Product ID	Description	Cutting Edge	Capacity
10322	Oval Head Cutter Large 127mm (5")	Semi-Flush	0.2-1.5mm
10324	Oval Head Cutter Large 127mm (5")	Flush	0.15-1.5mm

Mini Oval Head Cutter 110mm (4.3")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs ►
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Cutting Edge	Capacity
10332	Mini Oval Head Cutter 110mm (4.3")	Flush	0.1-1.25mm
Tapered Head Cutter 114mm (4.5")			
Manufactu	red from 400 series stainless steel		

- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Cutting Edge	Capacity
10325	Tapered Head Cutter 114mm (4.5")	Semi-Flush	0.2-1.25mm
10326	Tapered Head Cutter 114mm (4.5")	Flush	0.15-1.25mm

Tapered Relief Cutter 114mm (4.5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior ► jaw alignment and durability

Product ID	Description	Cutting Edge	Capacity
10329	Tapered Relief Cutter 114mm (4.5")	Flush	0.1-1.05mm

NOTE: Product ID's with * included in 10600A Precision Stainless Steel Pliers Set.

Mini Tapered Head Cutter 110mm (4.3")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Cutting Edge	Capacity
10331	Mini Tapered Head Cutter 110mm (4.3")	Flush	0.1-1.25mm

Tip Cutter 114mm (4.5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability
- Tip cutter with deep relief and low profile

Product ID	Description	Cutting Edge	Capacity
10330	Tip Cutter 114mm (4.5")	Flush	0.1-1.05mm

End Cutter 114mm (4.5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability
- Designed to cut close to the surface leaving smooth surface behind


Product ID	Description	Cutting Edge	Capacity
10327*	End Cutter 114mm (4.5")	Semi-Flush	0.2-1.25mm
Oblique He	ead Cutter 114mm (4.5")		
 Induction I Dual leaf sj ESD Safe ci Box Joint c alignment Designed t 	red from 400 series stainless steel hardened jaws prings ushioned grips onstruction provides superior jaw and durability to cut close to the surface o can be used for fine wire cutting	10328	3

Product ID	Description	Cutting Edge	Capacity	
10328	Oblique Head Cutter 114mm (4.5")	Semi-Flush	0.2-1.25mm	
Long Nose Pliers w/cutter 120.5mm (4.75")				
 Manufactured from 400 series stainless steel Induction hardened jaws Dual leaf springs ESD Safe cushioned grips Box Joint construction provides superior jaw 10315 				

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10315*	Long Nose Pliers w/cutter	26.4mm	1.8mm	Serrated

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com







Technik Stainless Steel Pliers and Cutters

Chain Nose Pliers 114mm (4.5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- **Dual leaf springs**
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10301*	Chain Nose Pliers 114mm (4.5")	23.6mm	1.8mm	Smooth
10307	Chain Nose Pliers 114mm (4.5")	23.6mm	1.8mm	Serrated

Chain Nose Pliers 127mm (5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- **Dual leaf springs**
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10302	Chain Nose Pliers 127mm (5")	26.6mm	1.8mm	Smooth
10308	Chain Nose Pliers 127mm (5")	26.6mm	1.8mm	Serrated
10311	Chain Nose Pliers 127mm (5")	37.4mm	1.8mm	Smooth
103115	Chain Nose Pliers 127mm (5")	37.4mm	1.8mm	Serrated

Chain Nose Pliers 152mm (6")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw ► alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10333	Chain Nose Pliers 152mm (6")	38.8mm	2mm	Serrated
		/		

Flat Nose Pliers 114mm - 152mm (4.5" - 6")

- Manufactured from 400 series stainless steel ►
- Induction hardened jaws
- ► Dual leaf springs
- ESD Safe cushioned grips ►
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10303*	Flat Nose Pliers 114mm (4.5")	23.6mm	3.2mm	Smooth
10304	Flat Nose Pliers 127mm (5")	29.9mm	5.87mm	Smooth
10335	Flat Nose Pliers 152mm (6")	42mm	5.3mm	Smooth

Round Nose Pliers 114mm - 127mm (4.5 - 5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10305	Round Nose Pliers 114mm (4.5")	21.3mm	1.14mm	Smooth
10306	Round Nose Pliers 127mm (5")	23.6mm	1.14mm	Smooth

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Bent Nose Pliers 114mm (4.5")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
 - Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10309	Bent Nose Pliers 114mm (4.5")	22.8mm	1.5mm	Smooth
10310	Bent Nose Pliers 114mm (4.5")	22.8mm	1.5mm	Serrated

Bent Nose Pliers 152mm (6")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10313	Bent Nose Pliers 152mm (6")	40.6mm	2mm	Smooth

- Dual leaf springs
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10314*	Needle Nose Pliers	49mm	1.5mm	Serrated

Needle Nose Pliers Curved 152mm (6")

- Manufactured from 400 series stainless steel
- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Box Joint construction provides superior jaw alignment and durability

Product ID	Description	Jaw Length	Tip Width	Jaw Type
10953	Needle Nose Pliers Curved	31.2mm	1.3mm	Serrated

Precision Stainless Steel Pliers Set 6pc

- Induction hardened jaws
- Dual leaf springs
- ESD Safe cushioned grips
- Manufactured from 400 series stainless steel
- Box Joint construction provides superior jaw alignment and durability
- Set includes: Technik Stainless Steel Pliers & Cutters - 10301, 10303, 10314, 10315, 10321, 10327
- Tools come with a handy leatherette pouch

Product ID Des	escription
10600A Need	edle Nose Pliers Curved


NOTE: Product ID's with * included in 10600A Precision Stainless Steel Pliers Set.



10313

10314

10953




Pro	duct ID	Description	Jaw Length	Tip Width	Jaw Type
103	13	Bent Nose Pliers 152mm (6")	40.6mm	2mm	Smooth

Needle Nose Pliers 146mm (5.75")

Manufactured from 400 series stainless steel

Indu	uctic	on h	arc	lened	jaws
~		~			



46

10600A





10302

10301



10333

10335

Niptec Cutters & Parallel Action Pliers

Niptec TR 5000 Cutter

- Durable 5mm thick blades
- Compact ergonomic design
- Semi-flush cutting edge
- For use on copper wire up to 12 AWG
- ESD Safe

ESD Safe grip:	s make tool comfortable and easy to use	
Product ID	Description	Cutting E
10501	Niptec TR 5000 Cutter	Semi-Flush

Niptec TR 5000PG Cutter

- Durable 5mm thick blades
- Compact ergonomic design
- Flush cutting edge

- For use on copper wire up to 16 AWG
- ESD Safe grips make tool comfortable and easy to use

Product ID	Description	Cutting Edge	
10503	Niptec TR 5000PG Cutter	Flush	
Niptec TR 25	Cutter		

For use on copper wire up to 18 AWG

- ESD Safe grips make tool comfortable and easy to use
- Compact ergonomic design
- Flush cutting edge
- Narrow cutting head for access into dense areas

Product ID	Description	Cutting Edge
10521	Niptec TR 25 Cutter	Flush

Niptec TR 25-E Cutter

- For use on copper wire up to 18 AWG
- Blue non-slip grips make tool comfortable and ► easy to use
- Compact ergonomic design
- Flush cutting edge
- Narrow cutting head for access into dense areas

Product ID	Description	Cutting Edge	
10521EC	Niptec TR 25-E Cutter	Flush	
Niptec TR 20	Niptec TR 20 50M Cutter		
ESD Safe grips	s make tool comfortable and easy to use		

Compact ergonomic design

- Flush cutting edge
- Small cutting head angled at 48° for access into tight places
- For use on copper wire up to 22 AWG

Product ID	Description	Cutting Edge
10525	Niptec TR 20 50M Cutter	Flush
Flush cutting	onomic design	
ESD Safe grip:	cifically for cutting integrated circuit pins s make tool comfortable and easy to use g head angled at 45° for access into dense areas	10526

Product ID	Description	Cutting Edge
10526	Niptec TR 20 TM Cutter	Flush

Niptec TR 20M Cutter

Compact ergonomic design

10501

10503

10521

10521EC

10525

Edge

- ESD Safe grips make tool comfortable and easy to use
- For use on copper wire up to 20 AWG
- Small cutting head angled at 21° for access into tight places

Product ID	Description			Cutting Edge	
10527B	Niptec TR 20M Cutte	r		Flush	
 Pliers Parallel Action 5" Snipe Nose Grip remains consistently parallel along full length of jaw when open or closed Smooth, snipe profile jaws offer square vice-like grip Compound lever action with no spring Compact, ergonomic design Nickel-plated handles with jaws made of hardened steel 					
•		vs made of hardened st	teel		
•		rs made of hardened st	teel Max Open	Jaw Length	
 Nickel-pl 	ated handles with jaw			Jaw Length 25mm	

Compound lever action with no spring Nickel-plated handles with jaws made of hardened steel

Product ID	Description	Max Open	Jaw Length
10756	Flat Nose Pliers 8"	17mm	41mm
Serrated.Compour	Pliers w/Wire Cutters 5" laws with V-Slot for holding wire ad lever action with no spring ated handles with jaws made of steel	a cust	10761
Built-in w	ire cutter cuts soft wire up to 2.5mm (0.1")		

Grip remains consistently parallel along full length of jaw when open or closed

Product ID	Description	Max Open	Jaw Length		
10761	Flat Nose Pliers 8"	17mm	35mm		
 Flat Nose Pliers w/Wire Cutters 8" Serrated Jaws with V-Slot for holding wire Grip remains consistently parallel along full length of jaw when open or closed Compound lever action with no spring Cushion-grip handles with jaws made of hardened steel Built-in wire cutter cuts soft wire up to 6mm (0.24") 					
Product ID	Description	Max Open	Jaw Length		
10764	Flat Nose Pliers w/Wire Cutters 8"	17mm	41mm		
 Compound cutting a 	Cutter Compound Action 6.5" and lever action handles give you more pow and gripping and lever action handles require less	er for			

- Compound lever action handles require less 10754 force when cutting
- Durable, semi-flush cutting jaw will cut piano wire up to 2mm
- Ergonomic design provides extra comfort and ease in use

Product ID	Description	Max Open	Jaw Length
10754	Diagonal Cutter Compound Action 6.5"	17mm	41mm

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com



10527B



STEALTH Cutters



Premium Wire Cutters

- High performance alloy steel
- Non-reflective satin finish
- 60-63 HRC
- Precision screw joint construction



ESD Safe Comfort

- Designed for all hand
- **Dual Leaf Springs**



The Right Cutters For The **Right Job**

- Oval head, tapered head, and angled
- cutters Available with flush or semi-flush cutting
- blades

- 60-63 HRC
- Screw joint construction for precise blade alignment
- Exceptional cutting performance

Smooth Cutting Performance

Aven Stealth Cutters are manufactured from a high performance alloy steel for exceptional strength and durability. The cutters feature a non-reflective satin finish, a unique screw-joint for perfect alignment of the cutting blades whilst minimizing friction, induction hardened cutting edges (60-63HRC) that is produced using a proprietary grinding process to ensure edge angle accuracy and ESD safe ergonomically designed grips. Each cutter is individually inspected and checked for quality and performance.

HIM

- High performance alloy steel
- Ergonomic ESD safe comfort hand grips
- Ultra-responsive leaf springs for reduced hand fatigue
- Non-reflective satin finish

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108



Head Style	Image	Part#	Cutting Capacity	Line Drawing
Oval Head	.07	Flush: 10921F Semi-Flush: 10921S	Flush: 0.15-1.20mm Semi-Flush: 0.20-1.20mm	B2.09
Tapered Head	107	Flush: 10925F Semi-Flush: 10925S	Flush: 0.15 -1.00mm Semi-Flush: 0.20-1.10mm	A 13.65 B2.09 B2.09
Mini Oval Head	.07	Flush: 10927F	0.10 - 1.00mm	
Mini Tapered Head w/Relief	10	Flush: 10928F	0.10 - 1.00mm	
Angulated Cutter Mini	CHOT	Flush: 10934F	0.10 - 0.65mm	A 18.75 B2.09
Angulated Cutter Large	F-1.0	Flush: 10935F	0.10 - 0.65mm	A (A (B)
Extra Large Oval Head	A STATE	Flush: 10923	.10 - 2.0mm	Line Drawing Coming Soon

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108







Machined Stainless Steel

- Precise Tip Alignment **Exceptional Durability**

Ultra-Responsive



Dual Leaf Springs Reduce hand fatigue for repeated use ESD Safe Grips AVEN ESD

- Ergonomic comfort grips
- ESD Safe

Heavy-Duty Precision Pliers

Made from machined stainless steel, Aven's Stealth Pliers are designed for heavy-duty use. Featuring screw joint construction for maximum durability, ensuring precise alignment for the life of the pliers. Ultra-responsive leaf springs provide easy opening and closing of the pliers for reduced hand fatigue during repetitive use. ESD safe, ergonomic hand grips provide protection against static build up and feel comfortable for all hand sizes. Ideal for projects that include forming, bending and precision assembly.


IFAVEN G



7 Models Available

Seven tip styles ideal for a variety of applications







Choosing the Correct Tweezer



Aven offers a wide variety of tweezers to meet a broad range of applications and 2 different quality grades.

In order to choose the best tool for your application:

- 1. Determine the type of points best suited for your application.
- 2. Refer to the material guide below and select the correct material for your application.
- 3. Determine the quality level required for your application if applicable. (Table 1)

Special Coatings (Available on non-magnetic stainless steel only)

TE - Teflon Superior anti-scratch, non-stick material. Acid resistant. 400°F/200°C

EP - Epoxy Good electrical insulation and resistance to chemicals. Antiglare. 300°F/150°C

* To order tweezers with above mentioned coatings, call Aven for price and delivery time.

	Quality Grades (Table 1)
Accu-Tek ♦♦♦♦	Made from the finest steels. Perfectly Balanced for a superior feel. Light weight with soft tension with accurately finished points. Recommended for work under high power magnification aerospace and micro electronics and in applications where high precision is required. All Accu-Tek precision tweezers are made from anti-acid, anti-magnetic stainless steel.
Technik ♦ ♦ ♦	Finely crafted tweezers. Anti-glare finish to reduce eye strain. Hand finished points for accuracy. Recommended for micro electronics and precision assembly.

Material Selection Guide (Table 2)

Material	Tip Hardness	Magnetism	Corrosion Resistance
Titanium	Excellent	Never	Excellent
Carbon steel	Excellent	Yes	Low
Stainless Steel	Very Good	Some	Good
Stainless Steel, Anti- magnetic, Anti-acid	Good	None to very little	Excellent, Resists Acids
Carbon Composite	Soft	None	Non- corrosive

Titanium: Titanium tweezers are excellent for use in the silicon chip industry, as they do not shed particles like the stainless steel. When it is determined that microscopic particles are a detriment when handling abrasive parts we recommend using titanium tweezers. In addition since titanium tweezers are 100% non magnetic, they are extremely useful when working with magnetic materials or when working in a magnetic field. Titanium is lightweight and a high strength material.

Ceramic: ESD Safe, non magnetic. Resists all chemicals except hydrofluoric acids. Withstands temperatures up to 900°F. Heat sink fighter.

Plastic: We offer static dissipative plastic tweezers. Plastic tweezers are non magnetic, resist virtually all commercial solvents. Non absorbent and easy to clean. Tips are non-marring.

Carbofib: Fully ESD Safe (102 ohm) but at the same time, soft and non scratching. These conductive synthetic fiber tips are ideally suited to handle delicate and fragile components when extreme care and ESD safety are an absolute necessity. Every tweezers is manually finished and tested for maximum precision. Chemical resistant and heat resistant up to 256°C.

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Precision Tweezers

Style AA Tweezers

For general assembly, very strong and precise tips with fine finish. Available in different materials and quality grades. Length: 5" (130mm)

Product ID	Description	Material
18013-BR	Accu-Tek Tweezers AM-BR	Brass
18013USA	Technik Tweezers AA-SA	Stainless Steel
18011-CS	Aven Tweezers AA-CS	Carbon Steel, Nickel/Chrome Plated
18013TS	Accu-Tek AA (Swiss Made)	Titanium
18013TT	Aven Tweezers AA	Titanium
18013EZ	E-Z Pik Tweezers AA Yellow	Stainless Steel

Style ACTweezers

Sturdy tips for bending and handling very fine wire and components. Tweezers feature finger grips. Available in different materials and quality grades. Length: 4-3/4" (120mm)

Product ID	Description	Material
18016USA	Technik Tweezers AC-SA	Stainless Steel
18014-CS	Aven Tweezers AC-CS	Carbon Steel, Nickel/Chrome Plated

Style MM Tweezers

General purpose, tweezers with hardened, precision tips and fine finish. Available in different materials and quality grades. Length: 5" (130mm)

Product ID	Description	Material
18023USA	Technik Tweezers MM-SA	Stainless Steel
18014-CS	Aven Tweezers MM-CS	Carbon Steel, Nickel/Chrome Plated

Style 00 Tweezers

Flat edges, heavy duty strong blades tapering to a regular strong point. Available in different materials and quality grades. Length: 4-3/4" (120mm)

inless Steel
bon Steel, Nickel/Chrome Plated



Product ID	Description	Material
18032ACU	Accu-Tek Tweezers 00-SA	Stainless Steel
18032USA	Technik Tweezers 00-SA	Stainless Steel
18032-CS	Aven Tweezers 00-CS	Carbon Steel, Nickel/Chrome Plated
18032TS	Accu-Tek 00 (Swiss Made)	Titanium
18032TT	Aven Tweezers 00	Titanium
18032EZ	E-Z Pik Tweezers 00 Red	Stainless Steel
18032-ER	Comfort Grip Tweezers 00-SA	Stainless Steel

Style 00C Tweezers

Flat edges, heavy duty strong blades tapering to a regular strong point. Slightly shorter than 00. Length: 4-1/2" (115mm)

Product ID	Description	Material
18034USA	Technik Tweezers 00C-SA	Stainless Steel

Style 00D Tweezers

Flat edges, heavy duty strong blades tapering to a regular strong point. Tweezers feature finger grips. Available in different materials and quality grades. Length: 4-3/4" (120mm)





Titanium

Style 0 Tweezers

Product ID

18037ACU

18037-MS

18037USA

18036-CS

18037TT

Extremely fine straight points for general handling and positioning of minature parts or fine wire. Available in different quality grades. Length: 4-3/4" (120mm)

Aven Titanium Tweezers 00D

Product ID	Description	Material
18026ACU	Accu-Tek Tweezers 0-SA	Stainless Steel
18026USA	Technik Tweezers 0-SA	Stainless Steel

Style 0A Tweezers

Straight point tweezers with radius edges are uniquely designed for working in small yet dense areas. Length: 4-3/4" (120mm)

Product ID	Description	Material
18027USA	Technik Tweezers 0A-SA	Stainless Steel

Style 0CTweezers

Straight point tweezers with flat edges, fine tips and shortened overall length for delicate handling of small parts. Available in different quality grades. Length: 3-1/2" (90mm)

Product ID	Description	Material
18029ACU	Accu-Tek Tweezers 0C-SA	Stainless Steel
18029USA	Technik Tweezers 0C-SA	Stainless Steel



MM







AA



0

0A

0C



Style SS Tweezers

Extra long and narrow, straight point tweezers. Provides extended reach and access to confined areas. Available in different quality grades. Length: 5-1/2" (140mm)

Product ID	Description	Material
18040ACU	Accu-Tek Tweezers SS-SA	Stainless Steel
18040ACU	Artis Tweezers SS-SA	Stainless Steel
18040USA	Technik Tweezers SS-SA	Stainless Steel

Style 1 Tweezers

Designed for general use featuring strong blades with fine points. Available in different materials and quality grades. Length: 4-3/4" (120mm)

Product ID	Description	Material
18043ACU	Accu-Tek Tweezers 1-SA	Stainless Steel
18043USA	Technik Tweezers 1-SA	Stainless Steel
18043-CS	Aven Tweezers 1-CS	Carbon Steel, Nickel/Chrome Plated
18043ARS	Artis Tweezers 1-SA	Stainless Steel
18043TT	Aven Titanium Tweezers 1	Titanium

Style 2 Tweezers

Tapered, sharp point tweezers for bending and handling of small wires and parts. Available in different materials and quality grades. Length: 4-3/4" (120mm)



SS

Product ID	Description	Material
18046ACU	Accu-Tek Tweezers 2-SA	Stainless Steel
18046-MS	Mini 2-SA (Swiss Made)	Stainless Steel
18046USA	Technik Tweezers 2-SA	Stainless Steel
18046-CS	Aven Tweezers 2-CS	Carbon Steel, Nickel/Chrome Plated
18046TS	Accu-Tek 2 (Swiss Made)	Titanium
18046TT	Aven Titanium Tweezers 2	Titanium

Style 2A Tweezers

Straight Flat Tips. Provides large flat gripping surface. Available in different materials and quality grades. Length: 4-3/4" (120mm)

2 4
ZA

Product ID	Description	Material
18049ACU	Accu-Tek Tweezers 2A-SA	Stainless Steel
18049-MS	Mini 2A-SA (Swiss Made)	Stainless Steel
18049USA	Technik Tweezers 2A-SA	Stainless Steel
18049-CS	Aven Tweezers 2A-CS	Carbon Steel, Nickel/Chrome Plated
18049TS	Accu-Tek 2A (Swiss Made)	Titanium
18049TT	Aven Titanium Tweezers 2A	Titanium
18049EZ	E-Z Pik Tweezers 2A Black	Stainless Steel
18049-ER	Comfort Grip Tweezers 2A-SA	Stainless Steel
18043-ARS	Artis Tweezers 2A-SA	Stainless Steel

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108



Style 2AB Tweezers feature curved round tips, ideal for handling delicate or small parts. Tip angle facilitates wafer tray loading. Length: 4-3/4" (120mm)

Product ID	Description	Material
18050USA	Technik Tweezers 2AB-SA	Stainless Steel

Style 3 Tweezers

Fine point tweezers for general assembly or light magnification applications. Available in different materials and quality grades. Length: 4-3/4" (120mm)

Product ID	Description	Material
18053ACU	Accu-Tek Tweezers 3-SA	Stainless Steel
18053-MS	Mini 3-SA (Swiss Made)	Stainless Steel
18053USA	Technik Tweezers 3-SA	Stainless Steel
18053-CS	Aven Tweezers 3-CS	Carbon Steel, Nickel/Chrome Plated
18053TS	Accu-Tek 3 (Swiss Made)	Titanium
18053TT	Aven Titanium Tweezers 3	Titanium

Style 3C Tweezers

Fine point tweezers, slightly shorter than #3, for general assembly or light magnification applications. Available in different materials and quality grades. Length: 4-1/4" (110mm)

3C

3CB

3F

Product ID	Description	Material
18056ACU	Accu-Tek Tweezers 3C-SA	Stainless Steel
18056USA	Technik Tweezers 3C-SA	Stainless Steel
18054-CS	Aven Tweezers 3C-CS	Carbon Steel, Nickel/Chrome Plated
18056TS	Accu-Tek 3C (Swiss Made)	Titanium
18056TT	Aven Titanium Tweezers 3C	Titanium
18056EZ	E-Z Pik Tweezers 3C Light Blue	Stainless Steel
18056-ER	Comfort Grip Tweezers 3C-SA	Stainless Steel
18056ARS	Artis Tweezers 3C-SA	Stainless Steel

Style 3CB Tweezers

Long and narrow bent tip tweezers. Provides extended reach and access to confined areas. Length: 4-1/4" (110mm)

Product ID	Description	Material
18078ACU	Accu-Tek Tweezers 3CB-SA	Stainless Steel

Style 3F Tweezers

Tips touch over 3mm for holding tiny wires. Length: 4-3/4" (120mm)

Product ID	Description	Material
18079ACU	Accu-Tek Tweezers 3F-SA	Stainless Steel



Precision Tweezers

Style 35A Tweezers

Ideal for handling wafers, delicate parts, and delicate assembly work. Length: 4-3/4" (120mm)

Product ID	Description	Material
18201USA	Aven Tweezers 35A-SA	Stainless Steel

Style 36 Tweezers

Angled broad tip tweezers feature large paddle style tips. Wide tips provide firm grip. Length: 4-3/4" (120mm)

Product ID	Description	Material
18202USA	Aven Tweezers 36-SA	Stainless Steel

Style 4 Tweezers

Designed for extra fine work. Blades taper sharply from body to form very fine long rounded points. Available in different materials and quality grades. Length: 4-1/4" (110mm)

Product ID	Description	Material
18059ACU	Accu-Tek Tweezers 4-SA	Stainless Steel
18059USA	Technik Tweezers 4-SA	Stainless Steel
18057-CS	Aven Tweezers 4-CS	Carbon Steel, Nickel/Chrome Plated
18059TT	Aven Titanium Tweezers 4	Titanium

Style 5 Tweezers

Designed for extra fine work with long blades which break sharply from body and taper to the sharpest points available. Available in different materials and quality grades. Length: 4-1/4" (110mm)

Product ID	Description	Material
18062ACU	Accu-Tek Tweezers 5-SA	Stainless Steel
18062-MS	Mini 5-SA (Swiss Made)	Stainless Steel
18062USA	Technik Tweezers 5-SA	Stainless Steel
18060-CS	Aven Tweezers 5-CS	Carbon Steel, Nickel/Chrome Plated
18062TS	Accu-Tek 5 (Swiss Made)	Titanium
18062TT	Aven Titanium Tweezers 5	Titanium
18062EZ	E-Z Pik Tweezers 5 Green	Stainless Steel
18062-ER	Comfort Grip Tweezers 5-SA	Stainless Steel
18062ARS	Artis Tweezer 5-SA	Stainless Steel

Style 5A Tweezers

Features the sharpest points available. The oblique fine points provide greater visibility. Available in

different materials and quality grades. Length: 4-1/2" (115mm)

Product ID	Description	Material
18065ACU	Accu-Tek Tweezers 5A-SA	Stainless Steel
18065USA	Technik Tweezers 5A-SA	Stainless Steel
18065TT	Aven Titanium Tweezers 5A	Titanium



36

5

5A



Features super micro high precision bent tips provide maximum visiblilty. Available in different materials and quality grades. Length: 4-1/4" (110mm)

Product ID	Description	Material
18066USA	Technik Tweezers 5B-SA	Stainless Steel
18066-CS	Aven Tweezers 5B-CS	Carbon Steel, Nickel/Chrome Plated

Style 6 Tweezers

Angled fine tip is designed to allow greater access into tight areas. Available in different materials and quality grades. Length: 4-3/4" (120mm)

Product ID	Description	Material
18069ACU	Accu-Tek Tweezers 6-SA	Stainless Steel
18069USA	Technik Tweezers 6-SA	Stainless Steel
18067-CS	Aven Tweezers 6-CS	Carbon Steel, Nickel/Chrome Plated
18069TS	Accu-Tek 6 (Swiss Made)	Titanium
18069TT	Aven Titanium Tweezers 6	Titanium

Style 65A Tweezers

Long fine curved tips are designed to allow greater access into tight areas. Length: 5-1/2" (140mm)

Product ID	Description	Material
18076ACU	Accu-Tek Tweezers 65A-SA	Stainless Steel

Style 66 Tweezers

Long double bent tips are designed to allow greater access into tight areas. Length: 5-1/2" (140mm)

Product ID	Description	Material
18077ACU	Accu-Tek Tweezers 66-SA	Stainless Steel

Style 7 Tweezers

Designed with curved, super fine points for easy assembly work, allowing hand to rest on bench. Available in different materials and quality grades. Length: 4-1/2" (115mm)

Product ID	Description	Material
18072ACU	Accu-Tek Tweezers 7-SA	Stainless Steel
18072USA	Technik Tweezers 7-SA	Stainless Steel
18070-CS	Aven Tweezers 7-CS	Carbon Steel, Nickel/Chrome Plated
18072TS	Accu-Tek 7 (Swiss Made)	Titanium
18072TT	Aven Titanium Tweezers 7	Titanium
18072EZ	E-Z Pik Tweezers 7 Orange	Stainless Steel
18072-ER	Comfort Grip Tweezers 7-SA	Stainless Steel

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Tel: 734.973.0099 | Fax: 734.973.0097 | www.aveninc.com





6

~ ~





Precision Tweezers

18476USA

Style 7B Tweezers

Similar to style 7, pattern 7B tweezers feature serrated tips and have been designed with curved, super fine points for easy assembly work, allowing hand to rest on bench. Length: 4-1/2" (115mm)

Product ID	Description	Material
18074USA	Technik Tweezers 7B-SA	Stainless Steel

Style 15AWG Tweezers

Designed for culling hairsprings and electronic component wires. The blades, made from 400 series stainless steel induction for durability, feature hardened tips. Length: 4-1/2" (115mm)

Product ID	Description	Material
18114ACU	Accu-Tek Tweezers 15AWG-SA	Stainless Steel

Aven 6-Piece Tweezer Set

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Curved and straight tip tweezers are helpful when working in confined spaces
- Locking tweezers helpful for soldering and holding small parts

Aven 5-Piece Tweezer Set

Product ID

18472

Produ





7B

15AWG

18472

18473

Technik 5-Piece Precision Tweezer Set

- Finely crafted tweezers
- Anti-glare finish to reduce eye strain
- Hand finished points for accuracy
- Ideal for micro electronics and precision assembly
- Contains OO-SA, OOD-SA, 3C-SA, 5-SA and 7-SA styles
- Supplied in an elegant padded wooden case

Product ID	Description	
18476USA	Technik 5-Piece Precision Tweezer Set	
E-Z Pik 6-Pied	ce Tweezer Set	11111

- Color coated for easy identification
- Contains AA-SA, OO-SA, OODSA, 3C-SA, 5-SA and 7-SA styles
- Stainless steel, anti-magnetic, anti-acid
- Highly durable special coating for high visibility and easy identification

		18480EZ
Product ID	Description	
18480EZ	E-Z Pik 6-Piece Tweezer Set	
Titanium 6-P	Piece Precision Tweezer	11.

Set

Product ID

- Aven's most popular titanium tweezer styles in a handy pouch
- Titanium tweezers do not shed particles
- like the stainless steel tweezers Light weight and high strength material
- Contains 2A, 3c, OO, AA, 5 and 7 styles
- Extremely useful when handling magnetic materials
- 18480TT

Stainless steel finish provides excellent corrosion resistance Ideal for bending, separating and removing

Description

Aven 6-Piece Tweezer Set

- small items
- Curved and straight tip tweezers are helpful when working in confined spaces
- Lo sm

ocking twee nall parts	zers helpful for soldering and holding
uct ID	Description

```
18473
                    Aven 5-Piece Tweezer Set
```

Technik 6-Piece Precision Tweezer Set

- Finely crafted tweezers
- Anti-glare finish to reduce eye strain
- Hand finished points for accuracy
- Ideal for micro electronics and precision assembly
- Contains AA-SA, OO-SA, OODSA, 3C-SA, 5-SA and 7-SA styles

18475USA

Product ID	Description
18475USA	Technik 6-Piece Precision Tweezer Set

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

18480TT	Titanium 6-Piece Precision Tweezer Set
Carbofib 3-C	FTweezers

Description

These Swiss made, ESD safe tweezers feature excellent wear and abrasion resistance. Ideal for handling sensitive materials such as electronic components, micro-mechanical parts, glass and ceramic substrates, these tweezers provide very high rigidity, excellent tensile and flexural strength and have good chemical resistance to oils, grease, fuels, and nonpolar solvents. Length: 5" (130mm)

Product ID	Description	Tip Style	Tip Width	Style
18702	Carbofib 302-CF Tweezers	Straight, Broad	2mm	302
18704	Carbofib 304-CF Tweezers	Straight, Ultra Fine	0.6mm	304
18760	Carbofib 3-CF Tweezers	Straight, Fine	0.8mm	3
18762	Carbofib 5-CF Tweezers	Straight, Ultra Fine	0.5mm	5
18767	Carbofib 2-CF Tweezers	Straight, Fine	0.8mm	2
18768	Carbofib 2A-CF Tweezers	Straight, Rounded	1.8mm	2A
18769	Carbofib 7-CF Tweezers	Curved, Fine	0.6mm	7

Plastic & Carbofib Tweezers

9-Piece Artis Tweezers

Aven's cutting edge design features a angled bend at the end of the tip, which provides a softer overall grip with a large surface area that reduces hand fatigue, enhancing productivity. The durable tweezers are protected by an attractive ESD safe coating and highly feature polished stainless steel tips.



18517

18523

18526

18529

Contains AA,MM, OO, SS, 1-SA, 2A-SA, 3C, 5-SA, and 7-SA styles

Product ID	Description	Material
18040ARS	Artis 9- Piece Tweezers w/ Caryying Case	Stainless Steel

Style 2C Plastic Tweezers

Straight with very fine tips and made of chemically resistant lightweight plastic, this anti-static tool will not damage sensitive electronic devices nor contaminate materials when used in corrosive environments

when used in e		
Product ID	Description	Length
18517	Plastic Tweezers 2C Fine, Straight Tips	4-1/2" (115mm)

Style 7 Plastic Tweezers

Curved with very fine tips and made of chemically resistant lightweight plastic, this anti-static tool will not damage sensitive electronic devices such as hard drives nor contaminate materials when used in corrosive environments.

Product ID	Description	Length
18523	Plastic Tweezers 7 Fine, Curved Tips	4-1/2" (115mm)

Style 35 Plastic Tweezers

Straight with flat tips and made of chemically resistant lightweight plastic, this anti-static tool will not damage sensitive electronic devices such as hard drives nor contaminate materials when used in corrosive environments.

Product ID	Description	Length
18526	Plastic Tweezers 35 Straight, Flat Tips	4-1/2" (115mm)

Style 35A Plastic Tweezers

Straight with broad, flat tips and made of chemically resistant lightweight plastic, this anti-static tool will not damage sensitive electronic devices such as hard drives nor contaminate materials when used in corrosive environments.

Product ID	Description	Length
18529	Plastic Tweezers 35A Straight, Broad, Flat Tips	4-1/2" (115mm)
Style 702A ESD Plastic Tweezers Manufactured from Polyetheretherketone reinforced with 30%		
carbon fiber (PEEK/CF30), these very hard, rigid, high tensile and flexural strength tweezers are ideal for the handling		
of components in cleaning, chemical, and assembly of components. 18531		

Product ID	Description	Length
18531	ESD Plastic Tweezers 702A Straight, Flat Tips	4-1/2" (115mm)

Style 2AB Plastic Tweezers

Curved with rounded tips and made of chemically resistant lightweight plastic, this anti-static tool will not damage sensitive electronic devices such as hard drives nor contaminate materials when used in corrosive environments.

Product ID	Description	Length
18514	Plastic Tweezers 2AB Curved, Flat Tips	4-1/2" (115mm)

AVEN

18514

18532

18533

18534

18536

Style 705 ESD Plastic Tweezers

Manufactured from Polyetheretherketone reinforced with 30% carbon fiber (PEEK/CF30), these very hard, rigid, high tensile and flexural strength tweezers are ideal for the handling of components in cleaning, chemical, and assembly of components.

Product ID	Description	Length
18532	ESD Plastic Tweezers 705 Very Fine, Tapered Tips	4-1/2" (115mm)

Style 707 ESD Plastic Tweezers

Manufactured from Polyetheretherketone reinforced with 30% carbon fiber (PEEK/CF30), these very hard, rigid, high tensile and flexural strength tweezers are ideal for the handling of components in cleaning, chemical, and assembly of components.

	Product ID	Description	Length
18533 ESD Plastic Tweezers 707 Fine Tips 4-1/2" (115mm)	18533	ESD Plastic Tweezers 707 Fine Tips	4-1/2" (115mm)

Style 707A ESD Plastic Tweezers

Manufactured from Polyetheretherketone reinforced with 30% carbon fiber (PEEK/CF30), these very hard, rigid, high tensile and flexural strength tweezers are ideal for the handling of components in cleaning, chemical, and assembly of components.

Product ID	Description	Length
18534	ESD Plastic Tweezers 707A Curved, Fine Tips	4-1/2" (115mm)
Style 709 ESD Plastic Tweezers Manufactured from Polyetheretherketone reinforced with 30% carbon fiber (PEEK/CF30), these very hard, rigid, high tensile and flexural strength tweezers are ideal for the handling of components in cleaning, chemical, and assembly of components.		
Product ID	Description	Length
18535	ESD Plastic Tweezers 709 Broad, Flat Tips	4-1/2" (115mm)
Style 710 ESD Plastic Tweezers Manufactured from Polyetheretherketone reinforced with 30% carbon fiber (PEEK/CF30), these very hard, rigid, high tensile		

carbon fiber (PEEK/CF30), these very hard, rigid, high tensile and flexural strength tweezers are ideal for the handling of components in cleaning, chemical, and assembly of components.

Product ID	Description	Length
18536	ESD Plastic Tweezers 710 Wide, Flat Tips	4-1/2" (115mm)

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108



Ceramic & General Purpose Tweezers

Victor Ceramic Tweezers

- Low thermal conductivity and high thermal shock resistance
- Ceramic tweezers are used in applications where extreme heat
- is present
- Highly resistant to all strong acids except hydrofluoric
- Chemically and electrically inert
- Solder will not adhere to surface

18801

Product ID	Description	Material
18803	Ceramic Tweezers Ultra Fine Smooth Tips	Ceramic

Accu-Tek Ceramic Tweezers

- Low thermal conductivity and high thermal shock resistance
- 100% non magnetic, non rusting and non static
- Highly resistant to all strong acids except hydrofluoric
- Solder will not adhere to surface
- Will hold tip geometry better than metal
- Swiss made stainless steel handles

18811

Product ID	Description	Material
18810	Ceramic Tweezers Pattern 71	Ceramic Tips/Stainless Steel Bodies
18811	Ceramic Tweezers Pattern 72	Ceramic Tips/Stainless Steel Bodies
18812	Ceramic Tweezers Pattern 73	Ceramic Tips/Stainless Steel Bodies
18813	Ceramic Tweezers Pattern 74	Ceramic Tips/Stainless Steel Bodies
18814	Ceramic Tweezers Pattern 7MZ	Ceramic Tips/Stainless Steel Bodies

Aven Fiber Grip Tweezers

- Polished stainless steel tips firmly hold without contaminating
- Heat-resistant fiber grips protect your hands from heat while soldering
- Ideal for soldering, bending, separating and removing small items
- Cross-lock mechanism opens when pressed

1	8	4	1	5
	~			-

Product ID	Description
18415	Aven Fiber Grip Tweezers - Straight
18417	Aven Fiber Grip Tweezers - Curved

Aven Self Locking Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Cross-lock mechanism opens when pressed and closes when released

18419

Product ID	Description
18419	Aven Self Locking Tweezers - Narrow
18421	Aven Self Locking Tweezers - Wide
18423	Aven Self Locking Tweezers - Narrow Short

Stainless steel finish provides excellent corrosion resistance Ideal for bending, separating and removing small items

Aven College Forceps w/Lock

- Curved tip is helpful when working in confined spaces

18400

18402

18430

18436

18428

I	Product ID	Description	
	18400	Aven College Forceps w/Lock	
Aven College Forceps w/Alignment Pin			
	Stainless steel finish provides excellent corrosion resistance		
	 Alignmen applicatio 	t pin keeps tips aligned under high stress ns	

Inside and outside serrations provide better gripping and handling

Product ID	Description	Tip Style
18401	Aven College Forceps w/Alignment Pin	Straight, Serrated
18402	Aven College Forceps w/Alignment Pin	Curved, Serrated
18403	Aven College Forceps w/Alignment Pin	Offset Curved, Serrated
18438	Aven College Forceps w/Alignment Pin	Curved, Serrated

Aven Forceps w/Plastic Coated Tips

- Stainless steel finish provides excellent corrosion resistance
- Plastic coated tips provide chemical resistance
- Serrated handles provide better gripping

Product ID	Description
18430	Aven 8" Forceps w/Plastic Coated Tips
18431	Aven 12" Forceps w/Plastic Coated Tips

Aven Forceps w/Straight Serrated Tips

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Long, straight tip is helpful when working in confined spaces
- Serrated handles provide better gripping

Product ID	Description
18432	Aven 12" Forceps w/Straight Serrated Tips
18433	Aven 10" Forceps w/Straight Serrated Tips
18434	Aven 8" Forceps w/Straight Serrated Tips
18435	Aven 6" Forceps w/Straight Serrated Tips
18436	Aven 5" Forceps w/Straight Serrated Tips

Aven Cross Locking Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for soldering and holding small parts

General Purpose & Quick Test Tweezers



18487

18488

18494

18910

Aven Utility Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Serrated handles provide better gripping

18425

18481

18481

18483

Product ID	Description	Tip Style
18425	Aven 7" Utility Tweezers - Curved	Curved, Serrated
18426	Aven 7" Utility Tweezers - Straight	Straight, Serrated

Aven 4 3/8" General Purpose Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items

Serrated handles provide better gripping

Product ID	Description	Tip Style
18481	Aven 4 3/8" Curved Tweezers	Curved, Serrated
18482	Aven 4 3/8" Tapered Tweezers	Tapered, Smooth

Aven Blunt Tip Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Serrated handles provide better gripping

Blunt tips are useful for handling larger items

Product ID	Description	Tip Style
18486	Aven 3 1/8" Blunt Tweezers	Blunt, Smooth
18490	Aven 5 15/16" Blunt Tweezers	Blunt, Serrated
18492	Aven 10" Blunt Tweezers	Blunt, Serrated

Aven 3" Sharp Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Medium-sharp, serrated tip is helpful when working in confined spaces
 Corrected handles previde batter grinning
- Serrated handles provide better gripping

Product ID	Description	Tip Style
18483	Aven 3" Sharp Tweezers	Medium Sharp, Serrated

Aven General Purpose Flat Tip Tweezers

•	Stainless steel finish provides excellent corrosion resistance Ideal for bending, separating and removing small items	18484	18485	18489

Product ID	Description	Tip Style
18484	Aven 3 1/8" Tweezers	Sharp-Flat
18485	Aven 3 1/2" Tweezers	Sharp-Flat
18489	Aven 4 3/4" Smooth Tweezers	Sharp-Flat

Aven 4 3/8" Spade Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Spade tip is helpful when working in confined spaces
- Serrated handles provide better gripping

Product ID	Description	Tip Style
18487	Aven 4 3/8" Spade Tweezers	Spade

Aven Offset Spade Tweezers

- Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Spade tip is helpful when working in confined spaces
- Serrated handles provide better gripping

Product ID	Description	Tip Style
18488	Aven 4 1/8" Offset Spade Tweezers	Spade
18491	Aven 4 1/2" Offset Spade Tweezers	Spade

Aven Toothed Tissue Forceps

- ▶ Stainless steel finish provides excellent corrosion resistance
- Ideal for bending, separating and removing small items
- Toothed models are ideal for handling the various thicknesses of tissues

Product ID	Description	Tip Style
18494	Aven Toothed Tissue Forceps	Toothed

Quick-Test Auto-Scanning Tweezers

- Measures AC/DC voltage, resistance, continunity & diode test
- Auto Scanning Mode/Auto range
- Testing pins gold plated to reduce resistance and prevent rust
- ► Uses Lithium battery CR2032, included
- Will automatically identify whether component is a resistor, capacitor or diode

Product ID Description

18910 Quick-Test Auto-Scanning Tweezers

Register online to receive updates on the newest products and for the latest specials from Aven.



Soldering & Desoldering

Soldering/Desoldering Tools & Accessories

Soldering Station with LCD

- Display, ESD Safe 400 Series
- High-quality sensor and heat exchange system guarantee precise temperature control at the soldering tip
- Soldering iron tool heats rapidly from room temperature to 350C in 30 seconds
- Suitable for general purpose soldering as well as specialized lead-free soldering applications
- Sponge and coiled brass tip cleaner ensure a clean soldering tip free from debris and corrosive material
- Strong, deluxe iron holder provides safe secure place to store heated iron between uses

Product ID Description

17400 Soldering Station with LCD Display, ESD Safe 400 Series

Soldering Station with LCD Display, ESD Safe

405 Series

- LCD temperature control display with blue backlight
- Long lasting, durable high quality ceramic heater
- Sponge and recessed area provides a convenient method for cleaning the tip
- Suitable for general purpose soldering as well as specialized lead-free soldering applications
- Safety guard iron holder

17405

Product ID	Description
17405	Soldering Station with LCD Display, ESD Safe 405 Series

Soldering Kit - 6pc

- ▶ 40 Watt Soldering Iron heats up to 900° F
- Ideal for use on electrical/electronic components, audio equipment, etc.
- Includes desoldering pump for removing liquid solder
- Provides basic tools needed for many soldering projects
- 6 Pc kit comes complete with replaceable fine tip

Soldering Kit - 6pc

Product ID

Product ID

▶ 40 Watt Soldering Iron heats up to 900° F

Description

- Ideal for use on electrical/electronic components, audio equipment, etc.
- Includes desoldering pump for removing liquid solder
- Provides basic tools needed for many soldering projects

Description

6 Pc kit comes complete with replaceable fine tip

17502

17501

17502 Soldering Kit - 7pc

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Soldering Iron 80W with Fine Tip

- Ideal for general purpose soldering applications including metal board, tube or large components
- Round, soft grip, non-slip handle
- Durable cord with a 5-foot reach
- Fitted with long life replaceable fine tip

duct ID Description

521 Soldering Iron 40W with Fine Tip

Soldering Iron 40W with Fine Tip

- Ideal for general purpose soldering
- Round, soft grip, non-slip handle
- Durable cord with a 5-foot reach
- Fitted with long life replaceable fine tip

Product ID Description

17521 Soldering Iron 40W with Fine Tip

N-Series Soldering Iron Tips

- Long life, lead-free soldering iron tips
- Replacement tips for soldering the different components of PCBs
- Five different sizes
- Includes two tips
- For use with 17400 & 17405 ESD Safe Soldering Stations with LCD Display

Product ID	Description
17400-N9-1	N-Series Soldering Iron Tips (N9-1)
17400-N9-2	N-Series Soldering Iron Tips (N9-2)
17400-N9-3	N-Series Soldering Iron Tips (N9-3)
17400-N9-4	N-Series Soldering Iron Tips (N9-4)
17400-N9-5	N-Series Soldering Iron Tips (N9-5)

C-Series Soldering Iron Tips

- Long life, lead-free soldering iron tips
- Replacement tips for soldering the different components of PCBs
- Four different sizes
- Includes two tips
- For use with 17521 Soldering Iron 40W

Product ID	Description	
17521-C1-1 C-Series Soldering Iron Tips (C1-1)		
17521-C1-2 C-Series Soldering Iron Tips (C1-2)		
17521-C1-3 C-Series Soldering Iron Tips (C1-3)		
17521-C1-4	C-Series Soldering Iron Tips (C1-4)	

B-Series Soldering Iron Tips

- Long life, lead-free soldering iron tips
- Includes two tips
- For use with 17510 Soldering Iron 80W

Product ID	Description
17510-B5-1	B-Series Soldering Iron Tips (B5-1)



17510





Soldering & Desoldering

Soldering/Desoldering Tools & Accessories

Dual Function Smoke Absorber & Bench Fan

ESD Safe

- Functions as a solder smoke absorber and a standard fan
- Compact & space-saving
- 10 speed settings
- Adjustable metal stand
- ESD safe
- Includes carbon filter for absorbing solder smoke

Product ID Description

17015	Dual Function Bench Fan & Smoke Absorber

Lead Free Solder Pot 200W

- Heating element liquifies solder quickly and provides excellent thermal stability
- Crucible is made from stainless steel with titanium plating, featuring corrosion resistance and prolonged service life
- Suitable for melting solder, plastic, resin and more
- Ideal for tinning ends of stranded wire leads, pretinning small electrical parts and dip soldering small circuit boards

Product ID	Description	Solder Pot Capacity
17100-200	Lead Free Solder Pot 200W	800g
17100-150	Lead Free Solder Pot 150W	500g
17100-100	Lead Free Solder Pot 100W	250g

Lead Free Solder Pot 300W

- Heating element liquifies solder quickly and provides excellent thermal stability
- Crucible is made from stainless steel with titanium plating, featuring corrosion resistance and prolonged service life
- Suitable for melting solder, plastic, resin and more
- Ideal for tinning ends of stranded wire leads, pre-tinning small electrical parts and dip soldering small circuit boards 17100-300

Product ID	Description	Solder Pot Capacity
17100-200	Lead Free Solder Pot 300W	1300g

Desoldering Pump - High Impact Plastic 13"

- Durable corrosion resistant plastic construction with precision metal ► plunger
- Cushioned shock reduction minimizes board damage
- Teflon (PTFE) non-stick coated tip
- Easy to clean one-touch cylinder

Product ID Description

17535 Desoldering Pump - High Impact Plastic 13"

Desoldering Pump - ESD Safe Plastic 8.5"

- Durable corrosion resistant plastic construction
- Easy to clean one-touch cylinder

Description

Cushioned shock reduction minimizes board damage

Desoldering Pump - ESD Safe Plastic 8.5"

		~

Desoldering Pump - Metal Body 7.5"

- Durable corrosion resistant aluminum construction with precision metal plunger
- Cushioned shock reduction minimizes board damage
- Push Button for Easy Plunger Release
- Easy to clean one-touch cylinder

Product ID Description 17537 Desoldering Pump - Metal Body 7.5"

Portable Soldering Iron 30-70W

- 30 to 70 Watt power range
- Cordless, Simple and Safe Operation
- Ready to use in 20 seconds after Ignition
- Adjustable tip temperature from 400°C to 1300°C
- (750°F to 2500°F)
- Supplied with 1mm Conical Tip

Product ID	Description
17801	Portable Soldering Iron 30-70W
17801-T01	T-01 1mm Conical Tip
17801-T02	T-02 2mm Chisel Tip
17801-S05	S-05 Hot Knife Tip
17801-S07	S-07 Heat Blower Tip
17801-S30	S-30 Deflector Tip

Solder Core Wire

- Good solderability, no spattering and noncorrosive
- Leaded solder 60/40 | Lead-free solder 99.3/0.7
- 360-440° F melting point
- 1-1.2mm diameter solder available
- Ideal for use on PCB, electronic devices and fine electrical soldering

Product ID Descriptio

17553	Solder 100g 1.2mm 60/40
17555	Solder 100g 1.0mm 60/40
17553LF	Solder 100g 1.2mm Lead Free
17555LF	Solder 100g 1.0mm Lead Free
17551	Solder in Tube 1.0mm 60/40
17552	Solder in Tube 1.2mm 60/40
17551LF	Solder in Tube 1.0mm Lead Free
17552LF	Solder in Tube 1.2mm Lead Free

Desoldering Wick

- Made of clean, oxide-free copper wire
- Tight weave enables quick "on and off" desoldering Concentrated fine copper braiding utilizes less length of ►
- wick for each desoldering application **RoHS** compliant

		ipiant
	Product ID	Description
	17540 Desoldering Wick 1.5mm (0.06")	
	17541 Desoldering Wick 2mm (0.08")	
	17542 Desoldering Wick 2.5mm (0.1")	
17545 Desoldering Wick 2.5mm with dispenser case and 41.5M replacement cores		

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Product ID

17536





17801

17555

17551

AVEN

6717

SOLDER







17100-200

17535



2-in-1 Soldering/Desoldering Station



Soldering & Desoldering in one unit

Aven's 2-in-1 Soldering/Desoldering Station provides the flexibility of soldering and desoldering in one compact unit. Suitable for manual mounting and reworking of SMD components, audio equipment, RC hobbies and more.

Includes a vacuum-pump desoldering gun to melt and remove solder. Simply press the trigger to suck the molten solder into the barrel.

Comes complete with a deluxe stand to store the soldering iron and desoldering gun when not in use. This stand includes a cleaning sponge and a cleaning coil.

Soldering Iron	
Voltage	24V
Power Consumption	MAX130W
Temperature Range	160-480 C

Desolderin	ng Gun
Voltage	24V
Power Consump- tion	MAX 200W

Central Unit	
Power Supply	110-130V
Power Consumption	184W
Fuse	3.15A

Features

- Adjustable temperature from 160° 480° C
- Dual LCD displays ensures easy and reliable temperature control
- Long life soldering/desoldering tips
- Vacuum pump desoldering tool with excellent thermal recovery easily removes solder from PCB
- Ceramic heater
- Heats up rapidly
- Deluxe stand to store soldering iron and desoldering gun. Includes a cleaning sponge and coil.



Desoldering Wick 2.5mm with Dispenser Wheel



Convenient and Easy To Use

Aven's 2.5mm Desoldering Wick with Dispenser Wheel is designed with soldering applications in mind. The ergonomic wick case fits comfortably in all hand sizes and features a thumb wheel for easy dispensing and retracting of the wick. Includes four replacement spools (five total spools), 1.5m of thread each.

Desoldering Wick 2.5mm with Dispenser Wheel	
Item #	17545
Weight	0.5lbs
Dimensions (dispenser)	3.9375 x 1.8125 x 1.8125
Length (wick)	1.5m
Width (wick)	2.5mm



Rotating thumb wheel to retract wick thread





Quickly removes excess solder



Includes four additional spools

1.5m of thread per spool

- Includes four replacement desoldering wick spools
- Quickly absorbs excess solder
- Despenser wheel prolongs life of the wick by keeping the thread sealed
- Built-in thumb wheel designed to provide easy control of the wick



Aven 1.5mm, 2mm, and 2.5mm desoldering wicks also available



Soldering & Desoldering

Benchtop Accessories & Soldering Aids

Benchtop Smoke Absorber

- Removes flux fumes from soldering work bench ►
- Fumes absorbed by carbon activated filter
- Fan is quiet and will not add significant noise to your workspace
- Stand allows the smoke absorber to be adjusted to varying angles



Adjustable Circuit Board Holder

Retractable to accommodate various board sizes up to 198mm wide and up to 4mm thick

Adjustable Circuit Board Holder

Helping Hands Magnifier with Clamps

Heavy-duty cast iron base provides stability

Useful auxiliary tool in soldering, model making and other

Magnifier can be swiveled and fixed to desired position

Two alligator spring clips that hold work firmly in any position

- Clamps allow PCB to rotate 360°
- **Rigid metal structure**

Product ID

hobbies

or angle

17010

- Rubber feet of the base ensure stability
- Ideal for clamping PCB, for soldering/ desoldering or rework

Description



26000

Product ID	Description
17701	Benchtop Smoke Absorber
17701F	Carbon Activated Filter 3pcs with PVC Bag

Aven Heat Guns

- Heats Up Quickly
- 3 Nozzle Attachments For a Variety of Applications
- **Durable Construction** ►
- High and Low Airflow Settings ►
- Compact, Ergonomic Design
- Adjustable Heat Control



17602

Product ID	Description
17601	Heat Gun 1500W with Adjustable Temperature Control
17602	Heat Gun 1500W with Digital Temperature Control

Solder Reel Stand

- Allows solder wire to be drawn out smoothly
- Compact design keeps work benches neat and orderly
- Holds up to 1kg (approximately 2lbs.) roll of solder wire
- Solder reel stand is the ideal solution for easy

Product ID Description

17560 Solder Reel Stand

Soldering Iron Stands

- Ideal for holding pencil type soldering ► irons
- Weighted metal base features built in sponge trav
- Designed to withstand everyday industrial use
- Two per pack

Product ID Description

17533 Solder Iron Stands

Soldering Iron Stand with Soft Coiled Brass

Tip Cleaner

- Replaceable soft coiled brass tip cleaner
- Cleans tip without messy wet sponges
- Uses low abrasive brass, no water needed
- Works with any tip
- Lengthens tip life by reducing oxidation
- Sturdy heavy duty stand with built in tip cleaner

Product ID	Description
17530	Soldering Iron Stand with Soft Coiled Brass Tip Cleaner
17530-TC	Soft Coiled Brass Tip Cleaner

AVEN, INC. | 4330 VARSITY DRIVE | ANN ARBOR, MI 48108

Product ID Description

5-Piece Solder Aid Kit 17523

Soldering Aids 6-Pc Kit

- Kit includes six of the most popular soldering aids
- Specialized tools to remove components from
- PCBs and clean holes choked with solder Brushes designed for cleaning surface
- contamination Scrapers remove shielding from wires and rust from metal to improve adhesion of solder

Product ID	Description
17524	Soldering Aids 6-Pc Kit



17523

17524

17012



Third Hand w/Tweezers

2x magnifier is removable

- Stainless steel construction
- Heavy-duty base provides excellent
- Designed as a "third hand" allowing both
- Multi-position swivel clamps permit holding of piece at any angle

Product ID Description

17012 Third Hand w/Tweezers

5-Piece Solder Aid Kit

- Popular solder aids
- Tweezer included Head sink included
- 5-piece set provides the right tool at the right time





17533

17530

- - stability and prevents movement

26000

hands free for soldering