


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|---|---------|-------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 4/27/11 | D.FRISIELLO |
| B | ECN 5496: ADDED L-COM LOGO, NOTE 3 | 5/9/11 | D.FRISIELLO |
| C | ECN 5631: REVISED NOTE 3 TO 1AP14-011, REMOVED MIDDLE HOLES | 7/25/11 | D.FRISIELLO |



NOTES:

1. MATERIAL: .06 THICK COLD ROLLED STEEL.
2. FINISH: MORTON'S FLAT BLACK POWDER COAT #10-7011.
3. SILKSCREEN PER 1AP14-011.DXF, COLOR: WHITE
4. ALL INSIDE RADII .031 UNLESS OTHERWISE SPECIFIED.
5. BREAK ALL SHARP EDGES AND DEBURR ALL HOLES.
6. ALL DIMENSIONS, TOLERANCES, AND THREAD SIZES ARE AFTER FINISH IS APPLIED.
7. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

RoHS Compliant ✓

| | | | | |
|---|--|---------|---|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY D.FRISIELLO | 4/27/11 | | |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | CHECKED BY M.MARTINEZ | 4/27/11 | CATEGORY RACK PANEL | |
| | APPROVED BY M.MARTINEZ | 4/27/11 | PRODUCT DESCRIPTION 1U X19" RACK PANEL, BLANK | |
| PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | SIZE A | FSCM NO. 43321 |
| | COLOR VARIATIONS MAY OCCUR | | DWG. NO. PR175BLK | REV. C |
| | SCALE: NONE | | CAD FILE: PR175BLK.SLDDRW | |
| | | | SHEET 1 OF 1 | |