SIEMENS

Datasheet 6ED1052-2FB00-0BA8

LOGO! 230RCEO, LOGIC MODULE, PU/I/O: 230V/230V/RELAY, 8DI/4DO; W/O DISPLAY, MEMORY 400 BLOCKS, EXPANDABLE, ETHERNET BIULD IN WEB-SERVER, DATALOG STANDARD MICRO SD CARD FOR LOGO! SOFT COMFORT V8 PREVIOS PROJECT USABEL

Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide

Supply voltage	
115 V DC	Yes
230 V DC	Yes
permissible range, lower limit (DC)	100 V
permissible range, upper limit (DC)	253 V
115 V AC	Yes
230 V AC	Yes

Time of day	
Time switching clocks	
• Number	8
• Power reserve	480 h

Digital inputs	
Number of digital inputs	8

Digital outputs	
Number of digital outputs	4; Relays
short-circuit protection	No; external fusing necessary

Changes preserved
© Copyright Siemens AG

Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	10 A

EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes

Degree and class of protection	
Degree of protection to EN 60529	
• IP20	Yes

Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
Developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes

Ambient conditions	
Operating temperature	
• Min.	0 °C
• max.	55 °C

Dimensions	
Width	71.5 mm
Height	90 mm
Depth	58 mm
last modified:	14.10.2014

Changes preserved
© Copyright Siemens AG