



The Leviton Load Center

The Future Made Current

Leviton is actively transitioning panels and breakers to a new version. Please refer to the final page of this document which includes a cross-reference list, as needed.



NEMA 1 - Indoor *Order Cover & Door Assembly separately

Amp Rating	# of Spaces/Circuits	Enclosure Catalog Number*	Flush/Surface Mount Cover & Door Assembly	
			Standard	with Observation Window
Main Breaker Factory Installed				
100	20	LP210-MB	LDC20	LDC20-W
125	20	LP212-MB	LDC20	LDC20-W
150	20	LP215-MB	LDC20	LDC20-W
200	20	LP220-MB	LDC20	LDC20-W
100	30	LP310-MB	LDC30	LDC30-W
125	30	LP312-MB	LDC30	LDC30-W
150	30	LP315-MB	LDC30	LDC30-W
200	30	LP320-MB	LDC30	LDC30-W
150	42	LP415-MB	LDC42	LDC42-W
200	42	LP420-MB	LDC42	LDC42-W
225	42	LP422-MB	LDC42	LDC42-W
200	66	LP620-MB	LDC66	LDC66-W
225	66	LP622-MB	LDC66	LDC66-W
Main Lugs Only				
225	20	LP222-ML	LDC20	LDC20-W
225	30	LP322-ML	LDC30	LDC30-W
225	42	LP422-ML	LDC42	LDC42-W
225	66	LP622-1L	LDC66	LDC66-W

* Please refer to cross-reference at end of this document for SKUs in transition



NEMA 3R - Outdoor

Amp Rating	# of Spaces/Circuits	Catalog Number
Main Breaker Factory Installed		
100	20	LP210-3B
125	20	LP212-3B
150	20	LP215-3B
200	20	LP220-3B
125	30	LP312-3B
150	30	LP315-3B
200	30	LP320-3B
150	42	LP415-3B
200	42	LP420-3B
225	42	LP422-3B
Main Lugs Only		
225	20	LP212-3L
225	30	LP320-3L
225	42	LP422-3L

* Please refer to cross-reference at end of this document for SKUs in transition



Meter Main, UG/OH Service Entrance with Distribution Section and Feed-Through Lugs

Amp Rating	# of Spaces/Circuits	Catalog Number	Bypass	Cover
150	8	LP815-TMC*	None	Ringless**
200	8	LP820-TMC*	None	Ringless**
150	8	LP815-HMC	Horn	Ringless
200	8	LP820-HMC	Horn	Ringless
150	8	LP815-LMC*	Lever	Ringless
200	8	LP820-LMC*	Lever	Ringless
150	8	LP815-5MC*	Lever with 5th Jaw Installed	Ringless
200	8	LP820-5MC*	Lever with 5th Jaw Installed	Ringless
150	8	LP815-RMC	None	Ring Type
200	8	LP820-RMC	None	Ring Type

* Meter Equipment Group (MEG) Approved

**Includes internal trough to enable branch wiring through top of enclosure



Meter-Load Center Combination, All-in-one, Surface mount, UG Service Entrance, EUSERC

Amp Rating	# of Spaces	Catalog Number	Bypass	Cover
100	30	LP310-MC	None	Ring Type
125	30	LP312-MC	None	Ring Type
150	30	LP315-MC	None	Ring Type
200	30	LP320-MC	None	Ring Type
200	42	LP420-MC	None	Ring Type
225	42	LP422-MC	None	Ring Type

* Please refer to cross-reference at end of this document for SKUs in transition



Meter-Load Center Combination, All-in-one, Semi-flush mount, UG/OH* Service Entrance, EUSERC

Amp Rating	# Spaces/ circuits	Catalog Number	Bypass	Cover
Main Breaker Factory Installed				
125	12	LP112-SR	None	Ring Type
200	12	LP120-SR	None	Ring Type
125	30	LP312-SR	None	Ring Type
200	30	LP320-SR	None	Ring Type
200	40	LP420-SR	None	Ring Type
225	40	LP422-SR	None	Ring Type
Main Lugs Only				
225	12	LP120-SRL	None	Ring Type

* Overhead feed requires Overhead Tunnel Kit accessory

** Please refer to cross-reference at end of this document for SKUs in transition



Main Breakers

Amp Rating	Catalog Number
100	LM100-T
125	LM125-T
150	LM150-T
175	LM175-T
200	LM200-T
225	LM225-T



MB Conversion Kit for Semi-flush Mount Meter-Load Center Combinations

Amp Rating	Catalog Number
100	LMB10-T
125	LMB12-T
150	LMB15-T
175	LMB17-T
200	LMB20-T
225	LMB22-T

* Please refer to cross-reference at end of this document for SKUs in transition

BRANCH CIRCUIT BREAKERS

10kA short-circuit rating*

Standard



Amp Rating	1-Pole 120V	2-Pole 120/208V 120/240V
15	LB115-T	LB215-T
20	LB120-T	LB220-T
25	LB125-T	LB225-T
30	LB130-T	LB230-T
35	-	LB235-T
40	-	LB240-T
45	-	LB245-T
55	-	LB255-T
60	-	LB260-T
70	-	LB270
80	-	LB280
90	-	LB290
100	-	LB200
110	-	LB211
125	-	LB212

AFCI



Amp Rating	1-Pole 120V	2-Pole 120V/240V
15	LB115-AFT	LB215-AF
20	LB120-AFT	LB220-AF

GFCI - 5 mA Ground-Fault Protection of Personnel



Amp Rating	1-Pole 120V	2-Pole 120/208V 120/240V
15	LB115-GFT	LB215-G
20	LB120-GFT	LB220-G
25	LB125-GFT	LB225-G
30	LB130-GFT	LB230-G
40	-	LB240-G
50	-	LB250-G
60	-	LB260-G

GFPE - 30 mA Ground-Fault Protection of Equipment



Amp Rating	1-Pole 120V	2-Pole 120V/240V
15	LB115-EPT	LB215-EP
20	LB120-EPT	LB220-EP
25	LB125-EPT	LB225-EP
30	LB130-EPT	LB230-EP
40	-	LB240-EP
50	-	LB250-EP
60	-	LB260-EP

AFCI/GFCI - Dual Function



Amp Rating	1-Pole 120V
15	LB115-DFT
20	LB120-DFT

Surge Protection



Description	Catalog Number
15A Surge Protective Device and Circuit Breaker 120/240V	LSPD1-T
20A Surge Protective Device and Circuit Breaker 120/240V	LSPD2-T

*Series Rated 22kA with Leviton Main Breaker; see Series Ratings Tables for additional Ratings

Smart, 10kA short-circuit rating*

Smart Standard



Amp Rating	1-Pole 120V	2-Pole 120/240V
15	LB115-S	LB215-S
20	LB120-S	LB220-S
25	LB125-S	LB225-S
30	LB130-S	LB230-S
35	-	LB235-S
40	-	LB240-S
45	-	LB245-S
50	-	LB250-S
60	-	LB260-S
70 - 125	-	LSBMA**

Smart AFCI



Amp Rating	1-Pole 120V
15	LB115-AS
20	LB120-AS

Smart AFCI/GFCI - Dual Function



Amp Rating	1-Pole 120V
15	LB115-DS
20	LB120-DS

Smart GFCI - 5 mA Ground-Fault Protection of Personnel



Amp Rating	1-Pole 120V	2-Pole 120/240V
15	LB115-GS	LB215-GS
20	LB120-GS	LB220-GS
25	LB125-GS	LB225-GS
30	LB130-GS	LB230-GS
40	-	LB240-GS
50	-	LB250-GS
60	-	LB260-GS

Smart GFPE - 30 mA Ground-Fault Protection of Equipment



Amp Rating	1-Pole 120V	2-Pole 120/240V
15	LB115-ES	LB215-ES
20	LB120-ES	LB220-ES
25	LB125-ES	LB225-ES
30	LB130-ES	LB230-ES
40	-	LB240-ES
50	-	LB250-ES
60	-	LB260-ES

**Smart Breaker Metering Accessory; CT-based design, cannot remotely update or trip breaker

Catalog Number	Description
LDATA	Smart Breaker Data Hub

The LDATA Smart Hub collects data from smart circuit breakers and transmits it securely to the router

* Please refer to cross-reference at end of this document for SKUs in transition

*Series Rated 22kA with Leviton Main Breaker; see Series Ratings Tables for additional Ratings

ACCESSORIES

Locking & Latching Devices



Description	Catalog Number
Handle padlock device for branch circuit breakers	LBHPL
Handle padlock device for main circuit breakers	LMHPL
Door locking latch kit for indoor load centers	LDRLK
Door latch kit without lock for indoor load centers	LDRLA

Lugs, Ground and Neutral Bar Kits



Description	Catalog Number
Field-installable main lugs, 3 - 300	LL630
Ground lug, 6 - 2/0	LLGND
Neutral lug, 6 - 300	LLNTL
Phase/neutral load side lug, 14 - 4 (qty. 6)	LLPHN
Ground bar kit, 11 positions, 14 - 4	LGBKT
Neutral bar kit, 14 - 1/0	LNBKT
Neutral lug, 4 - 2/0	LL420
Feed through lug accessory	LFTLA

Outdoor & Meter Combination Load Center Accessories



Description	Catalog Number
Conduit hub, 1"	LHUB1
Conduit hub, 2"	LHUB2
Conduit hub, 2 1/2"	LHUB2
Closing plate	LCLPT
5th Jaw for standard meter sockets	L5JAW
5th Jaw with neutral for lever bypass meter socket	L5JAW-N
Ground connector	LGDMC
Sealing ring	LRING

Overhead Tunnel Kits: for Semi-flush Mount Meter-Load Center Combinations

Description	Catalog Number
For 12-space Panel	LOTK1
For 30-space Panel	LOTK3
For 40-space Panel	LOTK4

Miscellaneous



Description	Catalog Number
Manual transfer interlock kit	LITLK
Breaker Hold Down kit	LBHDK
Angle iron bracket for flush mount load centers	LBRKT
Circuit Identification Sticker (qty. 5)	LSTIK
Filler Plates (qty. 10)	LFPLT
Terminal covers for main circuit breaker	LTCVR
Bonding strap kit	LPBSK
Cover screw kit (qty. 6)	LDCSK
GFCI-protected outlet labels, pack of 1000	GFLBL-LBL
EMERGENCY DISCONNECT labels, pack of 10	LDSCS

LEVITON LOAD CENTER CROSS-REFERENCE

LOAD CENTERS

NEMA 1 - INDOOR WITH MAIN BREAKER	
Current Cat. No.	New Cat. No.
LP210-MB	LP210-BPD
LP212-MB	LP212-BPD
LP215-MB	LP215-BPD
LP220-MB	LP220-BPD
LP310-MB	LP310-BPD
LP312-MB	LP312-BPD
LP315-MB	LP315-BPD
LP320-MB	LP320-BPD
LP415-MB	LP415-BPD
LP420-MB	LP420-BPD
LP422-MB	LP422-BPD
LP620-MB	LP620-BPD
LP622-MB	LP622-BPD

NEMA 1 - INDOOR WITH MAIN LUGS	
Current Cat. No.	New Cat. No.
LP212-ML	LP222-LPD
LP320-ML	LP322-LPD
LP422-ML	LP422-LPD
LP622-1L	LP622-LPD

NEMA 3R - OUTDOOR WITH MAIN BREAKER	
Current Cat. No.	New Cat. No.
LP210-3B	LR210-BDD
LP212-3B	LR212-BDD
LP215-3B	LR215-BDD
LP220-3B	LR220-BDD
LP312-3B	LR312-BDD
LP315-3B	LR315-BDD
LP320-3B	LR320-BDD
LP415-3B	LR415-BDD
LP420-3B	LR420-BDD
LP422-3B	LR422-BDD

NEMA 3R - OUTDOOR WITH MAIN LUGS	
Current Cat. No.	New Cat. No.
LP212-3L	LR222-LDD
LP320-3L	LR322-LDD
LP422-3L	LR422-LDD

NEMA 3R - SURFACE MOUNT METER MAIN WITH MAIN BREAKER	
Current Cat. No.	New Cat. No.
LP815-TMC	LS815-BTD
LP820-TMC	LS820-BTD
LP815-HMC	LS815-BHD
LP820-HMC	LS820-BHD
LP815-LMC	LS815-BLD
LP820-LMC	LS820-BLD
LP815-5MC	LS815-B5D
LP820-5MC	LS820-B5D
LP815-RMC	LS815-BRD
LP820-RMC	LS820-BRD

NEMA 3R - SURFACE MOUNT ALL-IN-ONE WITH MAIN BREAKER	
Current Cat. No.	New Cat. No.
LP310-MC	LJ310-BED
LP312-MC	LJ312-BED
LP315-MC	LJ315-BED
LP320-MC	LJ320-BED
LP420-MC	LJ420-BED
LP422-MC	LJ422-BED

NEMA 3R - SEMI FLUSH MOUNT ALL-IN-ONE WITH MAIN BREAKER	
Current Cat. No.	New Cat. No.
N/A	LG110-BED
LP112-SR	LG112-BED
LP120-SR	LG120-BED
N/A	LG310-BED
LP312-SR	LG312-BED
LP320-SR	LG320-BED
LP420-SR	LG420-BED
LP422-SR	LG422-BED

NEMA 3R - SEMI-FLUSH MOUNT ALL-IN-ONE WITH MAIN LUGS	
Current Cat. No.	New Cat. No.
LP120-SRL	LG122-LED

MAIN BREAKERS

MAIN BREAKERS	
Current Cat. No.	New Cat. No.
LM100	LM100-T
LM125	LM125-T
LM150	LM150-T
N/A	LM175-T
LM200	LM200-T
LM225	LM225-T

Main Breaker Conversion Kit for Semi-Flush All-In-One Load Centers	
Current Cat. No.	New Cat. No.
LMB10	LMB10-T
LMB12	LMB12-T
LMB15	LMB15-T
N/A	LMB17-T
LMB20	LMB20-T
LMB22	LMB22-T



Leviton Manufacturing Co., Inc.

Tech Line: 1-800-824-3005

Mon-Fri 8am-10pm EST, Saturday 9am-7pm EST, Sunday 9am-5pm EST

For 24/7 product support visit www.leviton.com/support

Visit our Website at: www.leviton.com/loadcenter

© 2022 Leviton Manufacturing Co., Inc. All rights reserved.
All trademarks are the property of their respective owners.

