



LOCK NUT  
OPTIONAL  
ADD: L



CATALOG NUMBER	SEALING RANGE	BODY BORE
RSR-400	NO HOLES	1.320
RSR-406	.250 - .375	1.320
RSR-410	.500 - .626	1.320
RSR-411	.562 - .687	1.320
RSR-412	.625 - .750	1.320
RSR-413	.688 - .812	1.320
RSR-414	.750 - .875	1.320
RSR-415	.812 - .937	1.320
RSR-416	.875 - 1.000	1.320
RSR-417	.937 - 1.062	1.320
RSR-418	1.000 - 1.125	1.320
RSR-419	1.062 - 1.187	1.320
RSR-420	1.125 - 1.250	1.320
RSR-422	1.250 - 1.375	1.320
RSR-423	1.375 - 1.450	1.320

ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSR-400-B	BODY	ALUMINIUM	1
2	SRB-506 THRU SRB-523	BUSHING	NEOPRENE	1
3	SW-500	WASHER	C.R.S. ZINC PLATED	1
4	RSR-500-N	NUT	ALUMINIUM	1
5	LN-125	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	<b>REMKE</b> <b>REMKE INDUSTRIES</b> 310 CHADDICK DR, WHEELING, IL. 60090	
A	4/22/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1° BEND ± 1° ONE PLACE DECIMAL ± .015 TWO PLACE DECIMAL ± .010 THREE PLACE DECIMAL ± .005	JCN	4/13	TITLE: <b>RSR-400 SERIES</b>	
			INTERPRET GEOMETRIC TOLERANCING PER:	DRAWN CHECKED ENG APPR. MFG APPR. Q.A.		SIZE <b>A</b> DWG. NO. <b>RSR-400 ASSEMBLY</b>	
			MATERIAL <b>ALUMINIUM</b>	<b>PROPRIETARY AND CONFIDENTIAL</b> THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.		SCALE: 1:1	
			FINISH			SHEET 1 OF 1	
			DO NOT SCALE DRAWING				