

Important Note

The U329-000-10G is intended for data transfer purposes only. It will not support video transmission and should not be used for this purpose.

USB-C to USB-A Adapter (F/M), USB 3.2 Gen 2 (10 Gbps)

MODEL NUMBER: **U329-000-10G**



Connects a USB-C device to the USB-A port on your computer, laptop or USB hub.

Features

Connects a USB-C Device to Your Computer or Laptop's USB-A Port

The U329-000-10G lets you connect a device with USB-C capabilities, such as a smartphone, tablet or hard drive, to the USB-A port on your PC, laptop or USB hub. The palm-sized adapter fits to the end of a USB-C cable, giving you maximum flexibility and more opportunities to share data or charge your phone using a USB-A laptop or wall charger. Ideal for keeping up with newer smartphones and other devices that have a USB-C port and come with a USB-C cable.

Transfers Data at Fast USB 3.2 Gen 2 Speeds

This USB adapter supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps, which is twice as fast as USB 3.2 Gen 1 and 20 times faster than USB 2.0. It also produces up to 0.9A for charging and powering mobile devices. The U329-000-10G is backward compatible with previous USB generations, so you can continue using older devices while getting high-speed performance from new devices. *Note: The U329-000-10G is intended for transferring data. It is not capable of transmitting video.*

Ready to Use Right Out of the Package

The plug-and-play USB 3.2 Gen 2 adapter is specifically designed to accept USB-C and Thunderbolt 3 plugs from a wide variety of cables, hubs, hard drives, adapters and other compatible devices. It requires no software, drivers or external power. It is small enough to carry in your pocket, purse, briefcase or laptop bag, so you'll always be ready to connect wherever you are.

Specifications

OVERVIEW

Highlights

- Converts a male USB-C connector to a male USB-A connector
- Supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps for connecting hard drives and other data intensive tasks
- Produces 900mA (0.9A) for charging and powering phones and other mobile devices
- Backwards compatible with previous USB generations
- Plug and play with no external power or software required

Package Includes

U329-000-10G USB-C to USB-A Adapter (F/M)

UPC Code	037332282064
Device Compatibility	Amazon Kindle; Chromebook; Computer; Laptop; Phone; Tablet
Technology	USB; USB 3.x
Country/Region	Global
DATA	
Data Ports	USB C (FEMALE)
Data Ports Details	USB-C - USB 3.2 Gen 2 (10 Gbps)
INPUT	
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
CHARGING	
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
PHYSICAL	
Color	Black
Material of Construction	PVC, UL94V-0
Total Number of Ports	1
Shipping Dimensions (hwd / in.)	5.90 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	14.99 x 9.91 x 1.27
Shipping Weight (lbs.)	0.02
Unit Dimensions (hwd / in.)	0.310 x 0.630 x 1.100
Unit Dimensions (hwd / cm)	.78 x 16 x 2.8
Unit Dimensions (hwd / mm)	7.8 x 16 x 28
Unit Packaging Type	Polybag
Unit Weight (kg)	0
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	900MA Downstream Power for Connected USB-C Devices

CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
Data Transfer Rate	10 Gbps
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55024; EN 55032; UL 94
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty