

## HAR SERCOS III Typ C 4xAWG22/7 trail 50m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0147
Specification	HAR SERCOS III Typ C 4xAWG22/7 trail 50m
HARTING eCatalogue	<a href="https://b2b.harting.com/09456000147">https://b2b.harting.com/09456000147</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Description of the cable	Flame retardant
	Halogen-free
	UV resistant
	Oil resistant
Printing on cable	HARTING SERCOS III CAT5e * 22AWG (SHIELDED) (UL)E333432 CMX 75 °C VERIFIED CAT 5E PATCH CABLE FRNC* 094560001010200 „sequential length in meters“ „internal lot number“

### Version

Cable length	50 m
Number of cores	4
Core structure	4x AWG 22/7

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +70 °C unmoved
	-20 ... +60 °C moved
Cable diameter	6.3 ... 6.7 mm
Minimum bending radius	5x Cable diameter (repeated bending)
	3x Cable diameter (singular bending)



Pushing Performance  
 Since 1945

## Technical characteristics

Drag chain compatible	Yes
Bending cycles	≥ 3.000.000 & traversing distance ≤ 0.2 m & speed ≤ 4 m/s & acceleration ≤ 4 m/s <sup>2</sup>
Tensile strength	≤150 N
Test voltage U <sub>r.m.s.</sub>	2 kV Wire / wire / shielding
Coupling attenuation @ 20 °C / 100 MHz	20 mΩ/m
Conductor resistance @ 20 °C	≤120 Ω/km
Insulation resistance @ 20 °C	≥500 MΩ x km
Impedance @ 100 MHz	100 Ω ±5 %

## Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Red
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Specifications	ISO/IEC 11801 EN 50173 IEC 24702 EN 50173-3 IEC 61918 EN 50288-2-1 IEC 61156-5 IEC 60332-1-2 Flame retardancy EN 60811-2-1 Oil resistance
UL / CSA	UL 444 DUZX.E333432 CSA-C22.2 No. 214 DUZX7.E333432
Standards	SERCOS III Type C

## Commercial data

Packaging size	1
Net weight	2,966 g
Country of origin	Germany



**Pushing Performance**  
Since 1945

## Commercial data

European customs tariff number	85444290
GTIN	5713140273504
eCl@ss	27061801 Data and communication cable (copper)

---