




Cable Glands Accessories

Multi-Hole Cable Gland Inserts



Multi-Hole Cable Gland Inserts | IP65 Rating



Mencom Multi-Hole Cable Gland Inserts will allow the user to use one cable gland for multiple wires, cables, or tubes. The inserts fit into the Mencom "MCG" or "PCG" cable glands, and will seal to IP65.

Part Number	# of Holes	Diameter of Holes mm (inches)	Fits Into	
PG09-0x0	0	None	MCG-09 MCG-09R MCG-3/8 MCG-3/8R	PCG-09 PCG-09-B PCG-09R PCG-09R-B
PG09-2x3	2	3 (0.118)		
PG09-2x3.5	2	3.5 (0.138)		
PG09-3x2	3	2 (0.079)		
PG09-3x3.5	3	3.5 (0.138)		
PG09-4x2	4	2 (0.079)		
PG09-4x3	4	3 (0.118)		
PG11-0x0	0	None	MCG-11 MCG-11R PCG-11 PCG-11-B PCG-11R PCG-11R-B PCG-3/8	PCG-3/8-B PCG-3/8R PCG-3/8R-B PCG-M16 PCG-M16-B PCG-M16R PCG-M16R-B
PG11-2x3	2	3 (0.118)		
PG11-2x4	2	4 (0.157)		
PG11-2x4.5	2	4.5 (0.177)		
PG11-2x5	2	5 (0.197)		
PG11-3x3	3	3 (0.118)		
PG11-3x4	3	4 (0.157)		
PG11-3x5	3	5 (0.197)		
PG11-4x3	4	3 (0.118)		
PG11-7x2.7	7	2.7 (0.107)		
PG13.5-0x0	0	None	MCG-13.5 MCG-13.5R MCG-1/2 MCG-1/2R PCG-13.5 PCG-13.5-B PCG-13.5R	PCG-13.5R-B PCG-1/2X PCG-1/2X-B PCG-1/2Y PCG-1/2Y-B PCG-M20R PCG-M20R-B
PG13.5-2x4.5	2	4.5 (0.177)		
PG13.5-2x5	2	5 (0.197)		
PG13.5-2x6	2	6 (0.236)		
PG13.5-3x4	3	4 (0.157)		
PG13.5-3x5	3	5 (0.197)		

Inserts are intended for use with wires, cables, or tubes that have diameters that are within ±0.020" of the "hole diameter" listed. Inserts without holes allow the user to drill holes for low volume, custom applications. Inserts can be pre-installed in cable glands for orders of 100 or more. Order as follows:

Multi-Hole Insert
PG 11-3X3

Desired Cable Gland
MCG-11

Resulting Part Number
MCG-11-3X3

Cable Glands & Adapters

U