

Large Signal Tower, Bright Outdoors



Outstanding notification

- 20+ times brighter than conventional products*
- Loud, 92dB alarm

*Comparison between LGE red and LR10 red

Various lighting patterns

- Continuous on, flashing, triple flash, and motorless rotation
- Light dimming

High environmental performance and global compliance

- IP69K with enhanced dust and water resistance
- Conforms to various worldwide standards





Outdoor alerting




Status notification for control panels and industrial machinery



IP69K compliant. Ideal for food and pharmaceutical plants

How to Order


LR10 - 3 0 2 W J N W - RYG



M12 Connection



Reduces installation and replacement time.




1	Blinking Common	7	Power Supply
2	LED B	8	Power Supply
3	LED C	9	LED R
4	LED G	10	Buzzer
5	Common	11	Pattern 1 Common
6	LED Y	12	Pattern 2 Common

Product List

Model	Number of Tiers	Rated Voltage	Buzzer	Luminous Color
LR10-102WJNW-R/Y/G	1	24V DC	None	Red / Amber / Green
LR10-202WJNW-RY/RG	2			Red, Amber/Red, Green
LR10-302WJNW-RYG	3			Red, Amber, Green
LR10-402WJNW-RYGB	4			Red, Amber, Green, Blue
LR10-502WJNW-RYGBC	5			Red, Amber, Green, Blue, White
LR10-1M2WJNW-R/Y/G	1	100-240V AC	None	Red / Amber / Green
LR10-2M2WJNW-RY/RG	2			Red, Amber/Red, Green
LR10-3M2WJNW-RYG	3			Red, Amber, Green
LR10-4M2WJNW-RYGB	4			Red, Amber, Green, Blue
LR10-5M2WJNW-RYGBC	5			Red, Amber, Green, Blue, White
LR10-102WJBW-R/Y/G	1	24V DC	Yes	Red / Amber / Green
LR10-202WJBW-RY/RG	2			Red, Amber/Red, Green
LR10-302WJBW-RYG	3			Red, Amber, Green
LR10-402WJBW-RYGB	4			Red, Amber, Green, Blue
LR10-502WJBW-RYGBC	5			Red, Amber, Green, Blue, White
LR10-1M2WJBW-R/Y/G	1	100-240V AC	Yes	Red / Amber / Green
LR10-2M2WJBW-RY/RG	2			Red, Amber/Red, Green
LR10-3M2WJBW-RYG	3			Red, Amber, Green
LR10-4M2WJBW-RYGB	4			Red, Amber, Green, Blue
LR10-5M2WJBW-RYGBC	5			Red, Amber, Green, Blue, White
LR10-302WMMW-RYG	3	DC24V (M12 Connector)	None	Red, Amber, Green

Optional Parts



Mounting bracket



CAUTION

To ensure correct use of these products, read the "Instruction Manual" prior to use. Failure to follow all safeguards can result in fire, electric shock, or other accidents. Specifications are subject to change without notice.

PATLITE (U.S.A.) Corporation

www.patlite.com

●PATLITE and the PATLITE logo are either registered trademarks or trademarks of PATLITE Corporation in JAPAN and/or other countries.

O-BB05A | EN | 2303 A | PLUS