

Reshaping  
your world™

**NORTON**

SAINT-GOBAIN

**GEMINI®**

## MAKE THE RIGHT CHOICE MORE COMFORTABLE

Norton RightCut products offer the longest life and fastest cut with more stability and a narrower pass. Our upgraded Norton Gemini RightCut wheels are the best aluminum oxide option in the market for steel and ferrous metals.

The 100% aluminum oxide abrasive has been infused with a new bond technology and processing for a thinner wheel design and low kerf loss. Our exclusive new design will outlast and out cut competitive aluminum oxide blades.

### FEATURES & BENEFITS

- Thinner and Faster Cutting
  - Provides a clean, burr-free, quality cut
  - Ensures a precise, straight cut
  - Increases productivity
- Longer Lasting
  - Extends wheel usage for significant cost savings
- Easier to Use
  - Requires less pressure
  - Increases operator comfort

**Right  
Cut™**



[www.nortonindustrial.com](http://www.nortonindustrial.com)

THE **MUSCLE** BEHIND THE MACHINE®

**NORTON**

SAINT-GOBAIN



**NORTON**  
SAINT-GOBAIN

**GEMINI®**

**RightCut™**

GEMINI RIGHTCUT  
CUT-OFF WHEELS

## The All New General Purpose RightCut Cut-Off Wheels


Your operators will appreciate a comfortable cut as it quickly and easily slices through a variety of steels. You will appreciate how RightCut can cut your cost.

**No other aluminum oxide wheel has all this.**



### General Purpose Availability

SIZE (D x T x H)	25 PACK	BULK PACK	5 PACK
<b>Type 01/41</b>			
4 x .045 x 5/8	66243527956		
4-1/2 x .045 x 7/8	66252823602	66252841213	66252842160
5 x .045 x 7/8	66252823603	66252841214	66252842170
6 x .045 x 7/8	66252823604	66252841215	66252842175
7 x .045 x 7/8	66252832323		
<b>Type 27/42</b>			
4 x .045 x 5/8	66252842180		
4-1/2 x .045 x 5/8-11	66252842025		66252842161
4-1/2 x .045 x 7/8	66252842026	66253370065	
5 x .045 x 5/8-11	66252841939		
5 x .045 x 7/8	66252842036	66253370066	66252842171
6 x .045 x 5/8-11	66252830587		
6 x .045 x 7/8	66252842202	66253370067	66252842176
7 x .045 x 7/8	66252912626		
9 x 1/16 x 5/8-11	66253019115		



### Application Specific Availability

SIZE (D x T x H)	MAX. RPM	STD. PKG.	PART #
<b>STAINLESS/INOX</b>			
<b>Type 01/41 - RightCut Cut-Off</b>			
4-1/2 x .045 x 7/8	13,580	25	66252841997
5 x .045 x 7/8	12,225	25	66252841998
6 x .045 x 7/8	10,185	25	66252841999
7 x .045 x 7/8	8,600	20	66252842000
<b>Type 27/42 - RightCut Cut-Off</b>			
4-1/2 x .045 x 5/8-11	13,580	10	66252841913
4-1/2 x .045 x 7/8	13,580	25	66252841912
5 x .045 x 5/8-11	12,225	10	66252841915
5 x .045 x 7/8	12,225	25	66252841914
6 x .045 x 5/8-11	10,185	10	66252841917
6 x .045 x 7/8	10,185	25	66252841916
7 x .045 x 5/8-11	8,600	10	66252841919
7 x .045 x 7/8	8,600	20	66252841918
<b>3/32 STEEL/METAL</b>			
<b>Type 01/41 - RightCut Cut-Off</b>			
4-1/2 x .090 x 7/8	13,580	25	66252823599
5 x .090 x 7/8	12,225	25	66252823600
6 x .090 x 7/8	10,185	25	66252823601
<b>Type 27/42 - RightCut Cut-Off</b>			
4-1/2 x 3/32 x 5/8-11	13,580	10	66252841903
4-1/2 x 3/32 x 7/8	13,580	25	66252841940
5 x 3/32 x 5/8-11	12,225	10	66252841904
5 x 3/32 x 7/8	12,225	25	66252843587
6 x 3/32 x 5/8-11	10,185	10	66252841905
6 x 3/32 x 7/8	10,185	20	66252841906
7 x 3/32 x 5/8-11	8,600	10	66252841907
7 x 3/32 x 7/8	8,600	20	66252841908
<b>ALUMINUM</b>			
<b>Type 01/41 - RightCut Cut-Off</b>			
4-1/2 x .045 x 7/8	13,580	25	66252841994
5 x .045 x 7/8	12,225	25	66252841995
6 x .045 x 7/8	10,185	25	66252841996
<b>Type 27/42 - RightCut Cut-Off</b>			
4-1/2 x .045 x 7/8	13,580	25	66252841909
5 x .045 x 7/8	12,225	25	66252841910
6 x .045 x 7/8	10,185	25	66252841911

#### BEST

NORTON NorZon Plus RightCut

#### BETTER

NORTON BlueFire RightCut

#### GOOD

NORTON Gemini RightCut, NORTON Metal RightCut

### THE MUSCLE BEHIND THE MACHINE®

[www.facebook.com/NortonIndustrial](http://www.facebook.com/NortonIndustrial) | [www.youtube.com/NortonIndustrial](http://www.youtube.com/NortonIndustrial) | [www.nortonabrasives.com](http://www.nortonabrasives.com)

#### USA CUSTOMER SERVICE:

Toll Free Phone: 1 (800) 551-4413  
Toll Free Fax: 1 (800) 551-4416

#### CANADA CUSTOMER SERVICE:

Toll Free Phone: 1 (800) 263-6565  
Toll Free Fax: 1 (800) 561-9490

#### FORM #8520 REV. 04/15

© Saint-Gobain April 2015.

Norton, Gemini, and The Muscle Behind The Machine are registered trademarks; RightCut is a trademark of Saint-Gobain Abrasives.



**SAINT-GOBAIN**