

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TABLE 1


P/N	COLOR	LEGENDS (each)	"A" WIDTH +/- .062	MARKER PER CARD	STD. PKG. CARDS QTY.
PCM-0 thru PCM-99	WHITE	'0' thru '99' [1 ea.]	.25 [6.35]	36	25
PCM-100 thru PCM-202	WHITE	'100' thru '202' [1 ea.]	.36 [9.15]	25	25
PCM-A thru PCM-Z	WHITE	'A' thru 'Z' [1 ea.]	.25 [6.35]	36	25
PCM-A1 thru PCM-A4	WHITE	'A1', 'A2', 'A3', 'A4' [1 ea.]	.25 [6.35]	36	25
PCM-B1 thru PCM-B5	WHITE	'B1', 'B2', 'B3', 'B4', 'B5' [1 ea.]	.25 [6.35]	36	25
PCM-C1 thru PCM-C4	WHITE	'C1', 'C2', 'C3', 'C4' [1 ea.]	.25 [6.35]	36	25
PCM-E1 thru PCM-E3	WHITE	'E1', 'E2', 'E3' [1 ea.]	.25 [6.35]	36	25
PCM-F1 thru PCM-F4	WHITE	'F1', 'F2', 'F3', 'F4' [1 ea.]	.25 [6.35]	36	25
PCM-H1 thru PCM-H5	WHITE	'H1', 'H2', 'H3', 'H4', 'H5' [1 ea.]	.25 [6.35]	36	25
PCM-L1 thru PCM-L5	WHITE	'L1', 'L2', 'L3', 'L4', 'L5' [1 ea.]	.25 [6.35]	36	25
PCM-M1, PCM-M2	WHITE	'M1', 'M2' [1 ea.]	.25 [6.35]	36	25
PCM-P1 thru PCM-P3	WHITE	'P1', 'P2', 'P3' [1 ea.]	.25 [6.35]	36	25
PCM-R1 thru PCM-R5	WHITE	'R1', 'R2', 'R3', 'R4', 'R5' [1 ea.]	.25 [6.35]	36	25
PCM-S1 thru PCM-S5	WHITE	'S1', 'S2', 'S3', 'S4', 'S5' [1 ea.]	.25 [6.35]	36	25
PCM-T1 thru PCM-T9	WHITE	'T1', 'T2', 'T3', 'T4', 'T5', 'T6', 'T7', 'T8', 'T9' [1 ea.]	.25 [6.35]	36	25

TABLE 2

P/N	COLOR	LEGENDS (each)	"A" WIDTH +/- .062	MARKER PER CARD	STD. PKG. CARDS QTY.
PCM-X1 thru PCM-X4	WHITE	'X1', 'X2', 'X3', 'X4' [1 ea.]	.25 [6.35]	36	25
PCM-1L1 thru PCM-1L3	WHITE	'1L1', '1L2', '1L3' [1 ea.]	.36 [9.15]	25	25
PCM-2L1 thru PCM-2L3	WHITE	'2L1', '2L2', '2L3' [1 ea.]	.36 [9.15]	25	25
PCM-3L1 thru PCM-3L3	WHITE	'3L1', '3L2', '3L3' [1 ea.]	.36 [9.15]	25	25
PCM-4L1 thru PCM-4L3	WHITE	'4L1', '4L2', '4L3' [1 ea.]	.36 [9.15]	25	25
PCM-1T1 thru PCM-1T3	WHITE	'1T1', '1T2', '1T3' [1 ea.]	.36 [9.15]	25	25
PCM-3T1 thru PCM-3T3	WHITE	'3T1', '3T2', '3T3' [1 ea.]	.36 [9.15]	25	25

NOTES:

1. MILLIMETER ARE IN ( ).
2. CHARACTERS TO BE UNDERLINE: 99, 66, 9, 6, 86, 89, 68, 98, 16, 19, 61, 91, 60 and 90.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	10/11/16	RVU	SEWH	JHAC	ADD UNDER LINE TO 99, 66, 9, 6, 86, 89, 68, 98, 16, 19, 61, 91, 60, AND 90. ADD NOTE 2.	GAECN03662
2	8/5/10	RVU	SEWH	MSAD	.36 [9.15] WAS .25 [6.35]. 2 PLCS. 25 WAS 36. LEGEND, 202 WAS 200.	6109
1	6/18/10	RVU	SEWH	MSAD	ADD 201, & 202 TO PCM-100 THRU PCM-202.	6068
0	10/14/09	RVU	SEWH	MSAD	DRAWING RELEASE.	5859

TITLE		SOLID NUMBERS AND LETTERS PCM-* WIRE MARKER CARDS CUSTOMER DRAWING		
ITEM REVISION NAME		100295CA/07		
DATASET FILE NAME		100295CA_DC_C10796/07F		
MATERIAL:		 GMC54WS		
DRAWING NUMBER:		C10796		
DRAWN BY	DATE	CHK	SCALE	SIZE
RVU	10/14/09	JHAC	NTS	A

D101000DA/15