


PART



CUTOUT

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN [] ARE METRIC.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- MATERIAL:
FRAME - POLYPROPYLENE (PP)
BLOCK - TPE
- PROTECTION CLASS WHEN USED WITH CEG GROMMETS
NEMA 1,12
IP 54
- TEMPERATURE RANGE: -22 - 212 °F
- FLAMMABILITY: VO
- RoHS COMPLIANT
- COMPLIANCE: cURus
- UV RESISTANT
- WEIGHT: SEE TABLE



PART NUMBER	A	B	INSTALLATION HEIGHT in. (mm)	NUMBER OF OPENINGS			a	b	c	d	e	PART WEIGHT	PKG QTY
	in. (mm)	in. (mm)		SMALL	MEDIUM	LARGE	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	lbs. (g)	
CEST1-E12	5.83 (148)	2.28 (58)	0.59 (15)	12	-	-	4.41 (142)	1.42 (36)	2.56 (112)	0.63 (16)	0.22 (5.5)	0.203 (92)	1
CEST1-E9	5.83 (148)	2.28 (58)	0.59 (15)	8	1	-	4.41 (142)	1.42 (36)	2.56 (112)	0.63 (16)	0.22 (5.5)	0.2 (91)	1
CEST1-E8	5.83 (148)	2.28 (58)	0.59 (15)	6	2	-	4.41 (142)	1.42 (36)	2.56 (112)	0.63 (16)	0.22 (5.5)	0.205 (93)	1
CEST1-E4	5.83 (148)	2.28 (58)	0.59 (15)	-	4	-	4.41 (142)	1.42 (36)	2.56 (112)	0.63 (16)	0.22 (5.5)	0.216 (98)	1
CEST1-D8	4.76 (121)	2.28 (58)	0.59 (15)	8	-	-	3.39 (86)	1.42 (36)	2.03 (52)	0.63 (16)	0.22 (5.5)	0.18 (82)	1
CEST1-D7	4.76 (121)	2.28 (58)	0.59 (15)	6	1	-	3.39 (86)	1.42 (36)	2.03 (52)	0.63 (16)	0.22 (5.5)	0.176 (80)	1
CEST1-D3	4.76 (121)	2.28 (58)	0.59 (15)	-	3	-	3.39 (86)	1.42 (36)	2.03 (52)	0.63 (16)	0.22 (5.5)	0.172 (78)	1
CEST1-C6	3.98 (101)	2.28 (58)	0.59 (15)	6	-	-	2.56 (65)	1.42 (36)	1.63 (41)	0.63 (16)	0.22 (5.5)	0.154 (70)	1
CEST1-C5	3.98 (101)	2.28 (58)	0.59 (15)	4	1	-	2.56 (65)	1.42 (36)	1.63 (41)	0.63 (16)	0.22 (5.5)	0.15 (68)	1
CEST1-C2	3.98 (101)	2.28 (58)	0.59 (15)	-	2	-	2.56 (65)	1.42 (36)	1.63 (41)	0.63 (16)	0.22 (5.5)	0.16 (73)	1
CEST1-B4	2.91 (74)	2.28 (58)	0.59 (15)	4	-	-	1.81 (46)	1.42 (36)	1.14 (29)	0.63 (16)	0.22 (5.5)	0.13 (59)	1

PART NUMBER		SEE TABLE	
TITLE			
CEST1 Control Drawing			
CUSTOMER DRAWING			
ITEM REVISION NAME		00872EBB/00	
DATASET FILE NAME		00872EBB_DC/00A	
THIRD ANGLE PROJECTION			
MATERIAL		SEE NOTE 4	
DRAWING NUMBER		00872EBB - DC	
DRAWN BY	DATE	CHK	SCALE
SERH	9/12/2022	MDS	1:1
SHEET 1 OF 1			B

00A	9/12/2022	SERH	MDS	JADE	INITIAL RELEASE	124032/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

B-SIZE CUSTOMER