



- NOTES:
- IDENTIFICATION: LOCKING POWER CORDS
 - PART NO. SEE TABLE
 - PART SPECIFICATION:
RATING: C14/C13 - 10A / 250V AC
C20/C19 - 16A / 250V AC
CABLE: SJT AND H05VV-F (17AWG OR EQUIVALENT) 3 CONDUCTOR, 105°C
 - RoHS COMPLIANT.
 - COMPLIANCE APPROVALS:
CE, UL, VDE, TUV
 - PRIMARY DIMENSIONS ARE IN INCHES, SECONDARY DIMENSIONS ARE IN (MILLIMETERS)

PART NUMBER	"A"		"B"		DIM "L" (mm/IN)	"C" COLOR	DESCRIPTION
	TYPE	COLOR	TYPE	COLOR			
LPCA01-X	C14	RED	C13	BLACK	24"/609.6mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, RED
LPCA02-X	C14	RED	C13	BLACK	48"/1,219.2mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, RED
LPCA03-X	C14	RED	C13	BLACK	72"/1,828.8mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, RED
LPCA04-X	C14	RED	C13	BLACK	96"/2,438.4mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, RED
LPCA05-X	C14	RED	C13	BLACK	120"/3,048mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, RED
LPCA06-X	C14	BLUE	C13	BLACK	24"/609.6mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, BLUE
LPCA07-X	C14	BLUE	C13	BLACK	48"/1,219.2mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, BLUE
LPCA08-X	C14	BLUE	C13	BLACK	72"/1,828.8mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, BLUE
LPCA09-X	C14	BLUE	C13	BLACK	96"/2,438.4mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, BLUE
LPCA10-X	C14	BLUE	C13	BLACK	120"/3,048mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, BLUE
LPCA11-X	C14	BLACK	C13	BLACK	24"/609.6mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, BLACK
LPCA12-X	C14	BLACK	C13	BLACK	48"/1,219.2mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, BLACK
LPCA13-X	C14	BLACK	C13	BLACK	72"/1,828.8mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, BLACK
LPCA14-X	C14	BLACK	C13	BLACK	96"/2,438.4mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, BLACK
LPCA15-X	C14	BLACK	C13	BLACK	120"/3,048mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, BLACK
LPCB01-X	C20	RED	C19	BLACK	24"/609.6mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, RED
LPCB02-X	C20	RED	C19	BLACK	48"/1,219.2mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, RED
LPCB03-X	C20	RED	C19	BLACK	72"/1,828.8mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, RED
LPCB04-X	C20	RED	C19	BLACK	96"/2,438.4mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, RED
LPCB05-X	C20	RED	C19	BLACK	120"/3,048mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, RED
LPCB06-X	C20	BLUE	C19	BLACK	24"/609.6mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, BLUE
LPCB07-X	C20	BLUE	C19	BLACK	48"/1,219.2mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, BLUE
LPCB08-X	C20	BLUE	C19	BLACK	72"/1,828.8mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, BLUE
LPCB09-X	C20	BLUE	C19	BLACK	96"/2,438.4mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, BLUE
LPCB10-X	C20	BLUE	C19	BLACK	120"/3,048mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, BLUE
LPCB11-X	C20	BLACK	C19	BLACK	24"/609.6mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, BLACK
LPCB12-X	C20	BLACK	C19	BLACK	48"/1,219.2mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, BLACK
LPCB13-X	C20	BLACK	C19	BLACK	72"/1,828.8mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, BLACK
LPCB14-X	C20	BLACK	C19	BLACK	96"/2,438.4mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, BLACK
LPCB15-X	C20	BLACK	C19	BLACK	120"/3,048mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, BLACK

PLEASE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		DATE	PRINT
THE JOB WILL NOT PROGRESS WITHOUT BUYER APPROVAL. PLEASE DO NOT DELAY DELIVERY.			
TITLE			
LOCKING POWER CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME			
02416LPC/00			
DATASET FILE NAME			
02416LPC_DC/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: 1/16" ± 0.005"			
N/A			
DRAWING NUMBER			
02416LPC_DC			
DATE	BY	CHK	SCALE
04/08/2021	PJST	GLM	NTS
SHEET NUMBER			
SHT 1 OF 1			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	04/08/2021	PJST	GLM	JAWI	RELEASED TO PRODUCTION	02416LPC