

# CIRCUIT BREAKERS | MISCELLANEOUS ELECTRICAL

#### **Hinged Single-Pole Breaker Lockouts**

- · Hinged single-pole lockout with locking post design, locks lever in off position to isolate and prevent breaker use
- · Ideal where panel closure is preferred

Description	Qty.	Part No.
Hinged Single-Pole	3	44-810
Breaker Lockouts	100	44-1810

#### Universal 120/277V Breaker Lockouts

- · Use thumbscrew to clamp lockout securely onto switch tongue. then pull cover over thumbscrew and lock in place to prevent clamp from being loosened
- Blade design provides tighter grip with less torque on thumbscrew

Description	Qty.	Part No.
Single-Breaker Lockouts	3	44-809
Cleat for Single-Pole Breaker Lockouts	3	44-785
Single-Pole Breaker Lockouts	50	44-1809

#### 480/600V Single/Multi-Pole Breaker Lockouts

- · Use thumbscrew to clamp lockout securely onto switch tongue, then pull cover over thumb-screw and lock in place to prevent clamp from being loosened
- Blade design provides tighter grip with less torque on thumbscrew

Description	Qty.	Part No.
480/600V Single/ Multi-Pole Lockout	1	44-807
480/600V Single/Multi-Pole Lockouts	50	44-1807
Cleat for 480/600V Single/Multi-Pole Lockouts	2	44-786

#### Large Breaker Lockout

- Designed to lockout large 480/600V breaker switches up to 2-1/2 in. wide and 7/8 in. thick
- Easy to install no tools required

Description	Qty.	Part No.
Large Breaker Lockout	1	44-823

#### **Multi-Pole Breaker Lockout**

- · Works with most major multipole breakers with tie-bar type switches from major brands including GE, ITE Sylvania, Challenger, Bryant, Westinghouse, SQUARE D (2/3 poles) and General Switch Co.
- · Easy to install thumbscrew secures and locks tie bar in place; no cable ties or tools required

Description	Qty.	Part No.
Multi-Pole Breaker Lockout	1	44-783

# Oversized Circuit Breaker Lockout System Circuit Breaker Lockout System

- · Unique Lockout system for oversized 480/600V circuit breakers
- System can be permanently installed into an electrical panel putting all lockout items at the point of need
- · Easy installation of adhesive mounting rails no tools required
- Pegs in mounting rails mate with holes in locking arms for security of arm when lock is
- Red arms lock off, green arms lock on

Description	Qty.	Part No.
Oversized Circuit Breaker	,	44-822
System	1	44-022

#### **Circuit Breaker Lockouts**



- · Attaches securely to breaker with simple thumb turn and clamping handle
- · 44-956 is designed for breakers with wide or tall toggles
- 44-957 fits standard height and tie-bar
- The narrow profile permits side-by-side breaker lockout

Description	Part No.
6	44-956
Circuit Breaker Lockout	44-957

#### **Plug Lockouts**

- Accommodates a variety of electrical plug and cord sizes to prevent accidental
- connection or disconnection Durable plastic body resists wear,
- chemicals, and job-site abuse
- Accommodates cable ties or padlocks (with up to 3/8 in. shackles)

Description	Size (in.)	Part No.
100V	2 x 2 x 3-1/2	44-818
220/550V	3-1/4 x 3-1/4 x 7	44-819

### **Plug Lockouts**

- Plug lockout, 44-792 works with high and low voltage plugs up to 3 in. in diameter and 5-1/2 in. in length, up to 1-1/4 in. cord diameter
- Plug lockout, 44-973 works with 110V/220V plugs up to 1-3/4 in. in diameter and 2-1/2 in. in length, up to a 1/2 in. cord diameter

Description	Part No.
Plug Lockout	44-792
Plug Lockout	44-793

- Covers most 120V - 277V Clamp-on 44-768 including single-Snap-on and multi-pole configurations Makes use of unique lock rail system, providing the following benefits: Allows panel door to be closed even when
- lockouts are in place Accommodates multiple locks, facilitating group lockout activity without
- Keeps weight off the breakers, protecting delicate electrical components from
- Positions locks and tags outside the panel, making sure lockout activity is clearly visible to anyone in the area
- Cables are 2 ft. in length
- · Lockout devices constructed of high-impact Isoplast® polymers
- Lock rails made of durable Isoplast® polymers with acrylic adhesive backing
- **Snap-on** For use on Square D NQO and other breakers that have a hole in the switch tongue. Align pins with hole and snap closed. Pins prevent switch from being thrown.
- Clamp-on For use on breakers that do not have a hole in the switch tongue, including multiple breakers with tie bars. Turn thumbscrew to clamp lockout securely onto switch, then snap the cover closed to prevent thumb wheel from being loosened.

Description	Qty.	Part No.
Clamp-on lockout for breakers without hole in the switch tongue, including multi-pole breakers with tie bars		44-764
Snap-on lockout for Square D NQO and other breakers with a hole in the switch tongue	1	44-768
4 in. Lock Rail with seven lock loops		44-769

Isoplast® is a registered trademark of Lubrizol Advanced Materials, Inc.

# **Electric Plug Lockout**

- Slides over cord prongs and locks in place to prevent cord from being plugged into an
- Cannot be removed without key
- Works on any 2- or 3-prong plug

Description	Part No.
Electric Plug Lockout	44-782

# MISCELLANEOUS ELECTRICAL | SIGNS | TAGS | LOCKS

#### **Wall Switch Lockouts**

- Universal Wall Switch Lockout locks out both toggle and Decora® wall switches
- · Universal design assures switch is locked on or off. Hinges open for unobstructed normal switch operation
- Standard wall switch lockout fits most wall-mounted single or three-way electrical switches

Description	Qty.	Part No.
Universal Wall Switch	1	44-772
Standard Wall Switch		44-789

Decora® is a registered trademark of Leviton Manufacturing Co., Inc.

#### **Cable Lockout**

 Unique hasp lockout device accepts up to six 9/32 in. padlocks and comes with a 6 ft. plastic-coated steel cable

Description	Part No.
Cable Lockout, 6 ft. cable	44-829

#### **Ball Valve Lockout Devices**

- · Best available method for locking out ball valves
- · Patented design fits most 44-847 major brand ball valves
- · Designed to lock in off position only
- · Complies with OSHA lockout standard

Valve Size (in.)	Max. Shackle Length	Material	Part No.
1/2 to 1-1/4		5.1	44-846
1-1/4 to 3	_	Polypropylene	44-847
1/4 to 1	0/72 :	Nylon	44-820
1-1/4 to 3	9/32 in.	Heavy Steel	44-821

#### **Adjustable Cable Lockout**

- · Infinitely adjustable safety hasp and cable
- Ideal for multiple circuit breaker panels and side-by-side gate valve lockouts
- · Feed the cable end through the points to be locked out, then back through the lockout body. Cinch it tight to remove any slack with the patented locking feature.
- Tough, flexible multi-stranded 6 ft., 1/4 in. diameter, steel cable is insulated with a clear vinyl coating
- · Tough, lightweight, dielectric thermoplastic body withstands chemicals; performs effectively in extreme conditions
- · Up to four workers can apply their personal safety locks
- Complete with high-visibility, reusable, write-on safety labels (English, French & Spanish). Identify the responsible person, then erase for the next job.

Description	Part No.
Adjustable Cable Lockout	44-808

#### **Gate Valve Lockouts**

44-824



- Unique rotating design allows for easy installation in confined space applications
- Each size rotates into itself and nests within the next larger size to save space
- · Up to four workers can apply their personal safety locks
- High-visibility permanent safety labels (English, French & Spanish) that can be written on then erased for the next job
- Tough, lightweight, dielectric thermoplastic bodies withstand chemicals and perform effectively in extreme conditions,
- Temperature range: -50°F (-46°C) to +350°F (177°C)

Valve Size	Qty.	Part No.
1 in. to 3 in.		44-824
2 in. to 5 in.	1	44-825
Set of 5 sizes (1 in. to 13 in.)		44-817

#### Safety Lockout Padlocks w/Key Retention

- Dedicated safety lockout device reduces confusion with other locks
- Complies with OSHA's "1-key,
- Non-conductive, lightweight body; four colors for easy identification
- Key retention ensures keys do not get lost while not in use
- · 1-1/2 in. shackle clearance; 1-1/2 in. wide lock with 1/4 in. shackle
- Keyed-alike, Master Lock® Keyed locks, 2nd key, additional colors available by special order

Bumper Color	Part No.
Blue	44-912
Black	44-914
Red	44-916
Yellow	44-918

Master Lock® is a registered trademark of Master Lock Company LLC.

#### **Lock Labels**

- Easy identification of employee's locks
- Write-on, vinvl labels with peel-off adhesive backing
- Polyester over laminate protects label

Description	Qty.	Part No.
Lock Labels	8 labels	44-898

#### **Steel Padlocks**

- Rustproofed, steel case with nickelplated shackle withstands abuse and environmental hazards
- Includes two keys
- 1-1/2 in. wide lock with 9/32 in. shackle diameter
- Keyed-alike and Master Lock® Keyed locks available by special order

Bumper Color	3/4 In. Shackle Part No.	2 In. Shackle Part No.
Blue	44-900	44-901
Red	44-906	44-907

Master Lock® is a registered trademark of Master Lock Company LLC

44-801

### **Safety Lockout Hasps**

- · Rustproofed, plated and vinyl-coated
- Labeled hasps feature anodized aluminum alloy construction for long-term durability

Jaw Diameter	Qty.	Part No.
1 in.	3	44-800
1-1/2 in.	2	44-801

## **Labeled Safety Lockout Hasps**

- Allow up to six workers to lock out a single energy source
- Permanent "Do Not Operate" labels accept pens, pencils, and permanent markers



Description	Color	Qty.	Part No.
	Blue	1	44-790
Do Not Operate	Red	1	44-791
	Red	50	44-1791

### **Heavy-Duty Lockout Tags**

- High-visibility lettering
- Laminated plastic tags have non-fade legends, resist corrosive and harsh environmental conditions
- · Vinyl tags are silk screened with a 7/8 in. metal grommet; fastener included
- Exceeds OSHA's 50-lb. pullout requirement
- Matte finish for easy writing surface

Heavy-Duty	Laminated
------------	-----------

neavy-Duty Laminateu			
Description		Qty.	Part No.
De Net Operate	STATE STATE	5/card	44-830
Do Not Operate	=	100/box	44-1830
Do Not Operate - Electricians at Wo	rk 🔐	5/card	44-832
Do Not Operate -	The second secon	5/card	44-833
(red striped background)	PENATE CONTRACTOR	100/box	44-1833

### **Economy Vinyl**

Description	Qty.	Part No.
Do Not Operate	25/bag	44-848
Do Not Operate - Electricians at Work	25/bag	44-843
Do Not Operate - (red striped background)	25/bag	44-849

# LOCKS | ACCESSORIES | KITS

#### Flash Protection Labels & Signs







44-893

44-894

**National Electric Code 110.16 Flash Protection:** Switchboards, panel boards, industrial control panels and motor control centers, in other than dwelling occupancies, that are likely to require examination, adjustment, servicing or maintenance while energized, shall be field marked to warn qualified persons of potential electric arc flash hazards. The marking shall be located so as to be clearly visible to qualified persons before examination, adjustment, servicing or maintenance of the equipment.

#### **NEC Arc Flash, Warning (Self-Sticking Polyester)**

Size	Qty.	Part No.
7.1/0 : 5 :	5	44-892
3-1/2 in. x 5 in.	100	44-892BK
5 in. x 7 in.	5	44-893
	5	44-894
7 in. x 10 in.	1	44-896

#### **NEC Arc Flash, Danger (Self-Sticking Polyester)**

Size	Qty.	Part No.
4 in. x 6 in.	5	44-895

#### Industrial Lockout/Tagout Kit

An industrial selection of lockout/tagout devices

Polypropylene plastic tool box resists oil and chemicals




	CD-GD SE	
Description		Part No.
Industrial Lockout/Tagout Kit		44-974
Kit Includes:	Qty.	Part No.
Hinged Single-Pole Breaker Lockouts	3	44-810
Universal 277V Breaker/Single Pole Lockouts	2	44-809
480/600V Breaker Lockout	1	44-807
Wall Switch Lockout	1	44-789
110V Small Plug Lockout	1	44-818
Ball Valve Lockout	1	44-820
1 in. Safety Lockout Hasps	2	44-800
Red Labeled Lockout	1	44-791
220/550V Plug Lockout	1	44-819
Striped Lockout Tags - Do Not Operate	10	44-849
Fuse Blockout	1	44-815
Fuse Blockout	1	K-7349
Gate Valve Lockout	1	44-824
Cleat for 277V Breaker Lockout	1	44-785
Cleat for 480/600V Breaker Lockout	1	44-786
Red Lockout Padlocks	4	44-916
Universal Multi-Pole Breaker Lockouts	2	44-783
Tool Box* (12 in. x 6 in. x 6 in.)	1	IA-3241

Quantities listed in kit description are for individual pieces, not carded packages. \*Tool Box color may vary.

#### Basic Lockout/Tagout Kit

A great selection of the most popular lockout/ tagout devices





Description		Part No.
Basic Lockout/Tagout Kit		44-970
Kit Includes:	Qty.	Part No.
Universal Multi-Pole Breaker Lockout	1	44-783
Wall Switch Lockout	1	44-789
1 in. Safety Lockout Hasp	1	44-800
480/600V Breaker Lockout	1	44-807
Universal 277V Breaker Lockout/Single Pole	1	44-809
Hinged Single-Pole Breaker Lockouts	2	44-810
110V Plug Lockout	1	44-818
Striped Lockout Tags - Do Not Operate	5	44-849
3/4 in. Red Padlock	1	44-906
Zipper Pouch	1	IA-3240

Quantities listed in kit description are for individual pieces, not carded packages.

#### Standard Lockout/Tagout Kit

Excellent selection of lockout/tagout devices, tags and locks for maintenance workers or contractors



Small nylon zipper pouch features belt loops and d-rings for easy attachment to belts, tool pouches, tool carts and more

·		
Description		Part No.
Standard Lockout/Tagout Kit		44-971
Kit Includes:	Qty.	Part No.
Hinged Single-Pole Breaker Lockouts	3	44-810
Universal 277V Breaker Lockouts/Single Pole	2	44-809
480/600V Breaker Lockout	1	44-807
Wall Switch Lockout	1	44-789
110V Small Plug Lockout	1	44-818
2 in. Shackle Red Padlocks	2	44-907
1 in. Safety Lockout Hasps	2	44-800
Lockout Tags - Do Not Operate	5	44-848
Striped Lockout Tags - Do Not Operate	5	44-849
Cleat for 277V Breaker Lockout	1	44-785
Cleat for 480/600V Breaker Lockout	1	44-786
Universal Multi-Pole Breaker Lockouts	2	44-783
Zipper Pouch	1	IA-3240

Quantities listed in kit description are for individual pieces, not carded packages.

#### **Lock Stations**





44-778

44-806

- Resilient polycarbonate material provides twice the heat resistance and quadruple the impact strength of typical stations
- Lockable cover prevents loss of valuable safety products and innovative hinge holds cover open for easy product selection

Description		Part No.
Four-Lock Station Kit		44-778
Kit Includes:	Qty.	Part No.
Four-Lock Station Board	1	_
Safety Padlocks, Red	4	44-916
Heavy-Duty Lockout Tags	12	_
1 in. Safety Lockout Hasps	2	44-800

Description		Part No.
Ten-Lock Station Kit		44-806
Kit Includes:	Qty.	Part No.
Safety Padlocks, Red	10	44-916
Heavy-Duty Lockout Tags	24	-
1 in. Safety Lockout Hasps	2	44-800



IDEAL INDUSTRIES, INC.

1375 Park Avenue, Sycamore, IL 60178, USA (815)-895-5181 (800)-435-0705 in USA

For complete sales office contact information, visit us at www.idealind.com

10/19 Printed in U.S.A. Form No. P-2734 ©2019 IDEAL INDUSTRIES. INC.