

Short Riser Panels for Hot/Cold Aisle Containment System - Standard 300 mm Rack Coolers, Set of 2

MODEL NUMBER: SRCTMTR300SH



Aisle Containment System keeps hot and cool air separated for better temperature control and equipment performance in hot aisle/cold aisle configurations.

Features

Riser Panels Designed for Standard-Width 300 mm In-Row Air Conditioners

These SmartRack® riser panels attach to the underside of the aisle containment system's upper support beams. This is to fill the gap between the telescopic beams (SRCTMTTLBM, sold separately) and your rack cabinets. All necessary installation hardware is included. The 3U SRCTMTR300SH measures 300 millimeters (12 inches) wide and 133 millimeters (5.2 inches) high to fit 45U/48U standard-width in-row air conditioners.

Aisle Containment System Manages Airflow for More Cooling Efficiency

Upon installation in your data center or server room, the modular, easy-to-assemble Aisle Containment System contains the air in a hot aisle or cold aisle, essentially creating a room within the aisle, while still keeping the aisle accessible. No costly contractor or HVAC specialist is required to install the system, which can be expanded or adapted to meet your needs. Assorted frame kits, beam kits, sliding double-door kits, roof panel kits and adapter riser panel kits (all sold separately) are necessary to assemble a hot or cold Aisle Containment System that accommodates the dimensions of your aisle and the rack enclosures within it.

Specifications

OVERVIEW	
UPC Code	037332274205
Accessory Type	Cooling Accessories
Aisle Containment System Component Type	Riser Panel
PHYSICAL	

Highlights

- Riser panels designed for standard-width 300 mm rack coolers
- Fill gap between rack coolers and aisle containment system's telescopic beams
- Minor assembly required using the included hardware

System Requirements

- SRCTMTTLBM Beam Kit
- SRCTMTFRM Frame Kit
- SRCTMTSDD Sliding Double-Door Kit
- SRCTMTCVR300 Static Roof Panel Kit

Package Includes

- (2) Riser panels
- (2) M6 x 16 screws
- (2) M6 hex nuts
- (4) M6 x 12 self-tapping screws
- (6) M6 washers
- Installation guide

Color	Black
Shipping Dimensions (hwd / in.)	7.87 x 14.56 x 3.93
Shipping Weight (kg)	1.70
Unit Dimensions (hwd / in.)	5.240 x 12.080 x 1.570
Rack Compatibility	300 mm (In-Row Cooler)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty