

FEATURES

- Ideal for a secure fastening using irregular or oversized holes
- Neat and tidy final finish
- Zinc coated
- Good protection against surface rust
- Recyclable
- Available in a wide range of sizes and drive types

RS PRO Hex Flange Screws

RS Stock No.: See Table Below



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Introducing the range of RS PRO Serrated Hex Flange Screws, a high-quality fastener solution for applications where a large bearing surface is required to evenly distribute a clamping force over an extended area. This makes them ideal for use with irregular or oversized holes like vehicle subframes. Each fastener is made from steel with a zinc coating, making them much more cost-effective than their stainless-steel counterparts, while offering a high level of protection against surface rust and oxidisation. Applications:

- Carpentry construction like decking, railings and small frames
- Metalwork and metal framing
- Building work and construction
- DIY

General Specifications

RS Stock Number	Approvals	Drive Type	Finish	Head Shape	Material	Thread Size	Stainless Steel Type	Length
2453220			Zinc Plated		Steel	10-24 X 5/24	Mild Steel	5/8
2453221			Zinc Plated		Steel	3/8-16	Mild Steel	2
2453222			Zinc Plated		Steel	5/16-18	Mild Steel	1
2453223			Zinc Plated		Steel	10-24 X 3/24	Mild Steel	3/4
2453226			Zinc Plated		Steel	3/8-16	Mild Steel	3/4
2453227			Zinc Plated		Steel	5/16-18	Mild Steel	3/4
2453228			Zinc Plated		Steel	1/4-20	Mild Steel	1 1/2
2453229			Zinc Plated		Steel	1/4-20	Mild Steel	3/4
2453230			Zinc Plated		Steel	5/16-18	Mild Steel	1 1/2
2453231			Zinc Plated		Steel	5/16-18	Mild Steel	1 3/4
2453232			Zinc Plated		Steel	3/8-16	Mild Steel	1 1/2
2453233			Zinc Plated		Steel	1/2-13	Mild Steel	1 3/4
2453236			Zinc Plated		Steel	1/2-13	Mild Steel	1 1/2
2453237			Zinc Plated		Steel	5/16-18	Mild Steel	1/2
2453238			Zinc Plated		Steel	3/8-16	Mild Steel	2 1/2
2453239			Zinc Plated		Steel	10-24 X 3/24	Mild Steel	3/4

Socket Screws



2453701	IFI 111	Hex	Zinc	Hex	Steel	#10/24	Mild Steel	1
2453727	IFI 111	Hex	Zinc	Hex	Steel	1/4-20	Mild Steel	1 1/4
2453734	IFI 111	Hex	Zinc	Hex	Steel	1/4-20	Mild Steel	2 1/2
2453845			Plain	Hex	Steel	1/4-20	Mild Steel	1/2
2454383	IFI 111		Zinc	Hex	Steel	10/32	Mild Steel	3/4
2454384	IFI 111		Zinc	Hex	Steel	10/32	Mild Steel	1
2454385	IFI 111		Zinc	Hex	Steel	10/32	Mild Steel	3/8
2454386	IFI 111		Zinc	Hex	Steel	10/32	Mild Steel	5/8
2454387	IFI 111		Zinc	Hex	Steel	1/4-20	Mild Steel	1
2454388	IFI 111		Zinc	Hex	Steel	10-24	Mild Steel	1/2
2454389	IFI 111		Zinc	Hex	Steel	3/8-16	Mild Steel	1
2454390	IFI 111		Zinc	Hex	Steel	5/16-18	Mild Steel	1 1/4
2454391	IFI 111		Zinc	Hex	Steel	3/8-16	Mild Steel	1 3/4
2454393	IFI 111		Zinc	Hex	Steel	1/4-20	Mild Steel	5/8
2454427	IFI 111		Zinc	Hex	Steel	5/16-18	Mild Steel	2
2454478	IFI 111		Zinc	Hex	Steel	3/8-16	Mild Steel	1 1/4
2454849	IFI 111	Hex	Zinc	Hex	Steel	10-32	Mild Steel	1/2

Classification

eCl@ss Version	
UNSPSC Version	