

Wall Mount Monitor Arm - Articulating Ergonomic VESA Wall Mount Monitor Arm - 20" (52cm) Long - Single Display up to 34" (30.9lb/14kg) - Swivel/Tilt/Rotate - Adjustable Screen Mount

Product ID: ARMWALLDSLP



Free up space with this wall-mount monitor arm and enjoy optimum viewing with the long dual-swivel extension arm. The premium design ensures smooth, effortless motion and makes it easy to re-position your display, to work in comfort or collaborate with others. The attractive silver finish complements your decor.

The wall-mount system is ideal for business, healthcare, financial or other settings, where you may want to share your screen, or for customer-facing interactive displays.

The wall-mount monitor arm extends a full 20.4" (52 cm) and has three swivel points, offering an extended range of motion. Move the dual-swivel arms left or right, to change your screen position. You can also adjust the swivel tension.

The robust aluminum design provides a stable wall-mount for your computer monitor or flat-screen TV up to 34". It's ideal for touch-screen stability. The universal display wall mount supports VESA mount monitors (75x75, 100x100) up to 30.9 lb. (14 kg) in weight.

Share your screen with ease. The display wall mount offers a full +180-degree/-180-degree pan, to move your screen left or right. It tilts freely +90/-15-degrees, to adjust the angle up or down. Rotate your screen for landscape or portrait viewing.

Push the swivel arm back to the wall, so your monitor sits just 5" (129 mm) from the wall when not in use.

The quick slide-and-click connections make the monitor wall mount easy to assemble and saves time when setting up multiple units.

The TAA compliant ARMWALLDSLP is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up space in business, commercial, industrial or office settings
- Share your screen with clients or visitors in office settings such as healthcare or financial
- Works well in non-desk environments as well as public places

Features

- **34 INCH MONITOR WALL MOUNT:** VESA 75x75/100x100mm compatible heavy duty articulating wall mount monitor arm supports a single display up to 34" (30.9lb/14kg)
- **WIDE RANGE OF MOTION:** Ergonomic monitor wall mount with +90/-15 tilt, +/-180 swivel, and 360 portrait/landscape rotating screen; Adjustable wall mounted monitor arm
- **20" LONG ARTICULATING ARM:** Featuring 3 different joints along the arm, each being able to swivel +/-90; Arm reaches out to 20.5" (520mm) & folds in to 5.1" (129.2mm) from wall for easy re-positioning
- **EASY INSTALLATION:** Premium silver aluminum single PC monitor wall mount w/ easy tool-less slide & click installation for arms & VESA plate/bracket (75x75/100x100mm); Reduced set-up time
- **ORGANIZED WORKSPACE:** Single LCD/LED computer monitor wall mount for areas with limited work surface space; Cable management clips along the arm; Decorative covers

Hardware

Warranty	10 Years
Cable Management	Yes
Articulating	No
# of Displays Supported	1
Mounting Options	Wall-Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

Weight Capacity (Per Display)	30.9 lb [14 kg]
-------------------------------	-----------------

Minimum Display Size	13"
Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	No
Maximum Arm Extension	20.5 in [520 mm]
Display Tilt	+90 / -15
Display Swivel	+180 / -180
Swivel / Pivot	+180/-180 at the wall 360 at the shoulder 360 at the elbow
Display Rotation	360

Physical Characteristics

Color	Silver
Material	Aluminum
Product Length	12.8 in [32.5 cm]
Product Width	13.4 in [34.0 cm]
Product Height	4.8 in [12.2 cm]
Weight of Product	7.5 lb [3.4 kg]

Packaging Information

Package Quantity	1
Package Length	13.4 in [34.0 cm]
Package Width	9.4 in [24.0 cm]
Package Height	3.9 in [10.0 cm]
Shipping (Package) Weight	4.6 lb [2.1 kg]

What's in the Box

Included in Package	1 - Wall Mount
	2 - Swivel Arms
	1 - Monitor Mount
	4 - Thumb Screws
	1 - M3 Hex Key
	2 - Wall Plugs
	2 - Mounting Screws
	1 - User Manual

****Product appearance and specifications are subject to change without notice.***