

Universal Projector Wall Mount - Projector Mount supports Short & Ultra Short Throw Projectors up to 33lb (15kg) - Tilt/Swivel/Rotate - Adjustable 16.5" to 27.7" from Wall

Product ID: PROJWALLMNT



The adjustable mount for short throw projectors helps you create a large image from a short distance and keeps your projector out of the way. It's ideal for classrooms, boardrooms, hospitality venues, and many other meeting spaces.

Supporting a wide range of projector brands, the short throw projector wall mount features a universal mounting pattern of 12.8" (325 mm) diameter and supports a weight capacity of 33.3 lb. (15 kg).

Adjust the distance of your projector from the wall using the telescopic arm, which extends from 16.5" to 27.7" (420 mm to 705 mm). The arm on the low-profile projector wall mount also tilts +5/- 5 degrees to help you find the ideal position. The lockable ball joint on the adjustable projector mount provides 360-degree swivel, +/- 25 degree horizontal / vertical tilt.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PROJWALLMNT is backed by a StarTech.com 2-year warranty and free, lifetime technical support

Certifications, Reports and Compatibility



Applications

- Mount a short throw projector in classrooms, lecture halls, or hospitality venues

- Ideal for boardrooms, lobbies, meeting rooms or other business applications

Features

- **UNIVERSAL PROJECTOR WALL MOUNT:** Supports short throw & ultra-short throw projectors w/ mounting hole pattern ranging up to 12.8" (325mm) in diameter; supports projectors up to 33.1lb (15kg)
- **ADJUSTABLE PROJECTOR MOUNT:** Supports both short and ultra short throw projectors; The arm allows you to position a projector between 16.5" & 27.7" from the wall (w/ incl tools) to adjust throw ratio
- **PRECISE ADJUSTABILITY:** Easily optimize projector placement with 3 color coded dials for +/-10 swivel, +/-5 tilt (pitch), +/-10 rotate (roll); +/-20mm lateral shift; Secure adjustment w/ incl wrench
- **BRAND COMPATIBILITY:** Projector wall mount compatible w/ projectors from brands like BenQ, Acer, Optoma, Eiki, Hitachi, Sanyo, NEC, Epson, Sony, LG & Dell among others(several screw sizes incl)
- **THOUGHTFUL DESIGN:** Heavy duty steel & aluminum construction, this wall projector mount/holder kit supports in-wall cable routing & integrated cable management; Includes decorative snap-on covers

Hardware

Warranty	2 Years
Mounting Options	Wall-Mount

Performance

General Specifications	Supports Short-Throw Ratio: 0.4:1
	Universal Mounting Pattern: 325 mm Diameter (12.8")
	Weight Capacity: 15kg (33.1 lb.)
	Wall Mount Arm Tilt: +/- 5
	Lockable Ball Joint: 360 Swivel, +/- 25 Horizontal & Vertical Tilt
Minimum Arm Extension	16.5 in [420 mm]
Maximum Arm Extension	27.8 in [705 mm]

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	40~60% RH

Physical

Characteristics

Color	Black & Silver
Material	Steel
Product Length	28.9 in [73.5 cm]
Product Width	7.1 in [18.0 cm]
Product Height	7.7 in [19.5 cm]
Weight of Product	7.5 lb [3.4 kg]

Packaging Information

Package Quantity	1
Package Length	22.4 in [57.0 cm]
Package Width	11.2 in [28.5 cm]
Package Height	5.7 in [14.5 cm]
Shipping (Package) Weight	9.7 lb [4.4 kg]

What's in the Box

Included in Package	1 - Wall Bracket
	1 - Projector Pole
	1 - Pole End Cap
	1 - Upper, Decorative Wall Cover
	1 - Lower, Decorative Wall Cover
	1 - Adjustment Module
	1 - Right, Adjustment Module Cover
	1 - Left, Adjustment Module Cover
	4 - Mounting Arms
	4 - Mounting Arm Covers
	1 - Hinge Connector
	6 - Wall Anchors

- 6 - Mounting Screws
- 4 - Washers
- 1 - Wrench (10mm)
- 1 - 5 mm Hex Key
- 4 - M3 x 24 mm Screws
- 4 - M4 x 24 mm Screws
- 4 - M5 x 24 mm Screws
- 4 - M6 x 8 mm Hex Screws
- 2 - M6 x 10 mm Screws
- 1 - M6 x 24 mm Screws
- 1 - M6 x 25 mm Hex Screw
- 4 - Nuts
- 1 - User Manual

****Product appearance and specifications are subject to change without notice.***