



1/2 ROUND SPACERS

RAF



RAF

Order Code: (code is blank)

<<<

>>>

Contents

Finishes:

select a finish

Quote

[\[How to create part numbers\]](#)

[\[Material Specifications\]](#)

| SELECT | PART NO. | LENGTH |
|-----------------------|----------|--------|
| <input type="radio"/> | 1215A | 31/32 |
| <input type="radio"/> | 1215 | 1/8 |
| <input type="radio"/> | 1215T | 5/32 |
| <input type="radio"/> | 1216 | 3/16 |
| <input type="radio"/> | 1216T | 7/32 |
| <input type="radio"/> | 1217 | 1/4 |
| <input type="radio"/> | 1217T | 9/32 |
| <input type="radio"/> | 1218 | 5/16 |
| <input type="radio"/> | 1218T | 11/32 |
| <input type="radio"/> | 1219 | 3/8 |
| <input type="radio"/> | 1219T | 13/32 |
| <input type="radio"/> | 1220 | 7/16 |
| <input type="radio"/> | 1220T | 15/32 |
| <input type="radio"/> | 1221 | 1/2 |
| <input type="radio"/> | 1221T | 17/32 |

| SELECT | PART NO. | LENGTH |
|-----------------------|----------|--------|
| <input type="radio"/> | 1222 | 9/16 |
| <input type="radio"/> | 1222T | 19/32 |
| <input type="radio"/> | 1223 | 5/8 |
| <input type="radio"/> | 1223T | 21/32 |
| <input type="radio"/> | 1224 | 11/16 |
| <input type="radio"/> | 1224T | 23/32 |
| <input type="radio"/> | 1225 | 3/4 |
| <input type="radio"/> | 1225T | 25/32 |
| <input type="radio"/> | 1226 | 13/16 |
| <input type="radio"/> | 1226T | 27/32 |
| <input type="radio"/> | 1227 | 7/8 |
| <input type="radio"/> | 1227T | 29/32 |
| <input type="radio"/> | 1228 | 15/16 |
| <input type="radio"/> | 1228T | 31/32 |
| <input type="radio"/> | 1229 | 1 |

| SELECT | PART NO. | LENGTH |
|-----------------------|----------|---------|
| <input type="radio"/> | 1230 | 1-1/16 |
| <input type="radio"/> | 1231 | 1-1/8 |
| <input type="radio"/> | 1232 | 1-3/16 |
| <input type="radio"/> | 1233 | 1-1/4 |
| <input type="radio"/> | 1234 | 1-5/16 |
| <input type="radio"/> | 1235 | 1-3/8 |
| <input type="radio"/> | 1236 | 1-7/16 |
| <input type="radio"/> | 1237 | 1-1/2 |
| <input type="radio"/> | 1238 | 1-9/16 |
| <input type="radio"/> | 1239 | 1-5/8 |
| <input type="radio"/> | 1240 | 1-11/16 |
| <input type="radio"/> | 1241 | 1-3/4 |
| <input type="radio"/> | 1242 | 1-13/16 |
| <input type="radio"/> | 1243 | 1-7/8 |
| <input type="radio"/> | 1244 | 1-15/16 |
| <input type="radio"/> | 1245 | 2 |

HOLE CLEARANCE CODE

| Select | CODE | +0.010 -0.000 |
|-----------------------|------|------------------|
| <input type="radio"/> | 6 | .140 |
| <input type="radio"/> | 8 | .166 |
| <input type="radio"/> | 10 | .192 |
| <input type="radio"/> | 12 | .218 |
| <input type="radio"/> | 25 | .252 |

| Select | CODE | MATERIAL | RoHS |
|-----------------------|------|-----------------|------|
| <input type="radio"/> | AL | ALUMINUM | YES |
| <input type="radio"/> | B | BRASS | YES |
| <input type="radio"/> | SS | STAINLESS STEEL | YES |
| <input type="radio"/> | S | STEEL | YES |
| <input type="radio"/> | N | NYLON | YES |
| <input type="radio"/> | PH | PHENOLIC | YES |

| Ordering Code | | | |
|---------------|----------------|---|--------|
| xxxx | x | x | x |
| | | | |
| | Clearance Hole | | Finish |
| Length | Material | | |

For non standard items
[please click here](#)



© 1999 RAF Electronic Hardware All Rights Reserved

Seymour CT 06483 203 888-2133 Fax: 203 888-9860 www.rafdwe.com