



Have a Question?  
Chat with a Product  
Information Specialist

What can we help you find?

5226600-1 Product Details

Share Print Email



5226600-1

TE Internal Number: 5226600-1  
 Active

**UHF/ Miniature UHF, RF Connectors**

Always EU RoHS/ELV Compliant (Statement of Compliance)

**Product Highlights:**

- Connector - RF
- Plug
- Applies To Coaxial Cable
- Without Snap-Lock
- Coaxial Cable Termination Type = Crimp

[View all Features](#)

- Quick Links**
- ▶ [Pricing & Availability](#)
  - ▶ [Search for Tooling](#)
  - ▶ [Product Feature Selector](#)
  - ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"><li>• <a href="#">PLUG,MINIATURE UHF</a> (PDF, English)</li></ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><a href="#">List all Documents</a></p>	<p><b>Related Products:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Tooling</a></li></ul>

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Product Type</a> = Connector - RF</li><li>• <a href="#">Gender</a> = Plug</li><li>• <a href="#">Dielectric Material</a> = Polypropylene</li></ul> <p><b>Mechanical Attachment:</b></p> <ul style="list-style-type: none"><li>• Panel Mount Retention = Without</li></ul> <p><b>Termination Features:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Coaxial Cable Termination Type</a> = Crimp</li><li>• <a href="#">Crimp Type</a> = Dual</li></ul> <p><b>Body Features:</b></p> <ul style="list-style-type: none"><li>• Snap-Lock = Without</li><li>• <a href="#">Body Size</a> = Miniature</li><li>• <a href="#">Body Plating</a> = Nickel</li></ul>	<p><b>Contact Features:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Center Contact Plating</a> = Tin</li></ul> <p><b>Configuration Features:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Coaxial Cable Type (RG/U or Mfg.)</a> = 58, 58A, 58B, 58C</li></ul> <p><b>Industry Standards:</b></p> <ul style="list-style-type: none"><li>• <a href="#">RoHS/ELV Compliance</a> = RoHS compliant, ELV compliant</li><li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li><li>• RoHS/ELV Compliance History = Always was RoHS compliant</li></ul> <p><b>Conditions for Usage:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Applies To</a> = Coaxial Cable</li></ul> <p><b>Other:</b></p> <ul style="list-style-type: none"><li>• Brand = AMP</li></ul>

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)



Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



DETAIL A  
RECOMMENDED STRIP LENGTH

- 1 SEE SEPARATE RESTRICTED CUSTOMER DRAWING
- 2 RG-58/U, RG-58A/U, RG-58B/U, AND RG-58C/U
- 3 USE CRIMPING TOOL: 220149-1
- 4 SEE INSTRUCTION SHEET I.S.2578
- 5 BULK PACKED

1	-	-	-	-	-	-	-	1-5226600-1
1	-	-	-	-	-	-	-	1-5226600-0
4/5	28.96 [1.140]	A	3	2	226599-2	226598-2	9-226603-0	5226600-1
REMARKS	L	STRIPPING SEE DETAIL	CRIMPING TOOL	FOR USE WITH CABLE	3 FERRULE QTY=1	2 COLLAR QTY=1	1 PLUG ASSY QTY=1	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
INCHES

MATERIAL  
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	0.41 [.016]
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

DWN  
A. FERNANDEZ-DOCK5  
CHK  
J. HAVENER  
APVD  
J. LIPPERT

01FEB2005  
01FEB2005  
01FEB2005

PRODUCT SPEC  
APPLICATION SPEC  
WEIGHT  
-

CUSTOMER DRAWING

Tyco Electronics Corporation  
Harrisburg, PA 17105-3608

NAME  
PLUG, MINIATURE UHF

SIZE A2	CAGE CODE 00779	DRAWING NO C=5226600	RESTRICTED TO -
------------	--------------------	-------------------------	--------------------

SCALE 4:1	SHEET 1	OF 1	REV 0
--------------	------------	---------	----------