

# **Catalog Number Selection**

Catalog Number Selection is for illustrative purposes only and not to be used to create new catalog numbers.

### Non-Illuminated Pushbuttons



### Illuminated and Non-Illuminated Push-Pulls



#### Note

① Add X at end of catalog number to receive parts assembled from factory.

## **Pushbuttons**

UL (NEMA) Type 3, 3R, 4, 4X, 12, 13

## **Momentary Pushbutton Operators, Non-illuminated**

	Button	Color	Catalog Number	
10250T10_	Flush button ①	Black	10250T101	
		Red	10250T102	<u>—</u>
		Green	10250T103	<del></del>
		Yellow	10250T104	<u>—</u>
		Gray	10250T105	<del></del>
		White	10250T106	<u>—</u>
		Blue	10250T108	<del></del>
		Orange	10250T109	<u>—</u>
10250T11_	Extended button	Black	10250T111	
		Red	10250T112	<u> </u>
		Green	10250T113	<u> </u>
		Yellow	10250T120	<u> </u>
		White	10250T116	<u> </u>
		Blue	10250T118	<del></del>
		Orange	10250T119	<del></del>
10250T5_	Half shrouded button		Vertical	Horizontal
		Black	10250T501	10250T511
		Red	10250T502	10250T512
		Green	10250T503	10250T513
		Yellow	10250T504	10250T514
		Gray	10250T505	10250T515
		White	10250T506	10250T516
		Blue	10250T508	10250T518
		Orange	10250T509	10250T519
10250T12_	Mushroom button	Black	10250T121	
		Red	10250T122	<del></del>
		Green	10250T123	<del>_</del>
		Yellow	10250T124	<del></del>
		Blue	10250T129	<del>_</del>
10250T17_	Jumbo mushroom button ②	Black	10250T171	
		Red	10250T172	<del>_</del>
		Red (EMERG. STOP)	10250T17213	<del>_</del>
		Green	10250T173	<del></del>
		Yellow	10250T174	
10250ED1164_	Low operating force— jumbo mushroom ②③	Black	10250ED1164-2	
		Red	10250ED1164-3	<u>—</u>
		Green	10250ED1164-4	
		Yellow	10250ED1164-5	
		Clear	10250ED1164	<u> </u>

**Note:** To order complete assembled unit using one composite catalog number, add contact block and legend plate suffix to the end of operator catalog number. Example: 10250T101-1TS33







**Contact Block** 





Legend Plate 10250<u>TS33</u>



## Notes

- ① To order operator with factory assembled extended retaining nut, 10250TA12, for thick panel applications, add suffix letter **E** to listed catalog number. Example: 10250T101**E**.
- ② Anodized aluminum head is not suitable for use in ultraviolet light applications.
- ③ Operating force—Standard = 2.4 lb; low force = 1.6 lb.