

Occupancy & Vacancy Sensors & Timers Timers

Pass & Seymour

Li legrand

Features


- Seven-button preset time switch.
- Manual ON/OFF.
- Adjustable time delay: 1, 5, 10, 20, 30, 60 minutes.
- Lighted switch for visibility in darkened rooms.
- Controls most types of lighting.

- cULus listed.
- 5-year warranty.
- Load: Incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp




RT1 shown with SWP26






RT1 Wiring



Product Controls



Pass & Seymour

□ legrand

Occupancy & Vacancy Sensors & Timers Timers






Features


- Programmable countdown time switch
- Manual ON/OFF.
- Digital countdown display.
- Adjustable time delay from 5-55 minutes (five-minute increments) to 1-12 hours (15-minute increments).
- Audible beep and visible light flash warnings before automatic-OFF.
- Lighted switch for visibility in darkened rooms.
- Works with most common lighting types.
- cULus listed.
- 5-year warranty.
- Load: Incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp



Catalog Number	Description	Rating	Load	Time- Running-Out Warning	Color				
Digital Timers									
RT12I RT12W RT12BK RT12LA	12-Hour Digital Timer, Neutral required	0-600W, 1/6 hp @ 120VAC 60 Hz	All	Yes Yes Yes Yes	lvory White Black Light Almond				

RT12 Wiring







RT24 shown with wall plate

Features

- Manual or programmed ON/OFF switching.
- Real time clock with day/date calendar.
- Easy to read LED display.
- Programming buttons accessible without removing wall plate.
- Eight programs can be assigned to any day or combination of days of the week.
- Automatically calculates sunrise and sunset times based on latitude and longitude.
- Audible or visual occupant warning before OFF.
- Power failure memory.
- Zero crossing circuitry.
- cULus listed.
- 5-year warranty.
- Load: Incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp

Catalog Number	Description	Rating	Load	Time- Running-Out Warning	Color
Astronomic Programmable Timers					
RT24I RT24W RT24BK RT24LA	24-Hour Programmable Timer	0-800W @ 120V 0-1200W @ 277V 1/6 hp @ 120/277V	All	Yes Yes Yes Yes	lvory White Black Light Almond