




What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)

TMS-RJS-RIBBON-4HT Product Details

[Share](#) [Print](#) [Email](#)



TMS-RJS-RIBBON-4HT

TE Internal Number: 754073-000

Active

Thermal Transfer & Dot Matrix Ribbons

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Printer Ribbons
- Printer Type = Thermal Transfer
- Ribbon Type = RJS-4HT
- Ribbon Color = Black
- Ribbon Width = 114.00 mm

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • Hardware/Software (PDF, English) • 4HT high performance black thermal transfer ribbon (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Printer Ribbons • Ink Type = Resin <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Printer Type = Thermal Transfer <p>Dimensions:</p> <ul style="list-style-type: none"> • Ribbon Width (mm [in]) = 114.00 [4.500] • Ribbon Length (M [ft]) = 300.00 [984.240] <p>Body Features:</p> <ul style="list-style-type: none"> • Ribbon Type = RJS-4HT • Ribbon Color = Black • Compatible Printers = TE Series • Compatible Materials = HT-SCE, HTCM-SCE-TP • Ribbon Configuration = Ink Side Out (Reverse Wound) 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Other:</p> <ul style="list-style-type: none"> • Brand = TE Connectivity • Comment = HTCM-SCE-TP with printer T312M only

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)