

# LUMILEDS<sup>™</sup> LUXEON<sup>®</sup> REBEL 11MM REFLECTIVE OPTIC



## **MECHANICAL DIMENSIONS**

7° "Spot" model 11.5mm (0.453") top diameter 11.2mm (0.433") base diameter 10.0mm (0.249") height

13° "Wide" model 9.7mm (0.433") top diameter 11.2mm (0.433") base diameter 3.8mm (0.142") height

## FEATURES / BENEFITS

- ▲ Only 11.5mm (0.453") maximum diameter
- Ideal for high packing density of LUXEON Rebel LEDs
- ▲ Adhesive backing for easy installation. Adhesive rated from -40°C to +120°C (-40°F to +248°F)
- ▲ Automatic alignment feature
- ▲ Spot & wide versions available
- ▲ Adhesive is approved to ESK-M3G162, WSK-3G184-A4 (Ford motor) & RES22LA06 type 2 (Rover)

## APPLICATIONS

Ideal for use with the new LUXEON Rebel LEDs in any application, particularly those where LEDs need to be spaced very closely together.

- Spot lighting
- ▲ Flood lighting
- ▲ Accent lighting
- RGB color mixing

## **ORDERING INFORMATION**

BASE LENSES		
Dialight P/N	Description	Degree*
OPC1-1-COL	7 degree "spot" model	7°
OPC1-2-COL	13 degree "wide" model	13°
*All angles refer to half divergence		

Dialight reserves the right to make changes at any time in order to supply the best product possible.

#### **Dialight Lumidrives**

York House • Weatherby Road • Long Marston, York, YO26 7NH Tel: 0845 6346161 • Fax: 0845 6346160 • www.dialight.com 1501 Route 34 South • Farmingdale, NJ 07727 USA


Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com

MDEXLUMREB10MM\_E


**Dialight Corporation** 




### **MECHANICAL DIMENSIONS**



### **PCB ALIGNMENT DIMENSION DETAILS**



## PHOTOMETRIC DATA



Consult factory for IES files

Dialight reserves the right to make changes at any time in order to supply the best product possible.

#### **Dialight Lumidrives**

York House • Weatherby Road • Long Marston, York, YO26 7NH Tel: 0845 6346161 • Fax: 0845 6346160 • www.dialight.com 1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com

MDEXLUMREB10MM\_E

**Dialight Corporation**