



- 1 CONNECTOR WILL ACCEPT POSTED TYPE III+ PIN CONTACTS.
- 2 CONTACT BODY: SELECT GOLD OVER NICKEL. CONTACT POST: TIN-LEAD PER MIL-T-10727 OVER COPPER PER MIL-C-14550A.
- 3 RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST: 1.02±0.08[.040±.003] DIA.
- 4 CONTACT BODY: SELECT GOLD OVER NICKEL. CONTACT POST: TIN OVER NICKEL.
- 5 POSITIONS LOADED WITH CONTACTS: 1-4, 10-17, 19-22, 24, 25, 29, 30, 32, 33.
- 6 POSITIONS LOADED WITH CONTACTS: 1-20, 22-28, 30-37.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
- 8 CONTACT BODY: TIN OVER NICKEL. CONTACT POST: TIN OVER NICKEL.
- 9 CONTACT BODY: SELECT GOLD OVER NICKEL. CONTACT POST: TIN/LEAD OVER NICKEL.
- 10 CONTACT BODY: TIN/LEAD OVER NICKEL. CONTACT POST: TIN/LEAD OVER NICKEL.

PRELIMINARY	5	NO	YES	YES	-	.170	2-206934-9
PRELIMINARY	5	NO	YES	NO	-	.413	2-206934-8
PRELIMINARY	5	NO	YES	NO	-	.257	2-206934-7
PRELIMINARY	9	NO	YES	YES	-	.119	2-206934-6
PRELIMINARY	5	NO	NO	NO	.150±.003	.240	2-206934-5
	10	NO	NO	NO	.150±.003	.220	2-206934-3
	5	NO	NO	YES	.150±.003	.119	2-206934-2
	5	NO	NO	NO	.150±.003	.119	2-206934-1
8 OBSOLETE	5	NO	YES	YES	-	.618	2-206934-0
	5	NO	NO	NO	.150±.003	.618	1-206934-9
	5	NO	NO	NO	.150±.003	.429	1-206934-8
	5	NO	YES	YES	-	.119	1-206934-7
PRELIMINARY	10	NO	NO	YES	.150±.003	.429	1-206934-5
	10	NO	YES	NO	-	.618	1-206934-4
	10	NO	YES	NO	-	.220	1-206934-3
6 PRELIMINARY	11	NO	NO	NO	.150±.003	.429	1-206934-2
	5	NO	NO	NO	.150±.003	.220	1-206934-1
PRELIMINARY	10	YES	NO	YES	-	.119	1-206934-0
	10	YES	YES	YES	-	.119	206934-9
	10	NO	NO	NO	.150±.003	.618	206934-7
	10	NO	NO	NO	.150±.003	.429	206934-6
	10	NO	NO	NO	.150±.003	.119	206934-5
	10	NO	YES	NO	-	.220	206934-4
OBSOLETE	10	NO	NO	NO	.158±.001	.618	206934-3
	10	NO	NO	NO	.158±.001	.429	206934-2
	10	NO	NO	NO	.150±.003	.220	206934-1
		CONTACT FINISH	M3 INSERTS	4-40 INSERTS	PERIPHERAL SEAL	B	A
							PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm. TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.005, 1 PLC ±.005, 2 PLC ±.005, 3 PLC ±.005, 4 PLC ±.005, ANGLES ±.005. MATERIAL: SEE CALLOUT. CONTACT: SEE CALLOUT. WEIGHT: -. SIZE: A1. CUSTOMER DRAWING. SCALE: 2:1. SHEET: 1 OF 1. REV: AF4.

DIN: J.GALLUCCI 5-30-91. CIRK: W.G.LENKER 4-14-92. APVD: K.BEAVER 4-14-92. NAME: RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 23-37, CPC. PRODUCT SPEC: 108-10024. APPLICATION SPEC: -. SIZE: A1. CASE CODE: 00779. DRAWING NO: 206934. RESTRICTED TO: -. WEIGHT: -. SCALE: 2:1. SHEET: 1 OF 1. REV: AF4.

STE TE Connectivity