

2TK2-48 Product Details

[Share](#) [Print](#) [Email](#)



Terminal Block Interface Modules & Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Accessory
- Accessory Type = SNAPTRACK Channel
- Track Width = 73.70 mm
- Track Length = 1219.20 mm
- PC Board Width = 69.90 mm

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

2TK2-48

(1-1437685-3)

TE Internal Number: 1-1437685-3

Active

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [2TK2-48 SNAPTRACK](#) (PDF, English)

Catalog Pages/Data Sheets:

- [BUCHANAN TERMINAL BLOCKS - INTERFACE MODULE SYSTEMS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Accessory
- Accessory Type = SNAPTRACK Channel

Electrical Characteristics:

- Track Width (mm [in]) = 73.70 [2.900]

Dimensions:

- PC Board Width (mm [in]) = 69.90 [2.750]

Body Features:

- Track Length (mm [in]) = 1219.20 [48.000]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Other:

- Brand = Buchanan

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)


Keep Me Informed



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0	B	REVISED PER ECO-13-012297	31JUL2013	KH MB

- 1 MATERIAL: RIGID PVC, COLOR: GRAY.
- 2. DESIGNED FOR 2.75 PC BOARD WIDTH.



1-1437685-3
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S SCHLEGEL	3/4/08		TE Connectivity						
DIMENSIONS: INCHES		CHK	C WARNER	3/4/08		NAME						
		APVD	C WARNER	3/4/08		PRODUCT SPEC						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				2TK2-48 SNAPTRACK						
MATERIAL		FINISH			SIZE	A2	CAGE CODE	00779	DRAWING NO	C=1-1437685-3	RESTRICTED TO	-
CUSTOMER DRAWING		SCALE			NTS	SHEET	1 of 1	REV	B			

1-1437685-3