



# Connectivity Solutions

Wireless

CATV


Audio &amp; Video

Networking &  
Structured Wiring

Military &amp; Aerospace

Test &amp; Measurement

## Product Detail



<b>Product Line:</b>	<a href="#">Aim</a> (Click for customer service)
<b>Part Number:</b>	25-7100
<b>Description:</b>	"F" TERMINATOR 1/4 WATT 5 %
<b>Product Family:</b>	CONNECTORS & ADAPTERS_F STYLE_TERMINATORS
<b>Connector A:</b>	F Type
<b>Genders:</b>	Male
<b>Standard Pack:</b>	25

20070523-1523



With one of the widest selections of 'F' connectors in the industry, we offer you a high-quality, cost-effective connectivity solution. All our 'F' connectors are designed to meet the high standards of the Satellite and Cable TV industries. Our 'F' type connectors are available for RG-59, RG-6 and RG-11 cable and are offered in twist-on, crimp, solder style, compression and weatherproof varieties.

**Weatherproof 'F' Connectors**



**Gel Filled 'F' (M)**  
Crimp, 0.324 Diameter, with O-ring for Weatherproof Application.



**F-56ALM WP (M)**  
Crimp, 1 Piece, 0.324 Diameter, Chromate Plated, with Interior Gasket.



**'F' Compression (M)** New!  
Crimp, 1 Piece for Weatherproof Applications (use crimp tool 24-77144P).

Part No.	Cable Type	Tool No.
25-7066	RG-6	24-7710P

Part No.	Cable Type	Tool No.
25-7056 (CPF56ALMWP)	RG-6	24-8866P

Nickel (10pk)	Gold (10pk)	Cable Type
25-2502-10PB	25-2502G-10PB	RG-59 Dual, Tri- & Quad Shield
25-2601-10PB	25-2601G-10PB	RG-6 Dual, Tri- & Quad Shield

**'F' 56 Series Connectors for RG-6**

(Use Crimp Tools 24-7710 or 24-8866P for connectors listed)



**Crimp-On F-56 (M)**  
with Separate 1/4" Ring.



**Crimp-On F-56ALX (M)**  
for RG-6 Tri-Shield & Quad Plenum Cable.



**Crimp-On F-56ALX (M)**  
for RG-6 Quad-Shield Cable.



**Crimp-On F-56A (M)**  
with attached 1/4" Rng.



**'F' Ratchet Crimp Tool**  
for RG-59, RG-6 and Quad Shield Cable.

Part No.
25-7150

Part No.
25-7033 (CPF56ALX)

Part No.
25-7034 (CPF56ALS)

Part No.
25-7160

Blister No.
24-8866P



**Crimp-On F-56ALM (M)**  
for RG-6 Cable.

Part No.
25-7032 (CPF56ALM)



**Crimp-On F-56 (M)**  
for Teflon/Plenum RG-6 Cable.

Part No.
25-7047



**Twist-On F-56 (M)**  
for standard RG-6 Cable.

Part No.
25-7180 (CPF156)



**Crimp-On F-56ALM (M)**  
for RG-6 Cable, Zinc Plated.

Part No.
25-7036

(M) = Male Plug (F) = Female Socket

**'F' 59 Series Connectors for RG-59**

(Use 24-7710 or 24-8866P for the following connectors)



**Crimp-On F-59 (M)**  
with Separate 1/8" Ring.

<b>Part No.</b>
25-7000



**Crimp-On Gold Plated F-59 (M)**  
with Separate 1/8" Ring.

<b>Part No.</b>
25-7000G



**Crimp-On F-59 (M)**  
with Separate 1/4" Ring.

<b>Part No.</b>
25-7010 (CPF591/4)



**Crimp-On F-59 (M)**  
with Separate 1/2" Ring.

<b>Part No.</b>
25-7020 (CPF591/2)



**Crimp-On F-59A (M)**  
with Attached 1/8" Ring.

<b>Part No.</b>
25-7050 (CPF59A)



**'F' Deluxe Hex Crimp Tool**  
for RG-6 & 59.

<b>Part No.</b>
24-7710



**Crimp-On F-59ALM (M)**  
for Standard RG-59 Cable.

<b>Part No.</b>
25-7030 (CP59ALM)



**Crimp-On F-59ALM (F)**  
for Standard RG-59 Cable.

<b>Part No.</b>
25-7081



**Crimp-On F-59ALX (M)**  
for Tri-Shield RG-59 & Quad Plenum.

<b>Part No.</b>
25-7031 (CP59ALX)



**Crimp-On F-59 (M)**  
for Teflon/Plenum RG-59 Cable.

<b>Part No.</b>
25-7049



**Crimp-On F-59 (M)**  
for Thin Cable RG-59, 62 Teflon.

<b>Part No.</b>
25-7035



**Right Angle Crimp-On F-59R (M)**  
for RG-59 Cable.

<b>Part No.</b>
25-7146



**Push-On F-59PG (M)**  
or RG-59 Cable with Center Pin.

<b>Part No.</b>
25-7080



**Twist-On F-59TW (M)**  
for Standard RG-59 Cable.

<b>Part No.</b>
25-7120



**Twist-On F-59TW (M)**  
with 1/2" Grip for Standard RG-59.

<b>Part No.</b>
25-7121



**Twist-On F-59TW (M)**  
for RG-59 with Male Quick Disconnect.

<b>Part No.</b>
25-7280



**F-59T (M)**  
Terminator  
1/2 Watt @ 5%

<b>Part No.</b>
25-7100

**'F' Connectors for RG-11**



**Crimp-On F-11 (M)**  
2 Piece, with Separate 1/5" Ring.

<b>Part No.</b>	<b>Cable Type</b>	<b>Tool No.</b>
25-7190	RG-11 (CPF111/5)	24-7712P



**Crimp-On F-11 (M)**  
1 Piece, for Standard RG-11 Cable.

<b>Part No.</b>	<b>Cable Type</b>	<b>Tool No.</b>
25-7191 (CPF11ALM)	RG-11	24-7711P



**Crimp-On F-11 (M)**  
3 Piece, for Teflon/Plenum RG-11 Cable.

<b>Part No.</b>	<b>Cable Type</b>	<b>Tool No.</b>
25-7192	RG-11	24-7712P

(M) = Male Plug (F) = Female Socket