


## 1-1102565-6 Product Details

[Share](#) [Print](#) [Email](#)



**1-1102565-6**

TE Internal Number: 1-1102565-6  
 Active

### HTS Connectors and Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- HD.40 Series
- Accessory
- Accessory Type = Hood
- Product Size = 6
- Locking Device Type = Side Clip at Housing Bottom

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Accessory
- Accessory Type = Hood
- Product Size = 6
- [Thread Size](#) = PG29
- Color = Gray

#### Body Features:

- Entry Style = Side
- Dimensions (L x H x W) (mm [in]) = 93.5 x 76.0 x 43.0 [3.68 x 2.99 x 1.69]
- Material = Die Cast Aluminum

#### Contact Features:

- Corrosion Protected = No

#### Configuration Features:

- Locking Device Type = Side Clip at Housing Bottom

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Applies To = Cable

#### Packaging Features:

- Packaging Method = Box
- Packaging Quantity = 5

#### Other:

- Series = HD.40
- Brand = AMP
- Comment = Includes cable fitting

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)
- [AODA Multi-Year Accessibility Plan](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed