



Actual



Representative

Catalog Number: 2920NM
Product ID: 7TAD105200R0000
UPC Number: 78621079740
EAN Number: 05414363101710
Status: Active

Liquidtight Strain Relief Connector, Straight, 1/2 Inch NPT Thread, Cable Range 0.125 Inch/3.2mm to 0.375 Inch/9.5mm, Throat Diameter 0.55 Inch, IP65 Rating, UV Resistant Polyamide 6.6 Body, Black

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief
Standard	UL E13938, CSA 52391
Size	1/2 Inch
Conductor Range	0.125 Inch/3.2mm to 0.375 Inch/9.5mm
Material	Polyamide/Nylon 6.6
Color	Black
Temperature Rating	-34 to +105 Degrees C
Environmental Conditions	Ordinary, Wet, or Dry Locations

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	3.2-9.5mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP65
Colour	Black
Model	Straight
Strain relief	Y
Operating temperature	-34-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	100
Outer Dimensions (inches)	12.75x8.75x5.5
Weight Uom	5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00927-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com