



Representative

**Catalog Number:** 5332  
**Product ID:** 7TAD012100R0005  
**UPC Number:** 78621005332  
**EAN Number:** 05414363075639  
**Status:** Active

1/2 Inch Straight Steel Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

#### Header

3D Model Available on Website

#### North American Specifications (UNSPSC)

|             |   |
|-------------|---|
| UNSPSC      | 39121420 Liquid tight connectors  |
| IGCC        | 4585 Liquid tight connectors  |
| Brand Name  | T&B   |
| Type        | Connectors-Straight   |
| Application | Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture. |
| Standard    | UL E23018, CSA  |
| Size        | 1/2 Inch  |
| Material    | Steel   |
| Finish      | Electro Zinc Plated/Chromate Coating  |

#### European Specifications (ETIM)

|   |  |
|---|--|
| ETIM  | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch                                | 1/2 inch   |
| Model   | Straight   |
| Revolving thread                                    | N  |
| Construction type                                   | External thread  |
| Connection type screw connection to housing         | Thread   |
| Thread type   | NPT  |
| Thread connection size                              | Other  |
| One-piece   | N  |
| Material housing                                    | Steel  |
| Approved in combination with protective conduit CSA | Y  |
| Approved in combination with protective conduit UL  | Y  |

#### Packaging

|                           |                 |
|---------------------------|-----------------|
| Inner Quantity            | 25              |
| Inner Dimensions (inches) | 6x4.5x4         |
| Outer Quantity            | 100             |
| Outer Dimensions (inches) | 9.56x8.63x6.31  |
| Weight Uom                | 25 lbs. per 100 |

#### Documents / Support Tools

|                             |                      |
|-----------------------------|----------------------|
| Technical Data Sheet CA     | Available on Website |
| Technical Data Sheet Global | wsd-001535           |

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)