

## FEM8D2S

ABB contact for United  
States of America

### General Information

---

<b>Extended Product Type:</b>	FEM8D2S
<b>Product ID:</b>	1SNA116913R0700
<b>EAN:</b>	3472591169133
<b>Catalog Description:</b>	FEM8D2S End Sections Grey
<b>Long Description:</b>	FEM8D2S - End Sections - Grey - 1.5mm Spacing

---

### Categories

---

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Sections

---

### Ordering

---

<b>EAN:</b>	3472591169133
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	39269097

---

### Dimensions

---

<b>Product Net Weight:</b>	10.00 g
----------------------------	---------

---

### Container Information

---

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	155 mm
<b>Package Level 1 Height:</b>	5 mm
<b>Package Level 1 Length:</b>	200 mm
<b>Package Level 1 Gross Weight:</b>	0.20000 kg
<b>Package Level 1 EAN:</b>	3472591169133
<b>Package Level 2 Units:</b>	600 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Height:</b>	150 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 3 Units:</b>	28800 piece

---

### Environmental

---

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

---

### Additional Information

---

<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>Color:</b>	Grey
<b>Function:</b>	End Sections
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Product Main Type:</b>	FEM8D2
<b>Product Name:</b>	End Section

Spacing: 1.5 mm

---

### **Certificates and Declarations (Document Number)**

---

**Declaration of Conformity - CE:** 1SND225002C1007  
**GOST Certificate:** 1SND161005A1104  
**RoHS Information:** 1SND230478F0202

---

### **Classifications**

---

**ETIM 4.0:** EC000886 - Endplate and partition plate for terminal block  
**ETIM 5.0:** EC000886 - Endplate and partition plate for terminal block  
**Object Classification Code:** X

---