



Actual



Actual

Catalog Number: LTC038
Product ID: 7TAD012620R0000
UPC Number: 78621078953
EAN Number: 05414363155058
Status: Active

Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/8 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39131706 Electrical conduit |
| IGCC | 5535 Electrical conduit |
| Brand Name | T&B |
| Type | Liquidtight Flexible Non-Metallic Conduit |
| Special Features | The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily |
| Application | Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles. |
| Standard | UL E95745, CSA |
| Trade Size | 3/8 Inch/16mm |
| Outside Diameter | 18.0mm |
| Inside Diameter | 12.3mm |
| Length | 30.5 Meters |
| Voltage Rating | 600 Volts |
| Material | PVC |
| Color | Black |

European Specifications (ETIM)

| | |
|---------------------------|----------------------------------|
| ETIM | EC001177 Protective plastic hose |
| Nominal size in inch | 3/8 inch |
| Material | PVC |
| Operating temperature | -18-+105°C |
| Flexibility | Flexible |
| Colour | Black |
| Approved according to CSA | Y |

Packaging

| | |
|---------------------------|--------------------|
| Outer Quantity | 100 |
| Outer Dimensions (inches) | 19.1x6.4x19.8 |
| Weight Uom | 12.56 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
|-------------------------|----------------------|

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com