Thomas&Betts



Representative

Catalog Number: Product ID: UPC Number: EAN Number: Status:

LT38P 7TAD012550R0005 78621045064 05414363100584 Active

3/8 Inch Non-Metallic Liquidtight Bullet Connector

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.
- Suitable for hazardous locations; Class I Div 2; Class II Div 1 & amp; 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

Header

3D Model

Available on Website

North American Specifications (UNSPSC)

| UNSPSC | 39121420 Liquid tight connectors |
|-------------|--|
| IGCC | 4585 Liquid tight connectors |
| Brand Name | T&B |
| Туре | Bullet-Straight |
| Application | T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub. |
| Standard | UL E23018, CSA |
| Size | 3/8 Inch |
| Material | Thermoplastic |

001170 Carery composition for protoctive pla

European Specifications (ETIM)

| ETIM | EC001178 Screw connection for protective plastic |
|---------------------------|--|
| | hose |
| Nominal size in inch | 3/8 inch |
| Model | Straight |
| Revolving thread | Ν |
| Construction type | External thread |
| Type of connection | Thread |
| Thread connection size | Other |
| Thread length | 14.48mm |
| Material screw gland | Other |
| Material sealing | Other |
| Colour | Black |
| Packaging | |
| Inner Quantity | 20 |
| Inner Dimensions (inches) | 8x5x4 |
| Outer Quantity | 100 |
| Outer Dimensions (inches) | 26.5x9.25x5.5 |
| Weight Uom | 7 lbs. per 100 |
| Documents / Support Too | Is |

| Technical Data Sheet CA | Available on Website |
|-----------------------------|----------------------|
| Technical Data Sheet Global | ta00970-tb2 |
| Instruction Sheet 1 | ta00998-tb2 |



Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com