



Representative

**Catalog Number:** LT4200P  
**Product ID:** 7TAD012550R0008  
**UPC Number:** 78621045087  
**EAN Number:** 05414363100638  
**Status:** Active

2 Inch 45 Degree Bullet Connector, Non Metallic Conduit Fitting, for Liquidtight FNMC Type B, Meets NEMA Ratings 4, 4X, 6, 6P, 12 and 13, Weather Stabilized Thermoplastic Material UL Listed for Direct Burial

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.
- Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Bullet-45 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	2 Inch
Material	Thermoplastic

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	20.17mm
Material screw gland	Other
Material sealing	Other
Colour	Black

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	6x5x4
Outer Quantity	5
Outer Dimensions (inches)	21.7x6.5x5.3
Weight Uom	67.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	ta00970-tb2
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)