



CONTACT • REQUEST A QUOTE

PRODUCTS

RESOURCES

COMPANY

PART NUMBER SEARCH

search site



« Clamping Knobs

## Five Arm (Star) Clamping Knobs

### Series #2850

Clamping knobs are available in different materials, thermoplastic, and phenolic for a multiple of applications.

A variety of shapes and diameters with plain, tapped bosses or with studs are available with standard threads to fit the application.

Perfect for the industrial machinery, medical, general equipment and other industrial applications.

Knobs can be decorated or customized to your specific need.

Davies Molding is pleased to introduce our series of soft touch knobs and handles. Our soft touch parts are molded with a soft thermoplastic overmolded "rubber" top with a tough thermoplastic body underneath. The soft feel of the knob provides a comfortable touch with a sure grip.




Colors available upon request.

Please note: Not all variations available are listed below. Please [contact Customer Service](#) to inquire about all available options.



REQUEST CAD DRAWING

REQUEST A QUOTE



Item #	Diameter A	Height B	Hub C	Material Type	Mounting Diameter	Mounting Type	Thread Length/Depth	Color
2850	1	0.875	0.75	Thermoset	1/4-20	Female Insert	0.375	BLACK
2850-A	1	0.875	0.75	Thermoset	5/16-18	Female Insert	0.50	BLACK
2850-B	1	0.875	0.75	Thermoset	3/8-16	Female Insert	0.50	BLACK
2850-D	1	0.875	0.75	Thermoset	5/16-18	Projecting Stud	0.50	BLACK
2850-E	1	0.875	0.75	Thermoset	3/8-16	Projecting Stud	1	BLACK
2850-G	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	0.75	BLACK
2850-N	1	0.875	0.75	Thermoset	5/16-18	Projecting Stud	1.5	BLACK
2850-Q	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	0.50	BLACK
2850-R	1	0.875	0.75	Thermoset	5/16-18	Projecting Stud	2	BLACK
2850-T	1	0.875	0.75	Thermoset	M6	Female Insert	12mm	BLACK
2850-U	1	0.875	0.75	Thermoset	8-32	Female Insert	0.375	BLACK
2850-W	1	0.875	0.75	Thermoset	5/16-18	Projecting Stud	1	BLACK
2850-X	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	1	BLACK
2850-Z	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	0.31	BLACK
2850AC	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	0.75	BLACK

2850AD	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	0.50	BLACK
2850AF	1	0.875	0.75	Thermoset	1/4-20	Female Insert	0.375	BLACK
2850AH	1	0.875	0.75	Thermoset	10-32	Female Insert	0.375	BLACK
2850AJ	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	1	BLACK
2850AN	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	0.625	BLACK
2850AQ	1	0.875	0.75	Thermoset	1/4-20	Projecting Stud	2.25	BLACK

PRODUCTS

- Knobs
- Handles
- Leveling Feet
- Latches
- Hinges
- Indexing Plungers
- Electronic Enclosures
- Two-Shot / Soft Touch
- Frac Balls
- Custom Molding

RESOURCES

- Engineering Specifications
- Distributor Listing
- Sales Representative Listing

COMPANY

- About Us
- Capabilities
- Certifications
- Contact Us
- Blog
- Careers

QUESTIONS ?

[select your industry]
▼

questions / comments

Copyright © 2016 Davies Molding, LLC. All Rights Reserved.  
 350 Kehoe Blvd. | Carol Stream, IL 60188-1818 | Phone: (800) 554-9208 | Fax: (630) 510-9944