







  
 **1-800-554-9208**
  
[CONTACT](#) • [REQUEST A QUOTE](#)

[PRODUCTS](#)

[RESOURCES](#)

[COMPANY](#)

PART NUMBER SEARCH



[« Bar/T Knobs](#)

## Bar/T Knobs

### Series #3085

Over 20 different shapes of bar knobs and T knobs available in both thermoplastic and phenolic materials.

Sizes ranging from 1-1/32" to 3-3/8" in diameter.

Female insert, projecting stud and thru-hole bar knobs options.

Click on the part number for additional information and search by diameter, mounting, material, etc.

Knobs can be decorated or customized to your specific need.


Colors available upon request.

Please note: Not all variations available are listed below. Please [contact Customer Service](#) to inquire about all available options.



[REQUEST CAD DRAWING](#)

[REQUEST A QUOTE](#)



Item #	Diameter A	Height B	Hub C	Material Type	Mounting Diameter	Mounting Type	Thread Length/Depth	Color
3085	1.125	0.75	0.50	Thermoset	1/4-20	Female Insert	0.375	BLACK
3085-A	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.56	BLACK
3085-B	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.75	BLACK
3085-C	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	1.00	BLACK
3085-D	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	1.25	BLACK
3085-L	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.625	BLACK
3085-P	1.125	0.75	0.50	Thermoset	M6x1-6g	Female Insert	0.50	BLACK
3085-R	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.50	BLACK
3085-S	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.875	BLACK
3085-W	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.625	BLACK
3085AD	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.50	BLACK
3085AK	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.44	BLACK
3085AL	1.125	0.75	0.50	Thermoset	1/4-20	Female Insert	0.375	RED
3085AW	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.375	BLACK
3085AX	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.75	BLACK

3085BA	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	2	BLACK
3085BC	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.56	BLACK
3085BD	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	2.50	BLACK
3085BF	1.125	0.75	0.50	Thermoset	1/4-20	Female Insert	0.50	BLACK
3085BG	1.125	0.75	0.50	Thermoset	1/4-20	Projecting Stud	0.75	BLACK

PRODUCTS

- Knobs
- Handles
- Leveling Feet
- Latches
- Hinges
- Indexing Plungers
- Electronic Enclosures
- Two-Shot / Soft Touch
- Frac Balls
- Custom Molding

RESOURCES

- Engineering Specifications
- Distributor Listing
- Sales Representative Listing

COMPANY

- About Us
- Capabilities
- Certifications
- Contact Us
- Blog
- Careers

QUESTIONS ?

Copyright © 2016 Davies Molding, LLC. All Rights Reserved.  
 350 Kehoe Blvd. | Carol Stream, IL 60188-1818 | Phone: (800) 554-9208 | Fax: (630) 510-9944