

# CR-P120AC2

ABB contact for United  
States of America



## General Information

---

<b>Extended Product Type:</b>	CR-P120AC2
<b>Product ID:</b>	1SVR405601R2000
<b>EAN:</b>	4013614498244
<b>Catalog Description:</b>	CR-P120AC2 Pluggable interface relay
<b>Long Description:</b>	The CR-P120AC2 pluggable interface relay is from the CR-P (pcb) relay range. This relay operates with a 120 V AC rated control supply voltage and has a 2 c/o (SPDT) output with contacts rated at 250 V / 8 A. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories.

---

## Categories

---

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

---

## Ordering

---

<b>EAN:</b>	4013614498244
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85364900

---

## Dimensions

---

<b>Product Net Width:</b>	12.7 mm
<b>Product Net Height:</b>	15.7 mm
<b>Product Net Depth:</b>	29.0 mm
<b>Product Net Weight:</b>	0.014 kg

---

## Container Information

---

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	332.0 mm
<b>Package Level 1 Height:</b>	28.0 mm
<b>Package Level 1 Length:</b>	17.0 mm
<b>Package Level 1 Gross Weight:</b>	0.157 kg
<b>Package Level 1 EAN:</b>	4013614373053

---

## Technical

---

<b>Function:</b>	Pluggable pcb interface relay CR-P
<b>Sub-Function:</b>	Relay w/o built in LED
<b>Output:</b>	2 c/o (SPDT) contacts
<b>Output Signal:</b>	250 V / 8 A
<b>Rated Control Supply Voltage (U<sub>g</sub>):</b>	120 V AC

---

## Environmental

---

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

---

## Certificates and Declarations (Document Number)

---

<b>CCC Certificate:</b>	CCC_2007010303228779
<b>CSA Certificate:</b>	CSA_1587291

<b>cUR Certificate:</b>	cUR_E244330
<b>Declaration of Conformity - CE:</b>	1SAD938501-0159
<b>EAC Certificate:</b>	EAC_RU_C-PL.ME77.B.01873
<b>GOST Certificate:</b>	GOST_POCC_DE.AB76.D02256
<b>RMRS Certificate:</b>	RMRS_12.04008.250
<b>RoHS Information:</b>	1SAA981040-4404
<b>UR Certificate:</b>	UR_E244330
<b>VDE Certificate:</b>	VDE_40019129

---

## Classifications

---

<b>Object Classification Code:</b>	K
<b>ETIM 4.0:</b>	EC001437 - Switching relay
<b>ETIM 5.0:</b>	EC001437 - Switching relay
<b>UNSPSC:</b>	39121500
<b>eClass:</b>	7.0 27371601

---

