

External 240V 3U Rack/Tower Battery Pack Enclosure + DC Cabling for select UPS Systems (BP240V10RT3U)

MODEL NUMBER: **BP240V10RT3U**



Description

BP240V10RT3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 240V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 240V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - [SU6000RT3U](#), [SU6000RT3UHV](#), [SU8000RT3U](#), [SU8000RT3U1TF](#), [SU8000RT3UG](#), [SU8000RT3UHW](#), [SU8000RT3UN50](#), [SU8000RT3UN50TE](#), [SU10000RT3U](#), [SU10000RT3U2TF](#), [SU10000RT3UG](#), [SU10KRT3U](#), [SU10KRT3UHV](#), [SU10K3/1INTPM](#), [SU16KRT](#), [SU16KRT-1TF](#), [SU16KRT8](#), [SU16KRTG](#), [SU16KRTHW](#), [SU20KRT](#), [SU20KRT-1TF](#), [SU20KRT8](#), [SU20KRTG](#), [SU20KRTHW](#) and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 240V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 240V external battery packs to the host UPS
- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- [2POSTRMKITHD](#) option supports balanced 2 point center-mounting in 2 post equipment racks

Highlights

- Extends the runtime of expandable 240V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

Package Includes

- BP240V10RT3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual



- 2-9USTAND option enables upright tower placement

Specifications

MODEL TEXT	
Key Benefit	Need more runtime? The BP240V10RT3U external battery pack extends the runtime of compatible Tripp Lite UPS Systems and has a rear connector for daisy-chaining multiple battery packs together to achieve an even longer runtime. Installation is quick, simple and versatile—the battery pack can be adapted to rackmount (3U), tower or stack form factors.
BATTERY	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple battery packs
DC System Voltage (VDC)	240
UPS Connection	Detachable cable with UPS specific DC connector (91.4 cm length, 6 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
Expandable Runtime	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (<u>2POSTRMKITHD</u>); Tower (<u>2-9USTAND</u>)
Minimum Required Rack Depth (inches)	33
Minimum Required Rack Depth (cm)	83.8
Shipping Dimensions (hwd / in.)	11.25 x 23 x 31.5
Shipping Dimensions (hwd / cm)	28.6 x 58.4 x 80
Shipping Weight (lbs.)	196.2
Shipping Weight (kg)	88.3
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 25
Unit Dimensions (hwd / cm)	13.34 x 44.45 x 63.5
Unit Weight (lbs.)	158.7
Unit Weight (kg)	71.4
Material of Construction	Black steel cabinet
External Battery Pack Form Factor	Rack/Tower
CERTIFICATIONS	
Certifications	Tested to UL, cUL, CE, NOM



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>