

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 25-ft.

MODEL NUMBER: **P560-025**



Description

Tripp Lite's 25 foot DVI Dual Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Note: Review your monitor manufacturer's specifications for a stated maximum DVI cable length. While many monitors only support a 5 meter (16ft) DVI cable, simply adding a Tripp Lite [B120-000](#) DVI Extender will guarantee full digital signal strength at any length up to 150ft. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual or Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI
- Dual Link digital signalling for transmission speeds to 9.9Gbps and 2560 x 1600 resolution
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors
- Check monitor manufacturer's cable length specs - may need Tripp Lite [B120-000](#) DVI Extender

Specifications

INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.6

Highlights

- For use with Dual or Single TMDS Link specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Check monitor manufacturer's cable length specs - may need Tripp Lite [B120-000](#) DVI Extender

System Requirements

- Monitor with DVI, and CPU with Dual or Single Link DVI capabilities

Package Includes

- DVI Dual Link TMDS cable - DVI-D, M/M, 25'



PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
CERTIFICATIONS	
Certifications	R0HS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>