



CONTACT • REQUEST A QUOTE

PRODUCTS

RESOURCES

COMPANY

PART NUMBER SEARCH

search site

« Control Knobs

Instrument Control Knobs

Series #1202

Control knobs and levers in thermoplastic, with or without flange and index/graduations.

Knobs can be decorated or customized to your specific need.

Perfect knobs for synthesizers and other electronic applications.

A variety of shapes and diameters with plain, tapped bosses or with studs are available with standard threads to fit the application.


A wide range of soft touch control knobs available in thermoplastic overmold.

Colors available upon request.

Please note: Not all variations available are listed below. Please [contact Customer Service](#) to inquire about all available options.



REQUEST CAD DRAWING REQUEST A QUOTE



Item #	Diameter A	Height B	Indicator Line	Inlay	Material Type	Mounting Diameter	Mounting Type	Set Screw Thread	Color
1202	0.78	0.625	No	No	Thermoset	0.25	Plain Molded Hole		BLACK
1202-A	0.78	0.625	No	No	Thermoset	0.25	Bushing		BLACK
1202-B	0.78	0.625	No	No	Thermoset	0.125	Plain Molded Hole		BLACK
1202-C	0.78	0.625	No	No	Thermoset	0.125	Bushing		BLACK
1202-D	0.78	0.625	No	No	Thermoset	0.19	Plain Molded Hole		BLACK
1202-F	0.78	0.625	No	No	Thermoset	0.25	Knurl Molded Hole		BLACK
1202-H	0.78	0.625	No	No	Thermoset	0.25 Flatted to 0.16	Spring		BLACK
1202-K	0.78	0.625	No	No	Thermoset	0.25 Keyway	Keyway Molded Hole		BLACK
1202-M	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole		BLACK
1202AF	0.78	0.625	No	Yes	Thermoset	0.25	Bushing		BLACK
1202AU	0.78	0.625	No	Yes	Thermoset	0.25 Flatted to 0.16	Spring		BLACK
1202AX	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole		BLACK
1202AY	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole		BLACK
1202AZ	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole		BLACK
1202BA	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole		BLACK

1202BC	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole	BLACK
1202BF	0.78	0.625	No	No	Thermoset	0.25	Bushing	BROWN
1202BJ	0.78	0.625	No	Yes	Thermoset	0.25	Bushing	BLACK
1202BM	0.78	0.625	No	Yes	Thermoset	0.125	Plain Molded Hole	BLACK
1202BP	0.78	0.625	No	Yes	Thermoset	0.125	Bushing	BLACK
1202BQ	0.78	0.625	Yes	Yes	Thermoset	0.19	Plain Molded Hole	BLACK
1202BZ	0.78	0.625	No	Yes	Thermoset	0.25 Keyway	Keyway Molded Hole	BLACK
1202CD	0.78	0.625	Yes	No	Thermoset	0.25 Flatted to 0.16	Spring	BLACK
1202CJ	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole	BLACK
1202CP	0.78	0.625	No	Yes	Thermoset	0.25	Bushing	BLACK
1202CY	0.78	0.625	No	No	Thermoset	M6 flatted to M4.5	Spring	BLACK
1202CZ	0.78	0.625	No	Yes	Thermoset	0.125	Plain Molded Hole	BLACK
1202DA	0.78	0.625	Yes	Yes	Thermoset	0.125	Plain Molded Hole	BLACK
1202DB	0.78	0.625	No	Yes	Thermoset	0.25	Plain Molded Hole	BLACK

PRODUCTS

- Knobs
- Handles
- Leveling Feet
- Latches
- Hinges
- Indexing Plungers
- Electronic Enclosures
- Two-Shot / Soft Touch
- Frac Balls
- Custom Molding

RESOURCES

- Engineering Specifications
- Distributor Listing
- Sales Representative Listing

COMPANY

- About Us
- Capabilities
- Certifications
- Contact Us
- Blog
- Careers

QUESTIONS ?

questions / comments

SEND

Copyright © 2016 Davies Molding, LLC. All Rights Reserved.
 350 Kehoe Blvd. | Carol Stream, IL 60188-1818 | Phone: (800) 554-9208 | Fax: (630) 510-9944