
1/2" Disc Thermostats - Automatic Reset CRA/ORA (625A) Series



These snap-action bimetal discs are housed in a ceramic case to handle extremely high temperatures. The increased factory calibrated set points are available up to 500°F (260°C). The contacts can either open or close on temperature rise.

All models are 100% temperature tested before leaving the factory.

Gold contacts available upon request. Value Added options available including over-mold and seal. For details regarding Value Added options, see pages 48.

Models available from stock - subject to availability	•	CRA - Close On-Rise (normally open)	٠	ORA - Open On-Rise (normally closed)
---	---	-------------------------------------	---	--------------------------------------

Open On-Rise	Model Number	Open ⁰F	Close ⁰F	Mounting	Terminals
Open	ORA-257-QCV	257 ± 9	230 ± 9	rotating bracket	.250 quick connects, vertical
Open	ORA-347-QCV	347 ± 16	284 ± 16	rotating bracket	.250 quick connects, vertical
Open	ORA-350-QC	350 ± 14	290 ± 20	rotating bracket	.187 quick connects, horizontal
Open	ORA-375-QC	375 ± 14	315 ± 20	rotating bracket	.250 quick connects, horizontal
Open	ORA-400-QC	400 ± 14	340 ± 20	rotating bracket	.250 quick connects, horizontal
Open	ORA-425-QC	425 ± 15	375 ± 20	rotating bracket	.250 quick connects, horizontal
Open	ORA-450-QC	450 ± 15	370 ± 20	rotating bracket	.250 quick connects, horizontal
Open	ORA-500-QC	500 ± 20	420 ± 20	rotating bracket	.250 quick connects, horizontal
Open	ORA-500-QCV50	500 ± 20	450 ± 20	rotating bracket	.250 quick connects, vertical

Note: Single operation (one-shot) feature is available. Once the contacts have opened, the contacts will not reclose until ambient temperature drops below -31°F (-35°C).

Special Order Map For CA/OA , OM, CR/OR, and CRA/ORA Series

Build Your Own Part								
Model Contacts Function	Terminal Bracket Type	Terminal Orientation	Set Point	°F/ºC Differential				
Model602SCA/OA Series - 1/2" Automatic Reset603U-HOM Series - 1/2" Manual Reset622ACR/OR Series - Standard Case - 1/2" A622PCR/OR - 4-Post Case - 1/2" Automatic625ACRA/ORA - High Temperature - 1/2" Automatic	Reset refer to pa	ge 8 ge 11 ge 11						
ContactsSSilver contactsKGold contacts								
FunctionXOpen on-rise (normally closed)YClose on-rise (normally open)								
Terminal Type Models CA/OA (602S) and OM (603U-H) Models CR/OR (622A and 622P) and CRA/ORA	(625A) refer to pa							
Bracket Type Models CA/OA (602S) and OM (603U-H) Models CR/OR (622A and 622P) and CRA/ORA	refer to pa (625A) refer to pa							
Terminal Orientation								

0° 45° 90°

Example Part Number								
602	S	X	BV	AS	90	145	٩F	30
Model	Contacts	Function	Terminal Type	Bracket Type	Terminal Orientation	Set Point	°F/ºC	Differential