



CONTACT • REQUEST A QUOTE

PRODUCTS

RESOURCES

COMPANY

PART NUMBER SEARCH

search site



« Clamping Knobs

Knurled Scalloped Clamping Knobs

Series #3050

Clamping knobs are available in different materials, thermoplastic, and phenolic for a multiple of applications.

A variety of shapes and diameters with plain, tapped bosses or with studs are available with standard threads to fit the application.




Perfect for the industrial machinery, medical, general equipment and other industrial applications.

Knobs can be decorated or customized to your specific need.

Davies Molding is pleased to introduce our series of soft touch knobs and handles. Our soft touch parts are molded with a soft thermoplastic overmolded "rubber" top with a tough thermoplastic body underneath. The soft feel of the knob provides a comfortable touch with a sure grip.

Colors available upon request.

Please note: Not all variations available are listed below. Please [contact Customer Service](#) to inquire about all available options.



REQUEST CAD DRAWING

REQUEST A QUOTE

Item #	Diameter A	Height B	Hub C	Material Type	Mounting Diameter	Mounting Type	Thread Length/Depth	Color
3050	1.75	0.94	1	Thermoset	1/4-20	Female Insert	0.375	BLACK
3050-A	1.75	0.94	1	Thermoset	5/16-18	Female Insert	0.50	BLACK
3050-B	1.75	0.94	1	Thermoset	3/8-16	Female Insert	0.50	BLACK
3050-C	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	0.56	BLACK
3050-D	1.75	0.94	1	Thermoset	5/16-18	Projecting Stud	0.75	BLACK
3050-E	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	0.44	BLACK
3050-H	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	1.25	BLACK
3050-J	1.75	0.94	1	Thermoset	0.25	Plain Molded Hole	0.50	BLACK
3050-K	1.75	0.94	1	Thermoset	0.25	Plain Molded Hole	0.50	BLACK
3050-U	1.75	0.94	1	Thermoset	3/8-24	Female Insert	0.625	BLACK
3050-Y	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	1.00	BLACK
3050AC	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	1.00	BLACK
3050AD	1.75	0.94	1	Thermoset	3/8-24	Projecting Stud	0.75	BLACK
3050AH	1.75	0.94	1	Thermoset	5/16-18	Projecting Stud	1.00	BLACK
3050AX	1.75	0.94	1	Thermoset	10-32	Female Insert	0.375	BLACK

3050BF	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	1.50	BLACK
3050BL	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	3.00	BLACK
3050BW	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	0.75	BLACK
3050BX	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	0.75	BLACK
3050CH	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	0.625	BLACK
3050CW	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	2.50	BLACK
3050DB	1.75	0.94	1	Thermoset	0.31	Bushing	0.625	BLACK
3050DS	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	0.375	BLACK
3050ED	1.75	0.94	1	Thermoset	3/8-24	Projecting Stud	1.25	BLACK
3050EE	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	0.75	BLACK
3050EH	1.75	0.94	1	Thermoset	5/16-18	Projecting Stud	0.75	BLACK
3050EM	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	0.50	BLACK
3050EP	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	1.25	BLACK
3050ES	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	1.75	BLACK
3050EU	1.75	0.94	1	Thermoset	3/8-16	Projecting Stud	2.25	BLACK
3050EX	1.75	0.94	1	Thermoset	1/4-20	Projecting Stud	0.31	BLACK

PRODUCTS

- Knobs
- Handles
- Leveling Feet
- Latches
- Hinges
- Indexing Plungers
- Electronic Enclosures
- Two-Shot / Soft Touch
- Frac Balls
- Custom Molding

RESOURCES

- Engineering Specifications
- Distributor Listing
- Sales Representative Listing

COMPANY

- About Us
- Capabilities
- Certifications
- Contact Us
- Blog
- Careers

QUESTIONS ?

Copyright © 2016 Davies Molding, LLC. All Rights Reserved.
 350 Kehoe Blvd. | Carol Stream, IL 60188-1818 | Phone: (800) 554-9208 | Fax: (630) 510-9944