




VOLEX
GROUP

Standard Cord Details: 17537 10 B1




| Specifications | |
|-----------------------------------|----------------|
| Certifications | |
| Part Number | 17537 10 B1 |
| Connector Type | C13 |
| Plug Type | none |
| Category | Plastic |
| Application | Non-Detachable |
| Plug Catalog No. | |
| Connector Catalog No. | |
| Cable | SJT AWG 18x3 |
| Jacket Color | black |
| Length in Feet | 9'10_ |
| Length in Meters | 3 |
| Temperature Rating | 60 C |
| Packaging Units Per Carton | H-100,H-25 |
| Color Coding | International |
| Nominal OD in Inches | 0.315 |
| Nominal OD in Millimeters | 8 |



VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: FOLD & TIE



NOTES:

- 1) CORDAGE: 18/3 SJT, 60°C, BLACK
- 2) APPROVALS:
- 3) RATING: 10 AMP/250 VOLTS
- 4) FLAME RATING : FT2
- 5) PACKAGING: 50 PIECES/CARTON
- 6) ALL DIMENSIONS IN MILLIMETERS.

| REV | DESCRIPTION | DATE |
|-----|---|---------|
| 2 | REDRAWN TO SHOW CHINESE MANUFACTURED CORD | 12/3/07 |
| 1 | C.U.D - NEW RELEASE | 9/17/07 |



FORM IN71-07 REV.A

- Indianapolis, IN
- Conover, N.C.
- Fremont, CA
- Aguascalientes, MX
- Tijuana, Mexico
- Hermosillo, MX
- Clinton, AR
- Kanata, Canada

Proprietary Notice:

This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

MATERIAL:
PLUG: PVC, BLACK
JACKET: PVC, BLACK, LEAD FREE

FINISH:
JACKET: SMOOTH

SCALE:
NOT TO SCALE

ECD:
N/A

ITEM DESCRIPTION
CORDSET - NORTH AMERICAN
WIRE HARNESS (9'10")

TOLERANCE UNLESS OTHERWISE SPECIFIED
.XXX ± .005
.XX ± .02
.X ± .03
FRACT. ± 1/32
ANGULAR ± 1/2°

| APPROVED | DRAWN BY | DATE: |
|----------|----------|---------|
| STC | STC | 9/17/07 |

PART NO.
17537 10 B1