





VOLEX

GROUP

## Standard Cord Details: 17422 10 B1



Specifications	
<b>Certifications</b>	
<b>Part Number</b>	17422 10 B1
<b>Connector Type</b>	none
<b>Plug Type</b>	5-15P
<b>Category</b>	Rubber
<b>Application</b>	Non-Detachable
<b>Plug Catalog No.</b>	
<b>Connector Catalog No.</b>	
<b>Cable</b>	SJ AWG 16x3
<b>Jacket Color</b>	Black
<b>Length in Feet</b>	12
<b>Length in Meters</b>	3.66
<b>Temperature Rating</b>	60 C
<b>Packaging Units Per Carton</b>	25
<b>Color Coding</b>	North America
<b>Nominal OD in Inches</b>	0.34
<b>Nominal OD in Millimeters</b>	8.64
<b>Notes</b>	See 17419 for 9ft version. See 17425 for 15ft version. See 17412 for 18 gauge version.



VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: BULK (NO HANK OR COIL)

- NOTES**  
 1) CORDAGE: 16/3 SJ, 60°C, BLACK  
 2) CERTIFICATIONS:   
 3) RATING: 13 AMP/125 VOLTS  
 4) FLAME RATING : FT2  
 5) PACKAGING: 40 PIECES/CARTON  
 6) ALL DIMENSIONS IN MILLIMETERS

REV	DESCRIPTION	DATE
2	REDRAWN TO SHOW CHINESE MANUFACTURED CORD	12/3/07
1	C.U.D - NEW RELEASE	9/7/07

 FORM IN71-07 REV.A	<input checked="" type="checkbox"/> Indianapolis, IN <input type="checkbox"/> Conover, N.C. <input type="checkbox"/> Fremont, CA <input type="checkbox"/> Aguascalientes, MX <input type="checkbox"/> Tijuana, Mexico <input type="checkbox"/> Hermosillo, MX <input type="checkbox"/> Clinton, AR <input type="checkbox"/> Kanata, Canada	<b>Proprietary Notice:</b> This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.	<b>MATERIAL:</b> PLUG: PVC, BLACK JACKET: PVC, BLACK ROHS COMPLIANT	<b>SCALE:</b> NOT TO SCALE	<b>ECD:</b> N/A	<b>ITEM DESCRIPTION</b> CORDSET - NORTH AMERICAN POWER SUPPLY CORD (12')		
	<b>FINISH:</b> JACKET: SMOOTH	<b>TOLERANCE UNLESS OTHERWISE SPECIFIED</b> .XXX ± .005 .XX ± .02 .X ± .03 FRACT. ± 1/32 ANGULAR ± 1/2°	<b>APPROVED</b> STC	<b>DRAWN BY</b> STC	<b>DATE:</b> 9/7/07	<b>PART NO.</b> 17422 10 B1		