








VOLEX

GROUP

## Standard Cord Details: 17268A 10 B1



Specifications	
<b>Certifications</b>	
<b>Part Number</b>	17268A 10 B1
<b>Connector Type</b>	C13
<b>Plug Type</b>	C14
<b>Category</b>	Plastic
<b>Application</b>	Y Cord
<b>Plug Catalog No.</b>	
<b>Connector Catalog No.</b>	
<b>Cable</b>	SJT AWG 18x3
<b>Jacket Color</b>	Black
<b>Length in Feet</b>	6': 2'legs
<b>Length in Meters</b>	
<b>Temperature Rating</b>	60 C
<b>Packaging Units Per Carton</b>	25
<b>Color Coding</b>	North America
<b>Nominal OD in Inches</b>	0.315
<b>Nominal OD in Millimeters</b>	8



VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: BULK (NO HANK OR COIL)

**NOTES:**

- 1) CORDAGE: 18/3 SJT, 60°C, BLACK, LEAD FREE
- 2) APPROVALS:
- 3) RATING: 10 AMPS/250 VOLTS
- 4) FLAME RATING : FT2
- 5) PACKAGING: 50 PIECES/CARTON
- 6) ALL DIMENSIONS IN MILLIMETERS.

REV	DESCRIPTION	DATE
1	C.U.D - NEW RELEASE	9/4/07



FORM IN71-07 REV.A

- Indianapolis, IN
- Conover, N.C.
- Freemont, CA
- Aguascalientes, MX
- Tijuana, Mexico
- Hermosillo, MX
- Clinton, AR
- Kanata, Canada

**Proprietary Notice:**

This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

MATERIAL:  
PLUG: PVC, BLACK  
JACKET: PVC, BLK, LEAD FREE

FINISH:  
JACKET: SMOOTH

SCALE:  
NOT TO SCALE

ECD:  
N/A

ITEM DESCRIPTION  
CORDSET - NORTH AMERICAN  
DETACHABLE POWER SUPPLY CORD (6')

TOLERANCE UNLESS OTHERWISE SPECIFIED  
.XXX ± .005  
.XX ± .02  
.X ± .03  
FRACT. ± 1/32  
ANGULAR ± 1/2°

APPROVED STC	DRAWN BY STC	DATE: 9/4/07
-----------------	-----------------	-----------------

PART NO.  
17268A 10 B1