

Grounding Accessories

Products		Product Documentation		
	Product Number	Product	Description	MSDS
	3040 UPC: 0-00-54007-34649-4 3M ID: 98-0798-0200-9	3M™ Accessories - Grounding Cord, 3040	Ground cord, 15 ft. (4.6 m), with 10 mm snap. Molded-in male snap fastener with integral one megohm resistor on one end, solderless terminal on other. Connects all 3M™ Static Control Mats and Runners to building ground.	
	3041 UPC: 0-00-54007-18090-6 3M ID: 98-0798-0856-8	3M™ Accessories - Grounding Kit, 3041	Grounding Kit for 3M™ Static Protective Hard Laminate includes #10 screw, lock washer, #10 nut, lock washer wing nut, #10 self-tapping screw and one 10 ft. (3.0 m) ground cord. Ground cord has a 1 megohm resistor.	
	3042 UPC: 0-00-54007-18223-8 3M ID: 98-0798-1054-9	3M™ Accessories - Grounding System, 3042	Wrist Strap Grounding System. Grounds two single conductor wrist straps and conveniently mounts beneath the edge of most work benches. Comes complete with 10 ft. (3.0 m) ground cord.	
	3037 UPC: 0-00-54007-18087-6 3M ID: 98-0798-0838-6	3M™ Accessories - Insulated Bulldog Clip, 3037	Fits standard banana plug.	
	3043 UPC: 0-00-54007-34761-3 3M ID: 98-0798-0400-5	3M™ Accessories - Interconnect Cord, 3043	Interconnect cord, 5 ft. (3.5 m), with 10 mm snap. Molded-in male snap fastener at each end. Connects all static control mats and runners to each other. Ground cord has a one megohm resistor.	
	3033 UPC: 0-00-54007-34763-7 3M ID: 98-0798-0402-1	3M™ Accessories - Snap Fastener, 3033	Snap Fastener, male, 0.125 in. (3.2 mm) hole, 10 mm diameter. For mats and runners. 1800/8800 Series.	
	3034 UPC: 0-00-54007-34764-4 3M ID: 98-0798-0403-9	3M™ Accessories - Snap Fastener, 3034	Snap fastener, female, 0.125 in. (3.2 mm) hole, 10 mm diameter. For 3M Mats and Runners 1800/8800 series.	



UPC: 0-00-54007-18444-7
3M ID: 98-0798-1353-5

8523, 10 x 8 x 2 in.

Carriers protect individual printed circuit boards from static and physical damage during storage and transport. Interiors are lined with dissipative cushioning foam.



[HGS1M](#)
UPC: 0-00-51111-15793-0
3M ID: 80-0011-2286-2

3M™ Standard Heel
Grounder, 1 Meg Resistor

Provides one grounding sole and an elastic strap around the heel.



[718](#)
UPC: 0-00-51138-71631-8
3M ID: 98-0798-4504-0

3M™ Static Sensor, 718

The 3M Static Sensor 718 is an easy-to-use, hand-held instrument designed to measure static voltages on objects and surfaces, arising from electrostatic charge buildups.



[718C](#)
UPC: 0-00-51138-71634-9
3M ID: 98-0798-4507-3

3M™ Static Sensor, 718C

The 3M Static Sensor 718C Is An Easy-To-Use, Hand-Held Instrument Designed To Measure Static Voltages On Objects And Surfaces, Arising From Electrostatic Charge Buildups.



[701C](#)
UPC: 0-00-51138-37610-9
3M ID: 98-0798-2536-4

3M™ Test Kit For Static
Control Surfaces, 701C

This Kit Contains A Lightweight, User-Friendly Megohmmeter Plus All Of The Components Needed To Make Testing Mats And Other Surfaces Simple And Accurate. All Of The Items Are Packaged In A Foam-Lined Carrying Case.



[2053](#)
UPC: 0-00-54007-49153-8
3M ID: 98-0798-2084-5

3M™ Toe Grounder
Assembly (Premium
Performance)2053

Designed for use with high-heeled shoes, the 3M Toe Grounder Assembly 2053 grounds personnel when they are in contact with conductive/dissipative flooring.



[8023](#)
UPC: 0-00-54007-18355-6
3M ID: 98-0798-1191-9

3M™ Workstation
Grounding Kit 8023 include
2` x 4` gray vinyl table
mat, 4` x 6` gray vinyl
floor mat with grounding
accessories and wrist strap

The 8021 consists of a 2 ft. x 4 ft. gray vinyl table mat and 4 ft. x 6 ft. gray vinyl floor mat with grounding accessories and wrist strap included.



[8024](#)
UPC: 0-00-54007-18356-3
3M ID: 98-0798-1192-7

3M™ Workstation
Grounding Kit 8024










The 8021 consists of a 2'x4' blue vinyl table mat and 4'x6' blue vinyl floor mat with grounding accessories and wrist strap included.



[8031](#)
UPC: 0-00-54007-18358-7
3M ID: 98-0798-1194-3

3M™ Workstation
Grounding Kit 8031
includes 2 x` 4` brown
vinyl table mat, 4` x 6`
black electrically
conductive floor mat with
grounding accessories and
wrist strap

The 8031 consists of a 2 ft. x 4 ft. brown vinyl table mat, 4 ft. x 6 ft. black electrically conductive floor mat with grounding accessories and wrist strap.

	8033 UPC: 0-00-54007-18360-0 3M ID: 98-0798-1196-8	3M™ Workstation Grounding Kit 8033	The 8033 kit consists of a 2 ft x 4 ft gray vinyl table mat and 4 ft x 6 in black electrically conductive floor mat with grounding accessories and also includes a wrist strap.
	8034 UPC: 0-00-54007-18361-7 3M ID: 98-0798-1197-6	3M™ Workstation Grounding Kit 8034	The 8034 kit consists of a 2 ft x 4 ft blue vinyl table mat and 4 ft x 6 in black electrically conductive floor mat with grounding accessories and also includes a wrist strap.
	8021 UPC: 0-00-54007-18353-2 3M ID: 98-0798-1189-3	3M™ Workstation Grounding Kit, 8021	The 8021 kit consists of a 2 ft. x 4 ft. brown vinyl table mat and a 4 ft. x 6 ft. brown vinyl floor mat with grounding accessories and also includes a wrist strap.
	724 UPC: 0-00-51138-55919-9 3M ID: 98-0798-3713-8	3M™ Workstation Monitor, 724	The 3M Workstation Monitor 724 continuously monitors the resistance of the operator and worksurface ground connections.
	3047 UPC: 0-00-54007-18224-5 3M ID: 98-0798-1055-6	3M™ Workstation Product - Common Point Grounding System, 3047	Common Point Grounding System, 10 ft. (3 m) to ground workstation components. Single-row, six-terminal strip, protective cover, three cable clips. Ground cord has a one megohm resistor.
	3048 UPC: 0-00-54007-18239-9 3M ID: 98-0798-1067-1	3M™ Workstation Product - Grounding System, 3048	Easily snaps onto mats and runners, (10 mm snap); grounds two single conductor wrist straps. Comes complete with ring connector and 15 ft. (4.6 m) ground cord. Ground cord has a one megohm resistor for mat connection only.
	3050 UPC: 0-00-54007-34820-7 3M ID: 98-0798-0502-8	3M™ Workstation Product - Snap Fastener, 3050	Snap fastener, female, 10 mm diameter. For 3M table and floor mats and runners 8200 Series.
	740 UPC: 0-00-51138-37598-0 3M ID: 98-0798-2525-7	3M™ Wrist Strap And Footwear Tester, 740	The 3M Wrist Strap And Footwear Tester 740 Is An Ac-Powered Unit Designed To Be Wall-Mounted In A Production Facility For Daily Testing Of Employees' Static Control Wrist Straps.
	740C UPC: 0-00-51138-37621-5 3M ID: 98-0798-2547-1	3M™ Wrist Strap And Footwear Tester, 740C	The 3M Wrist Strap And Footwear Tester 740 Is An Ac-Powered Unit Designed To Be Wall-Mounted In A Production Facility For Daily Testing Of Employees' Static Control Wrist Straps.