



Electrical OEM Materials

- Products
- Documentation & Literature
- News & Tradeshows
- Support

[United States](#) > [All 3M Products](#) > [Market Segments](#) > [Electronics, Electrical, and Communications](#) > [Electrical Products](#) > [Electrical OEM Materials](#) > [Products](#) > [Electrical OEM Products Catalog](#) > [Electrical & EMI Tapes](#) > [Tapes](#) > 3M™ Composite Film Electrical Tape 44-TAN-1/2"X90YD, 1/2 in x 90 yd (12,7 mm x 82 m), Polyester film/web film, 72 per case

3M™ Composite Film Electrical Tape 44-TAN-1/2"X90YD, 1/2 in x 90 yd (12,7 mm x 82 m), Polyester film/web film, 72 per case

3M ID 80610610471 UPC# 00054007558910 3M Product Number 44-TAN-1/2"X90YD



This .0055 inch thick tape is a polyester web reinforced polyester film coated with a rubber pressure-sensitive adhesive. On a 3 inch paper core this puncture-resistant tape is tough and conformable with excellent electrical properties.

Overview

Documentation

Specifications

Adhesion Strength	65 Ounce
Adhesive Material	Thermosetable rubber resin
Backing Material	Composite Film
Breaking Strength	40 Pound Per Inch (Of Width)
China RoHS - Below MCV	Yes
Color	Transparent
Core Material	Paper
Core Size	3 Inch
Dielectric Strength	5500 Volt
Electrolytic Corrosion Factor	1.0
Elongation	50 Percent
EU RoHS Compliant	Yes

Insulation Resistance	1 x 10 ⁶ megohms
Length	90 Linear Yard
Maximum Operating Temperature (Celsius)	130 Degree Celsius
Product Type	Polyester Film Tape/web film
Tape Length	90 Linear Yard
Tape Length (metric)	82.30 m
Tape Thickness	5.5 Milli-inch (mil)
Tape Total Thickness	5.5 Milli-inch
Tape Total Thickness (metric)	0.140 mm
Tape Width	0.50 in
Width	1/2 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

3M: [News](#) | [Careers](#) | [Investor Relations](#) | [MSDS Search](#) | [Transport Information Search](#) | [A-Z Product Index](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2014. All Rights Reserved.

