

# Multi-Flex Sheets — Highly Conformable Finishing

## Scotch-Brite™ Multi-Flex Abrasive Sheet A ULF (gold)

- Ultra flexible and conformable abrasive for cleaning or fine finishing
- Provides similar performance as steel wool grade 0000



## Scotch-Brite™ Multi-Flex Abrasive Sheet S ULF (gray)

- Highly conformable abrasive with silicon carbide mineral for exceptional finishes on wood and metal
- Provides similar performance as steel wool grade 000



## Scotch-Brite™ Multi-Flex Abrasive Sheet A VFN (dark maroon)

- Highly conformable abrasive with high cut for paint preparation and wood finishes without dumping edges
- Provides similar performance as steel wool grade 0



## Scotch-Brite™ Clean & Finish Rolls

- Flexible web for finishing, blending and polishing
- Conformable for access to hard-to-reach areas
- Can be cut to desired length for hand sanding or oscillating sanders



## Scotch-Brite™ Scrubbing Sponge 74 (Green)

- Highly conformable web laminate to a sponge backing
- Ideal for general purpose cleaning



# Multi-purpose Trial Pack

An easy, inexpensive way to see how the many Scotch-Brite™ Hand Pads outperform steel wool, wire brushes, and other non-woven hand pads. The trial pack includes one each of the following:

- Scrubbing Sponge 74
- Light Duty Pad 6448
- Heavy Duty Pad 7440
- Light Duty Cleansing Pad 7445
- Blending Pad 7446
- General Purpose Pad 7447
- Ultra-Fine Pad 7448
- Production Pad 8447
- Twist-Lok™ Pad Holder 961

## Scotch-Brite™ Product Ordering Information

| Description                   | UPC            | Color         | Grade | Inner Quantity       | Case Quantity |
|-------------------------------|----------------|---------------|-------|----------------------|---------------|
| Light Duty Cleansing Pad 7445 | 048011-16976-7 | ○ white       | —     | 20/box               | 3 boxes/case  |
| Ultra-Fine Hand Pad 7448      | 048011-04028-8 | ● gray        | S ULF | 20/box               | 3 boxes/case  |
| General Purpose Hand Pad 7447 | 048011-04029-5 | ● maroon      | A VFN | 20/box               | 3 boxes/case  |
| Production Hand Pad 8447      | 048011-24037-4 | ● maroon      | A VFN | 20/box               | 3 boxes/case  |
| Blending Hand Pad 7446        | 048011-04051-6 | ● gray        | S MED | 10/box               | 4 boxes/case  |
| Heavy Duty Hand Pad 7440      | 048011-04050-9 | ● tan         | A MED | 10/box               | 4 boxes/case  |
| Multi-Flex Abrasive Sheet     | 051131-07521-4 | ● dark maroon | A VFN | 60 sheets/roll       | 4 rolls/case  |
|                               | 051131-07522-1 | ● gray        | S ULF | 60 sheets/roll       | 4 rolls/case  |
|                               | 051131-07523-8 | ● gold        | A ULF | 60 sheets/roll       | 4 rolls/case  |
| Wood Finishing Roll 7745      | 051131-07745-4 | ● gold        | —     | 4.75 in x 15 ft/roll | 4 rolls/case  |
| Clean & Finish Roll           | 048011-00264-4 | ● maroon      | A MED | 4 in x 30 ft/roll    | 3 rolls/case  |
|                               | 048011-00265-1 | ● maroon      | A FIN | 4 in x 30 ft/roll    | 3 rolls/case  |
|                               | 048011-00266-8 | ● maroon      | A VFN | 4 in x 30 ft/roll    | 3 rolls/case  |
|                               | 048011-00270-5 | ● gray        | S VFN | 4 in x 30 ft/roll    | 3 rolls/case  |
|                               | 048011-00274-3 | ● maroon      | A MED | 6 in x 30 ft/roll    | 2 rolls/case  |
|                               | 048011-00275-0 | ● maroon      | A FIN | 6 in x 30 ft/roll    | 2 rolls/case  |
|                               | 048011-00276-7 | ● maroon      | A VFN | 6 in x 30 ft/roll    | 2 rolls/case  |
| Scrubbing Sponge 74           | 048011-20688-7 | ● green       | —     | —                    | 20/case       |
| Hand Pad Trial Pack 961S      | 048011-17144-9 | —             | —     | —                    | 5 packs       |
| Twist-Lok™ Pad Holder 961     | 048011-09493-9 | —             | —     | —                    | 10/case       |

**Product Use:** All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

**Warranty and Limited Remedy:** Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. **3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



### Industrial Business

Customer Response Center  
900 Bush Avenue, Building 21-1W-10  
St. Paul, MN 55106



Minimum 10% Post-Consumer Fiber

3M, Scotch-Brite and Twist-Lok are trademarks of 3M.

Printed in U.S.A.

© 3M 2003 61-5002-8008-8