





VOLEX

GROUP


## Standard Cord Details: 17503 10 B1

Specifications	
<b>Certifications</b>	
<b>Part Number</b>	17503 10 B1
<b>Connector Type</b>	C13
<b>Plug Type</b>	5-15P
<b>Category</b>	Plastic
<b>Application</b>	Detachable
<b>Plug Catalog No.</b>	PS204
<b>Connector Catalog No.</b>	386A
<b>Cable</b>	SJT AWG 16x3
<b>Jacket Color</b>	black
<b>Length in Feet</b>	9'10"
<b>Length in Meters</b>	3
<b>Temperature Rating</b>	60 C
<b>Packaging Units Per Carton</b>	H-100,H-25
<b>Color Coding</b>	International
<b>Nominal OD in Inches</b>	0.34
<b>Nominal OD in Millimeters</b>	8.64



VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: FOLD & TIE



**NOTES:**

- 1) CORDAGE: 16/3/SJT/60°C/BLACK
- 2) APPROVALS:
- 3) RATING: 13 AMP/125 VOLTS
- 4) FLAME RATING: FT2
- 5) PACKAGING: 50 PIECES/CARTON
- 6) ALL DIMENSIONS IN millimeters
- 7) PRODUCT IS ROHS COMPLIANT

1	C.U.D - NEW RELEASE	11/16/06
REV	DESCRIPTION	DATE



FORM IN71-D7 REV.A

- Indianapolis, IN
- Conover, N.C.
- Freemont, CA
- Aguascalientes, MX
- Tijuana, Mexico
- Hermosillo, MX
- Clinton, AR
- Kanata, Canada

**Proprietary Notice:**

This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

**MATERIAL:**  
 PLUG: PVC, BLACK  
 JACKET: PVC, BLACK  
 CONNECTOR: PVC, BLACK

**FINISH:**  
 JACKET: SMOOTH

**SCALE:**  
 NOT TO SCALE

**ECD:**  
 N/A

**ITEM DESCRIPTION**  
 CORDSET - NORTH AMERICAN  
 DETACHABLE POWER SUPPLY CORD (3 Mt)

**TOLERANCE UNLESS OTHERWISE SPECIFIED**  
 .XXX ±  
 .XX ±  
 .X ±  
 FRACT. ±  
 ANGULAR ±

<b>APPROVED</b> CR	<b>DRAWN BY</b> MAF	<b>DATE:</b> 11/16/06
-----------------------	------------------------	--------------------------

**PART NO.**  
 17503 10 B1