Double Shielded 26 AWG Stranded Cat 5E RJ45/RJ45 Patch Cord 25.0 Ft

Features for this product


- Double Shielded Foil + Braid Design Reduces EMI/RFI Interference
- Low Smoke Zero Halogen Jacket for Environmental and Safety Concerns
- 26 AWG Stranded Conductors for Flexibility
- Stock Lengths available up to 300Ft



When a regular shield is not enough, L-com's exclusive double-shielded patch cables are ideal. EMI/RFI interference is drastically reduced due to L-com's superior cable shielding, a combination of a 100% foil plus a 60% braid shield. The Low Smoke Zero Halogen jacket allows this industrial patch cable to meet today's environmental and safety requirements. With 26 AWG stranded conductors, this cable is flexible and easy to install even in tight spaces. We stock in full lengths up to 300 feet so that equipment runs can be pulled directly and simply plugged into either end.


| Details for this Modular product | | |
|----------------------------------|-----------------------|--|
| L-com Item # | TRD855DSZ-25 | |
| Manufacturer | L-com | |
| UPC # | 822335045712 | |
| RoHS Status | <u>RoHS Compliant</u> | |


Modular > Category 5E Shielded LSZH Patch Cords 10



Category 5E Double Shielded Low Smoke Zero Halogen Patch Cables for High EMI/RFI Environments

When a single shield is not enough, L-com's exclusive double-shielded patch cables are ideal. EMI/RFI interference is drastically reduced due to L-com's superior cable shielding, a combination of a 100% foil plus a 60% braid shield. The Low Smoke Zero Halogen (LSZH) jacket allows this industrial patch cable to meet today's environmental and safety requirements.





Category 5E Double Shielded LSZH 26AWG Stranded Patch Cables



This series features 26AWG stranded conductors that are flexible and easy to install even in tight spaces. L-com stocks lengths up to 300 ft and can



DOUBLE SHIELDED CATEGORY 5E

- Double shielded foil+braid reduces EMI/RFI interference
- Low smoke zero halogen jacket for environmental and safety concerns
- 26AWG conductors for flexibility
- Stock lengths are available up to 300 ft.



ship most orders the same day.

TRD855 TRD855

TRD855

TRD855 TRD85

TRD85

TRD85

TRD855 TRD85

TRD855

TRD855

| iray |
|------|
| iray |
| Gray |
| iray |
| Gray |
| Gray |
| iray |
| Gray |
| iray |
| iray |
| |

Category 5E Double Shielded LSZH 24AWG Solid Patch Cables

This series features 24AWG solid conductors allowing easy termination to IDC connectors. L-com stocks lengths up to 300 ft and can ship most orders the same day.

| TRD855SIG-1 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 1.0 ft | Lt. Gray |
|---------------|---|----------|
| TRD855SIG-2 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 2.0 ft | Lt. Gray |
| TRD855SIG-3 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 3.0 ft | Lt. Gray |
| TRD855SIG-5 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 5.0 ft | Lt. Gray |
| TRD855SIG-7 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 7.0 ft | Lt. Gray |
| TRD855SIG-10 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 10.0 ft | Lt. Gray |
| TRD855SIG-15 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 15.0 ft | Lt. Gray |
| TRD855SIG-25 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 25.0 ft | Lt. Gray |
| TRD855SIG-50 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 50.0 ft | Lt. Gray |
| TRD855SIG-75 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 75.0 ft | Lt. Gray |
| TRD855SIG-100 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 100.0 ft | Lt. Gray |